



FortiAP™-11C, 14C, 28C

Secure Remote Access Points



The Need for Secure Remote Access Points

Enterprises are looking to increase productivity through uninterrupted access to applications and resources, without compromising security and agility. You want to also extend your network to your employees' home offices and increase productivity, yet you want to retain visibility and control of your wireless network traffic by enforcing the same policies. You also need a solution that is easy for the employees to self install and for you to provision quickly and troubleshoot remotely.

Integrated Wireless Security and Access Solution

Fortinet's remote wireless access points deliver secure, identity-driven WiFi client access that creates a fortified WLAN network for the home user and tunnels traffic security to the corporate network. Centrally managed by a supported FortiGate® or FortiWiFi™ platform with its integrated wireless controller, these remote APs allow you to deploy a comprehensive, integrated security solution for your wireless and wired networks. The centralized FortiGate controllers enable you to deploy comprehensive unified threat management (UTM) protection over your wireless network.

Method of Operation

Upon powering up, this family of remote FAP automatically retrieves an IP address from the home WAN router and performs a DNS lookup of the preprovisioned domain name of your company to locate the wireless controller installed in your private cloud. Once connected to the wireless controller, it provides its device certificate to authenticate itself to the wireless controller and downloads its configuration along with the SSIDs it needs to broadcast throughout the home. You can configure the corporate controller to broadcast the same office SSID at the home office for seamless roaming and zero reconfiguration of employee laptops. Once the home user connects to the office SSID in their home, all their traffic will be forwarded through a secure encrypted tunnel to the corporate network without the need for any VPN clients. The wired ports can also be bridged with one of the SSIDs so devices, such as VoIP phones, can also connect to corporate office without any need for complex configuration. This product is designed to save IT administrators time and reduce helpdesk calls.

High Performance Secure Thin Access Points

- Leverage existing FortiGate or FortiWiFi platforms as controllers for low TCO
- Full range of authentications and access for all use cases
- Integration with FortiManager™ and FortiAnalyzer™ for unified control and reporting
- Fast Roaming for uninterrupted data access
- Automatic Radio Resource Provisioning (ARRP) for optimized throughput
- Flexible deployment options with simple per device pricing
- Layer 7 application QoS for maximum business productivity
- Rogue AP control for PCI DSS compliance



FortiCare

Worldwide 24x7 Support
support.fortinet.com



FortiWiFi / FortiAP

Secure business-grade wireless
Wireless.fortinet.com



FortiGuard

Threat Research & Response
www.fortiguard.com

www.fortinet.com



FAP-11C Plug-and-Play Access Point


The FortiAP-11C is a small plug-and-play access point suitable for traveling road warriors or remote access. This access point has an integrated power plug for easy storage and installation. It uses standards-based IEEE 802.11b/g/n to provide access to laptops and tablet devices. It also provides two Ethernet

ports (LAN and WAN) to allow devices such as Voice over IP telephones to easily connect to the corporate network, enabling an instant office environment for the distributed workforce.

FAP-14C and FAP-28C

The FortiAP-14C is a low cost 1x1 MIMO access point with integrated 5 port 10/100 switch in small desktop form factor. This device enables home office connectivity to the corporate network. FortiAP-28C is for larger offices and integrates a higher performance 2x2 MIMO access point with a 10 port Gigabit switch.

Remote AP discovers private cloud WiFi controller and securely tunnels all traffic



Differentiating Features & Benefits

Enterprise Unified Threat Management

Protects your network with the widest range of security and networking technologies seamlessly integrated into a single device: Firewall, IPS, Application Control, VPN, Web Filtering, and many others.

Application-Layer Quality of Service

Going above and beyond Wireless Multimedia Extensions (WME) by offering layer 7 traffic shaping and application use control.

'Single Pane of Glass' Management Console

Unmatched visibility and control of all wired and wireless network traffic that eliminates blind spots in your security infrastructure and ensures consistent and effective policy enforcement and compliance.

Remote AP

Allows simple and secure teleworker connection for wireless and wired devices alleviating the need for host VPN agents and complex configuration.



SPECIFICATIONS

TECHNICAL	FortiAP-11C	FortiAP-14C	FortiAP-28C
Hardware			
Hardware Type	Remote AP	Remote AP	Remote AP
Indoor/Outdoor Deployment	Indoor – Travel	Indoor – Home office	Indoor – Small office
Number of Radios	1	1	1
Number of Antennas	1 internal	1 internal	2 internal
Peak Antenna Gain	2 dBi for 2.4 GHz	2 dBi for 2.4 GHz	3 dBi for 2.4 GHz, 4 dBi for 5 GHz
Frequency Bands (GHz) *	2.400–2.4835	2.400–2.4835	2.400–2.4835, 5.150–5.250, 5.250–5.350, 5.470–5.725, 5.725–5.850
Frequency of Radio 1	2.4 GHz IEEE b/g/n	2.4 GHz IEEE b/g/n	2.4 GHz IEEE a/b/g/n, 5 GHz IEEE a/n
Tx/Rx Streams (802.11n mode)	1x1 MIMO with 1 spatial stream.	1x1 MIMO with 1 spatial stream.	2x2 MIMO with 2 spatial streams.
Ethernet Port	150 Mbps association rate.	150 Mbps association rate.	300 Mbps association rate.
Ethernet WAN Ports	1x 10/100/1000	1x 10/100	2x 10/100/1000
Ethernet LAN Ports	1x 10/100/1000	4x 10/100	8x 10/100/1000
Serial Console Port	No	No	No
USB Port	1 type A, 1 type B	No	2 type A, 1 type B
Power over Ethernet (PoE)	N/A	N/A	N/A
WME Multimedia Extensions	Yes (4 priority queues for voice, video, data and background traffic)	Yes (4 priority queues for voice, video, data and background traffic)	Yes (4 priority queues for voice, video, data and background traffic)
Simultaneous SSIDs	8 (7 for client access, 1 for monitoring)	8 (7 for client access, 1 for monitoring)	8 (7 for client access, 1 for monitoring)
EAP Type(s)	EAP-TLS, EAP-TTLS/MSCHAPv2, EAPo/EAP-MSCHAPv2, PEAPv1/EAP-GTC EAP-SIM, EAP-AKA, EAP-FAST	EAP-TLS, EAP-TTLS/MSCHAPv2, EAPo/EAP-MSCHAPv2, PEAPv1/EAP-GTC EAP-SIM, EAP-AKA, EAP-FAST	EAP-TLS, EAP-TTLS/MSCHAPv2, EAPo/EAP-MSCHAPv2, PEAPv1/EAP-GTC EAP-SIM, EAP-AKA, EAP-FAST
User/Device Authentication	WPA™ and WPA2™ with 802.1x or Preshared key, WEP and Web Captive Portal, MAC blacklist & whitelist	WPA™ and WPA2™ with 802.1x or Preshared key, WEP and Web Captive Portal, MAC blacklist & whitelist	WPA™ and WPA2™ with 802.1x or Preshared key, WEP and Web Captive Portal, MAC blacklist & whitelist
Maximum Tx Power	17 dBm (50mW) *	17 dBm (50mW) *	17 dBm (50mW) *
IEEE Specifications	802.11b, 802.11e, 802.11g, 802.11h, 802.11i, 802.11j, 802.11n, 802.1X	802.11b, 802.11e, 802.11g, 802.11h, 802.11i, 802.11j, 802.11n, 802.1X	802.11b, 802.11e, 802.11g, 802.11h, 802.11i, 802.11j, 802.11n, 802.1X

Dimensions

Height x Width x Length (in)	4.3 x 3.5 x 1.5	1.06 x 4.92 x 3.86	1.38 x 8.43 x 7.09
Height x Width x Length (mm)	110 x 89 x 34	27 x 125 x 98	35 x 214 x 180
Weight	0.22 kg (0.5 lbs)	0.1 kg (0.2 lbs)	0.5 kg (1.1 lbs)

Environment

Power Required	Integrated Power Plug	100–240 VAC, 50–60 Hz (external DC power adaptor)	100–240 VAC, 50–60 Hz (external DC power adaptor)
Power Consumption (AVG)	4.38 W	3.35 W	14 W
Power Consumption (MAX)	6.86 W	3.85 W	15 W
Heat Dissipation	17 BTU/h	4.5 BTU/h	45 BTU/h
Operating Temperature	-4–140°F (-20–60°C)	32–104°F (0–40°C)	32–104°F (0–40°C)
Storage Temperature	-4–158°F (-20–70°C)	-13–158°F (-25–70°C)	-13–158°F (-25–70°C)
Humidity	10 to 90% non-condensing	20 to 90% non-condensing	20 to 90% non-condensing

* Frequency selection and power may be restricted to abide by regional regulatory compliance laws.

DECLARATION OF CONFORMITY	FortiAP-11C	FortiAP-14C	FortiAP-28C
Organization	Compliance Identifier	Compliance Identifier	Compliance Identifier
CB	IEC 60950-1		IEC 60950-1
UL	UL 60950-1, CSA C22.2 No. 60950-1		UL 60950-1, CSA C22.2 No. 60950-1
FCC	FCC Part 15 Subpart B (ClassB), Subpart C		FCC Part 15 Subpart B (Class B), Subpart C and Subpart E
IC	RSS-210, RSS-GEN, RSS-102, ICES-003		IC RSS-210, RSS-GEN, RSS-102, ICES-003
CE	R&TTE Directive 1995/5/EC (EN 300 328, EN 301 489, EN 50385, EN 60950-1) EMC Directive 2004/108/EC (EN 55022, EN 55024) LVD Directive 2006/95/EC (EN 60950-1) RoHS2 Directive 2011/65/EU (EN 50581)		R&TTE Directive 1995/5/EC (EN 300 328, EN 301 893, EN 301 489, EN 50385, EN 60950-1) EMC Directive 2004/108/EC (EN 55022, EN 55024) LVD Directive 2006/95/EC (EN 60950-1) RoHS2 Directive 2011/65/EU (EN 50581)

RF RX/TX PERFORMANCE TABLE

		Radio 1	
		5 GHz	
		Tx Power (dBm)	
802.11 b		Rx Sensitivity	
1 Mbps		-86	
11 Mbps		-83	
802.11 g			
6 Mbps		-85	
9 Mbps		-83	
12 Mbps		-81	
18 Mbps		-79	
24 Mbps		-77	
36 Mbps		-73	
48 Mbps		-71	
54 Mbps		-69	
802.11n HT20			
MCS 0		-83	
MCS 1		-80	
MCS 2		-77	
MCS 3		-74	
MCS 4		-72	
MCS 5		-70	
MCS 6		-68	
MCS 7		-66	

ORDER INFORMATION

Product	SKU	Description
FortiAP-11C	FAP-11C	Remote wireless AP — 2x GE RJ45 ports (including 1x WAN port, 1x LAN port), single radio (802.11 b/g/n, 1x1 MIMO), Mounting kit not applicable, Integrated AC power adapter with international plugs.
	FC-10-P0011-311-02-DD	8x5 FortiCare Contract.
	FC-10-P0011-247-02-DD	24x7 FortiCare Contract.
	SP-ADAPTORPLUG-FAP11C	FAP-11C replacement power adapter plug package for Australia, China, EU, UK, US.
FortiAP-14C	FAP-14C	Remote wireless AP — 5x FE RJ45 ports (including 1x WAN port, 4x LAN ports), single radio (802.11 b/g/n, 1x1 MIMO), Integrated wall mount, AC power adapter included.
	FC-10-P0014-311-02-DD	8x5 FortiCare Contract.
	FC-10-P0014-247-02-DD	24x7 FortiCare Contract.
FortiAP-28C	FAP-28C	Remote wireless AP — 10x FE RJ45 ports (including 2x WAN ports, 8x LAN ports), single radio (802.11 a/b/g/n, 2x2 MIMO), Integrated wall mount, AC power adapter included.
	FC-10-P0028-311-02-DD	8x5 FortiCare Contract.
	FC-10-P0028-247-02-DD	24x7 FortiCare Contract.
FortiPlanner	N/A	FortiPlanner Wireless AP Deployment Planning Utility — FortiPlanner Lite Edition free download from Fortinet.com to support up to 50 Access Points. Requires Windows XP or Windows 7.
	FAP-FPL-PRO	FortiPlanner Wireless AP Deployment Planning Utility — Pro upgrade license unlocks FortiPlanner Lite (free version) to support more than 50 Access Points and includes site survey tool. Requires Windows 7.

REGION/COUNTRY SKU SUFFIX*									
Americas-FCC	China	Europe ETSI	International	Japan	Korea	Non-FFCA	Singapore	Taiwan	World 2.4G
-A	-C	-E	-I	-J	-K	-N	-S	-T	-W

*For the complete list of countries and regions, refer to <http://www.fortinet.com/wireless>.



GLOBAL HEADQUARTERS	EMEA SALES OFFICE	APAC SALES OFFICE	LATIN AMERICA SALES OFFICE
Fortinet Inc. 899 Kifer Road Sunnyvale, CA 94086 United States Tel: +1.408.235.7700 Fax: +1.408.235.7737	120 rue Albert Caquot 06560, Sophia Antipolis, France Tel: +33.4.8987.0510 Fax: +33.4.8987.0501	300 Beach Road #20-01 The Concourse Singapore 199555 Tel: +65.6513.3730 Fax: +65.6223.6784	Prol. Paseo de la Reforma 115 Int. 702 Col. Lomas de Santa Fe, C.P. 01219 Del. Alvaro Obregón México D.F. Tel: 011-52-(55) 5524-8480

Copyright© 2014 Fortinet, Inc. All rights reserved. Fortinet®, FortiGate®, FortiCare® and FortiGuard®, and certain other marks are registered trademarks of Fortinet, Inc., and other Fortinet names herein may also be registered and/or common law trademarks of Fortinet. All other product or company names may be trademarks of their respective owners. Performance and other metrics contained herein were attained in internal lab tests under ideal conditions, and actual performance and other results may vary. Network variables, different network environments and other conditions may affect performance results. Nothing herein represents any binding commitment by Fortinet, and Fortinet disclaims all warranties, whether express or implied, except to the extent Fortinet enters a binding written contract, signed by Fortinet's General Counsel, with a purchaser that expressly warrants that the identified product will perform according to certain expressily-identified performance metrics and, in such event, only the specific performance metrics expressly identified in such binding written contract shall be binding on Fortinet. For absolute clarity, any such warranty will be limited to performance in the same ideal conditions as in Fortinet's internal lab tests. Fortinet disclaims in full any covenants, representations, and guarantees pursuant hereto, whether express or implied. Fortinet reserves the right to change, modify, transfer, or otherwise revise this publication without notice, and the most current version of the publication shall be applicable.