



DISPLAY & TOUCH	17-inch 4:3 (1280x1024), 400 nits, 5-wire resistive touch
CPU SUPPORT	Intel® Core™ 2 Duo mobile 2.2GHz FPGA with low-noise fan
CHIPSET	Intel® GME965 chipset + ICH8M
MEMORY	2 Dual Channel DDR2 SODIMM socket supports up to 4GB
HDD SUPPORT	SATA port with 150 MB/s transfer rate
NETWORKING	2x1GbE ports, Realtek RTL8111B Gigabit Ethernet
AUDIO	Realtek ALC286 Audio Codec, 2 + 2 watts power amplifier
I/O PORTS	8 USB (4 external I/O, 2 ports with on-board pin headers, and 2 ports reserved for webcam and touch screen), 1 VGA DB-15, 1 DVI output, Triple audio jack, 3 Serial Ports DB-9, 2 Keyboard/Mouse Connectors, 2 LAN, 1 DC-in power connector
STORAGE	2.5" SATA HDD drive bay with anti-vibration mechanism, Bootable Compact Flash slot for CF type I/II storages
WALL MOUNT	VESA Mount 75/100mm
OPTICAL DRIVE	External ODD Only
EXPANSION SLOTS	1 x PCI 2.2 bus slot 1 x mini-PCI socket 1 x mini-PCIe socket
SYSTEM BIOS	Award BIOS, ACPI supported
POWER SUPPLY	Uses 100Watt AC Adapter. Input: 100 ~ 240 VAC, 1.25A max @ 47~63Hz. Output: 12V @ 8.33A. System can support DC12V~28V power input
SECURITY LOCK	Security lock slot located on the back of the system case
DIMENSIONS	420mm x 360mm x 85mm (W x D x H)

WEIGHT	Unit: 22lbs with base, 15.4lbs without base, Power Adapter: 1.9lbs.
OPERATING ENVIRONMENT	Operating Temperature: 10degC ~ 40degC, Storage Temperature: -20degC ~ 60degC
RELATIVE HUMIDITY	10% ~ 90% (non-condensing)
OPERATING SYSTEM	Microsoft Windows 7, Vista, XP, 2000, Linux
AVAILABLE COLORS	White, Black
SAFETY & EMI CERTIFICATIONS	CE/FCC Class B / EN60601-1 / UL60601-1, UL/cUL, VCCI, EPEAT Silver rated
ANTI-BACTERIAL COATING	The plastic coating PU-206 contains 0.4% Vanquish-100 (antimicrobial) demonstrated at least 99.6% bacterial reduction after 24 hours contacting after time
NOISE	< 35dB
POWER CONSUMPTION	80W

Corporate Headquarters
Cybernet Manufacturing
5 Holland, Buildings 201 & 205
Irvine, CA 92618
Toll free: 888-834-4577
Local: 949-600-8000
Fax: 949-600-8013
www.cybernetman.com
support@cybernetman.com
sales@cybernetman.com

Cybernet Europe
Network House, Hawkins Road
Colchester, Essex CO2 8LA
United Kingdom
UK Phone: 0845 539 1200
UK Fax: 0845 539 1201
International Phone: 44 1442 863388
International Fax: 44 1442 863444
www.cyberneteuropa.com
sales@cyberneteuropa.com
support@cyberneteuropa.com

Space Technology Co., Ltd.
4F, No 49, Lane 76, Rui Guang Rd.
NeiHu District, Taipei,Taiwan, R.O.C.
Tel: 886-2-2790-4776
Fax: 886-2-2793-3172
www.cybernet.com.tw
support@cybernet.com.tw
sales@cybernet.com.tw