

25 ft Coax High Resolution VGA Monitor Extension Cable - HD15 M/F

Product ID: MXT101HQ_25



This 25ft High Resolution VGA Extension Cable is designed to provide the highest video quality possible through VGA.

Ideally suited for high resolution VGA applications, this high quality male to female coaxial VGA extension cable helps to eliminates picture "ghosting" and fuzzy images inherent to non-coaxial cables, and provides superior EMI interference protection by using ferrite cores near the connector ends.

Certifications, Reports and Compatibility



Applications

- Extends your VGA monitor cable

Features

- Ideal for high resolution monitors (1920x1200 and above)
- Triple-coaxial + twisted-pair wire for crystal clear display
- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Ferrite core eliminates EMI interference
- Molded connector ends with strain relief

	Warranty	Lifetime
Hardware	Connector Plating	Nickel
Connector(s)	Connector A	1 - VGA (15 pin, High Density D-Sub) Male
	Connector B	1 - VGA (15 pin, High Density D-Sub) Female
Physical Characteristics	Cable Length	25 ft [7.6 m]
	Color	Black
	Product Weight	2.1 lb [0.9 kg]
	Wire Gauge	28 AWG
Packaging Information	Shipping (Package) Weight	2.1 lb [0.9 kg]
What's in the Box	Included in Package	1 - 25 FOOT COAXIAL CABLE 2 - Nuts

Product appearance and specifications are subject to change without notice.