



Ceramic Tower Heater



Model: DFH-TH-17-TO

- **3 comfort settings**
 - 900 W (Low)
 - 1,500 W (High)
 - Fan only mode
- **Adjustable thermostat**
- **Power indicator light**
- **Safety thermal protection**
- **Durable powder coated steel grill**
More heat resistant than plastic
- **Tip over safety switch**
The tip over switch is an added safety feature which will automatically disengage the heater should it get knocked over
- **Overheat protection device**
Instantly shuts off before becoming overheated
- **Oscillating**
Provides wider heat distribution
- **Large centrifugal blower**
Provides quiet, even heat
- **Assembled Dimensions**
8.78" w x 8.66" d x 31.12" h
- **Consumer Carton Dimensions**
9.76" w x 6.81" d x 26.57" h
- **Master Carton Dimensions - 4 Pcs**
20.28" w x 14.49" d x 27.95" h
- **Product Weight:** 7.50 lbs.
- **Loading Qty:** 1966



Failure to comply with the precautions and instructions provided with this heater can result in death, serious bodily injury and property loss or damage from hazards of fire, explosion, burn, asphyxiation, carbon monoxide poisoning and/or electrical shock. Manufactured and distributed by Twin-Star International, Inc. under license. duraflame™ and the duraflame flame logo are trademarks of duraflame, Inc. • ©2012 Twin-Star International, Inc. • Specifications are subject to change without notice