




REAR VIEW



SIDE VIEW



FRONT VIEW



NEMA L5-20P
(20 A, 1/N/PE, 100-120 V)

OUTPUT POWER

L5-20P

BANK	PHASE	RECEPTACLE TYPE (QUANTITY)	VOLTAGE (V)	MAX. CONTINUOUS AMPS (A)	
				PER RECEPTACLE	PER BANK
A	L1	18xNEMA 5-20	100-120	16	16

INPUT POWER

INPUT CORD	INPUT PLUG	WIRE COUNT	FREQUENCY (Hz)	VOLTAGE (V)	RATED AMPS (A)	MAX. CONT. AMPS (A)
10 ft / 3 m	L5-20P	1/N/PE	50/60	100-120	20	16

METERING PARAMETER	MEASUREMENT ACCURACY
VOLTAGE	±1 % + 0.1 VAC
CURRENT	±1.5 % + 0.01 A FROM 1 % TO 10 % OF UNIT RATING; ±1 % FROM >10 % TO 125 % OF UNIT RATING

RoHS COMPLIANT

AGENCY COMPLIANCE:


- UL certification: UL 60950-1 (2nd), CSA C22.2 No. 60950-1-07
- FCC certification
- CB certification: IEC 60950-1 (2nd)
- "-100" SUFFIX (PSE MODELS): INTERPRETATION OF DENAN TECHNICAL REQUIREMENTS MINISTERIAL ORDINANCE APPENDIX 12, J60950-1(H26), J55022(H22)

ENVIRONMENTAL RATING:

OPERATING TEMPERATURE: 5 °C - 60 °C (41 °F - 140 °F) NON-CONDENSING, NON-CORROSIVE, 10 % - 90 % RH
STORAGE TEMPERATURE: -20 °C - 85 °C (-4 °F - 185 °F)
MAX. OPERATING ALTITUDE: 2000 m

NOTES:

1. UNIT DIMENSIONS: 916.5 mm (36.1") H x 50 mm (2.0") D x 56 mm (2.2") W
2. UNIT WEIGHT: 2.3 kg / 5.0 lbs
3. SHIPPING DIMENSIONS: 1197 mm (47.1") H x 218 mm (8.6") D x 137 mm (5.4") W
4. SHIPPING WEIGHT: 4.3 kg / 9.5 lbs
5. (2) MOUNTING BUTTONS AND (2) MOUNTING BRACKETS SUPPLIED WITH EACH UNIT. EITHER OPTION CAN BE USED TO MOUNT THE PDU.

 Dimensions in mm				Allgemeintoleranzen General tolerances		Oberfläche Finish		Werkstoff / Material		Gewicht: Weight: -					
				-		-		-							
				Drawn	Date	Name		Bezeichnung / Description MPH2-NBV_L5-20P_18A Input and Branch Metered							
				Checked	13/01/16	Blass									
				Approved	13/01/16	Votýpka									
					-	-									
										Zeichnungs-Nr. / Drawing no.		Maßstab Scale 1:5			
B	17850	26/08/16	Racek							MPHB3303					
Rev.	Change	Date	Name							Verwendet in / Used in		-		Blatt/Sheet 1/1	