

Universal Reversible USB 2.0 Cable (Right / Left-Angle Reversible A to B M/M), 6 ft. (1.83 m)

MODEL NUMBER: UR022-006-RA



Reversible Right / Left Angle USB "A" connector plugs in any direction

Features

- 6ft, USB 2.0 Right / Left Angle A-Male to B-Male, with Universal / Reversible "A" connector
- USB 2.0 compliant, to 480Mbps transfer rates
- Backward compatible with previous USB generations
- Gold plated contacts and molded ends provide a lifetime of use
- 28AWG Data Pair, 24AWG Power pair

Specifications

OVERVIEW	
UPC Code	037332179470
Technology	USB 2.0 (High Speed); USB
PHYSICAL	
Color	Black
Cable Length (ft.)	6
Cable Length (m)	1.8
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50
Shipping Weight (kg)	0.06

Highlights

- 6-ft. (1.83 m), USB 2.0, Right / Left Angle A to B Peripheral device cable
- Universal, Reversible "A" connector allows plugging in any direction

System Requirements

- Any USB device requiring a USB cable
- USB2.0 performance only when used with USB2.0 device and USB2.0 controller

Package Includes

- Universal Reversible USB 2.0 Right / Left Angle A-Male to B-Male Device Cable - 6-ft. (1.83 m)



Shipping Weight (lbs.)	0.13
ENVIRONMENTAL	
Operating Temperature Range	-10/+75° C (14 to 167° F)
Storage Temperature Range	-20/+80° C (-4 to 176° F)
CONNECTIONS	
Side A - Connector 1	REVERSIBLE USB A (MALE)
Side B - Connector 1	USB B (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>