

AQUARIUS

WMAQC 641P UK

6kg Aquarius Washing Machine

Dimensions: H 850 x W 595 x D 540 (mm)
Colour: White+White



TECHNICAL SPECIFICATIONS

AQUALTIS



WMAQC 641P UK

White+White

Model

Colour

KEY INFORMATION

Max Wash Load – Cottons (Kg)	6.0
Max Spin Speed (rpm)	1400
User Interface	Led
Display includes "Time To End"	N
Super Silent	N
Water supply	Cold Fill Only
Door lock	Y
Motor	Collector
Balancing System	Y
Drum Capacity (L)	52
Weight (Kg)	65.8
Dimensions (mm) H x W x D / Minimum Installation Depth	850x595x540
Package Dimensions (mm) Height/Width/Depth	890x645x590
Built in or Freestanding	Freestanding

ENERGY / PERFORMANCE

Energy Efficiency Class	A+
Spin Efficiency Class	B
Energy Consumption (kWh) - 60C Cotton Cycle (Full Load)	1.05
Programme Time (mins) - 60C Cotton Cycle (Full Load)	195
Noise Emissions (dB) - 60C Cotton Cycle Wash Phase (Full Load)	58
Noise Emissions (dB) - 60C Cotton Cycle Spin Phase (Full Load)	80

WATER EXTRACTION EFFICIENCY (%)

Remaining Moisture - 60C Cotton Cycle (Full Load)	53
Annual Water Consumption based on 220 cycles (litres)	8643.0

WASH PROGRAMMES

Anti Stain Cycle	Y
Anti Allergy Cycle	Y
Woolmark Platinum Care	Y
Eco Cycles	N
Duvet Cycle	N
Silks	Y
Bed & Bath Cycle	Y
Shirts Cycle	N
Delicates Cycle	Y
Ultra Delicates Cycle	N
Colour Care Cycles (Whites, Blacks, Coloureds)	N
Steam Refresh Cycle	N
Auto Clean	Y

OPTIONS

Variable Temperature	N
Variable Spin	Y
Steam Hygiene	N
Eco Wash Function	N
Super Wash Function	Y
Anti Allergy Rinse	N
Extra Rinse	Y
Easy Iron	Y
Delay Timer	N
Pause / On-Off	Y
Selectable Child Lock	Y

