



Hi-Speed USB Active Extension Cable

Daisy-Chainable, A Male / A Female, 20 m (65 ft.)

Part No.: **150958**

Easily overcome distance limitations to connect USB devices.

Use the Manhattan Hi-Speed USB Active Cable to connect a computer USB port to a USB device almost anywhere in the room. Daisy-chain 2 cable extensions to provide a convenient, 40m (131-ft.) connection. Manhattan Hi-Speed USB Active Cable with built-in repeater is fully-compliant with USB 1.1 and Hi-Speed USB specifications to help devices operate at maximum performance. Plug-and-play capability, Windows/Macintosh versatility and no external power or driver requirements help provide greater flexibility in computer and peripheral placement and office layout.

Features:

- Extends and boosts the signal to any USB device — supports data transfer speeds up to 480 Mbps
- Built-in repeater helps maintain Hi-Speed USB signal quality, electrical and timing specifications
- Overcomes the 20m (65-ft.) USB distance limitation — ideal for connecting enclosures and other peripherals
- Daisy-chain two extensions for total distance of 40 m (131 ft.)
- Plug and play; Windows and Mac compatible; bus powered — requires no external power supply
- Lifetime Warranty

Specifications:

Standards and Certifications

- CE
- USB 2.0

Ports

- Standard-A male
- Standard-A female

General

- Throughput: 480 Mbps
- Bus powered
- Maximum length: 40 m (131 ft.)
- All USB-supported operating systems

Physical

- Length: 20 m (65 ft.)
- Weight: 587 g (21 oz.)

Package Contents

- Hi-Speed USB Active Cable



