

# HL-1212w

Compact Laser Printer with Wireless Networking



## Top Features:

### Fast Printing

- Help increase your productivity with a black print speed up to 21ppm

### Built-in Wireless Networking

- Easy to set up and share on your wireless network or connect locally via Hi-Speed USB 2.0 interface

### Mobile Device Printing

- Wireless printing from your mobile device via : Brother iPrint&Scan (free downloadable app)

### Stylish and Compact

- Fits virtually anywhere

### High-Quality Output

- Print professional reports, spreadsheets and documents at up to 2400 x 600dpi resolution

### Convenient Paper Handling

- Up to 150 sheet capacity paper tray holds up to legal sized paper

### Toner Save Mode

- Help save money by using Toner Save mode for your less critical business documents

### Outstanding Support

- We are Canadians serving Canadians. We provide machine-lifetime support including extensive online technical support options such as videos, TWITTER, FACEBOOK and more. We also provide a 1-year limited warranty. We're at your side every step of the way.

# HL-1212w

Compact Laser Printer with Wireless Networking

## Specifications:

<b>Print Technology</b>	Electrophotographic Laser
<b>Paper Size</b>	Up to 8.5" x 14" (legal)
<b>Print Speed (maximum)</b>	Up to 21ppm (letter)
<b>Time to First Page<sup>▲</sup></b>	Less than 10 seconds
<b>Print Resolution (maximum)</b>	Up to 2400 x 600 dpi
<b>Processor</b>	200 MHz
<b>Paper Input Capacity (maximum)<sup>∞</sup></b>	150-sheet capacity paper tray
<b>Media Types</b>	Plain paper, recycled paper
<b>Media Weights</b>	17 to 28 lbs.
<b>Print Driver Settings<sup>1</sup></b>	N-in-1 Printing, Watermark, Poster Printing
<b>Memory (std. / max.)</b>	32MB/32MB
<b>Standard Interfaces</b>	Wireless 802.11b/g/n, Hi-Speed USB 2.0
<b>Operating Systems Compatibility</b>	Windows <sup>®</sup> : XP Home / XP Professional / XP Professional x64 Edition / Windows Vista <sup>®</sup> / Windows <sup>®</sup> 7, 8, 8.1 / Windows Server <sup>®</sup> 2003 (32/64 bit) / 2008 / 2008 R2 / 2012 / 2012 R2 Mac <sup>®</sup> OS X <sup>®</sup> v10.7.5, 10.8.x, 10.9.x Linux
<b>Maximum Monthly Duty Cycle<sup>°</sup></b>	Up to 10,000 pages
<b>Recommended Monthly Volume<sup>*</sup></b>	Up to 250 to 1,800 pages
<b>Mobile Device Compatibility<sup>*</sup></b>	Brother iPrint&Scan
<b>Warranty</b>	1-year limited warranty
<b>ENERGY STAR<sup>®</sup> QUALIFIED</b>	Yes

## Supplies & Accessories\*:

TN-1030	Standard Yield Toner (approx. 1,000 pages) <sup>▼</sup>
DR-1030	Drum Unit (approx. 10,000 pages) <sup>▲</sup>

## Setup Information:

<b>UPC Code</b>	012502639824
<b>Unit Dimensions</b>	340 W x 238 D x 189 H mm
<b>Unit Weight</b>	4.6 Kg
<b>Carton Dimensions</b>	415 W x 303 D x 324 H mm
<b>Carton Weight</b>	5.5 Kg

## Carton Contents:

Brother HL-1212w
Starter Black Toner Cartridge (700 pages) <sup>▼</sup>
DR-1030 Drum Unit (10,000 pgs) <sup>▲</sup>
Quick Setup Guide
Installation and Documentation CD-ROM
AC Power Cord



\* Additional purchase required.

<sup>∞</sup> Maximum capacity based on using 20 lb. paper.

<sup>1</sup> Windows<sup>®</sup> only.

<sup>°</sup> Maximum number of printed pages per month can be used to compare designed durability between like Brother products. For maximum printer life, it is best to choose a printer with a duty cycle that far exceeds your print requirements.

<sup>\*</sup> Requires connection to a wireless network. See [www.brother.ca](http://www.brother.ca) for details, availability, and mobile device compatibility.

<sup>\*</sup> The recommended range of monthly printed pages to achieve the best possible performance and printer life. Printers are intended to handle occasional usage beyond this range with little or no effect. Consistently printing above the recommended print volume, however, may adversely affect the print quality or life of the machine. It is always best to choose a printer with an appropriate recommended print volume to allow for any anticipated increase in printing needs.

<sup>▼</sup> Approximate toner cartridge yield in accordance with ISO/IEC 19752 (letter/A4).

<sup>▲</sup> Drum yield is approx., and may vary by type of use.

<sup>▲</sup> From ready mode and standard tray.