

A high-angle photograph of a Kodak Scan Station 730EX. The device is a dark grey, flatbed-style scanner. On its top surface, a white control panel features several large, colorful touch-screen buttons: a green button for 'Claims Processing', a red button for 'Human Resources', a purple button for 'Scan to SFTP', an orange button for 'Scan to SharePoint', a pink button for 'Finance', and a blue button for 'Scan to email'. In the center of the panel are two small thumbnail images of scanned documents. To the right of the buttons is a power button and a status indicator showing 'Job Queue Idle...'. The scanner is shown with a document being scanned, and another document is visible in the output tray at the bottom. The background is white with a yellow diagonal line graphic.

Kodak

Scan Station 730EX

It's here to streamline
your workflow.

And it means business.

It's not what you put into your scanner. It's what your scanner puts into your business.



Scan Station 730EX

Stop wrestling with your data and start profiting from it with the new Kodak Scan Station 730EX.

Powerful integration capabilities enable customization through independent developers, so you can adapt processes to solve the unique challenges you face. And with simple network setup, robust remote management, and a built-in modem, you'll turn data into decisions quickly and seamlessly. With the **Kodak** Scan Station 730EX, your information is open for business.

More than Scanning, Doing


The Scan Station 730EX turns documents into actionable information. Powerful integration capabilities let application developers and independent software vendors create customer-specific apps to enable your workflow. Users can access integrated applications to easily look up projects, confirm deliveries, provide feedback, and check the status of projects in the system.

Simple and Robust Remote Management

If you have many networked Scan Stations throughout your business, a system administrator can efficiently configure and maintain these devices on your network from one place.

User-Friendly Experience

Combine our bright, easy-to-navigate touchscreen, intuitive user controls, and administrator controlled functionality for a user experience that promises fewer mistakes and faster proficiency without the distraction of a separate PC. And Scan Station's quiet operation makes it office friendly.



Intuitive touch-screen makes it easy to learn

Large
touchscreen
display

Information Management Made Easy

With increased ease of operation and improved file naming and security features, scanned content can be classified, organized, and searched by ad hoc users with minimal training while maintaining the degree of accessibility and security you've established.

Productivity. Assured.

Only Kodak Alaris offers essential services to ensure the optimal operation of your scanning solution at time of installation and beyond.

Kodak Scan Station 730EX services, such as Startup Assistance and Network Scanner Training, put Kodak Alaris knowledge to work for you. Plus, access to our Help Desk and product experts, along with the latest product improvements, will allow the **Kodak** Scan Station 730EX to satisfy your evolving business process needs for years to come.

CHALLENGE IN SOLUTION OUT

STREAMLINED PROCESSES

IMPROVED COMMUNICATION

INCREASED PRODUCTIVITY

Improved
paper handling

Internal
modem

Robust
build quality

➤ **IN THE INSURANCE BUSINESS**, personal relationships are everything. So when sales representatives have to return to the office one day each week to process new applications and check the status of older ones, business suffers. The **Kodak** Scan Station helped one of our insurance customers keep their sales reps on the road five days a week, doing the work that matters. Their reps can now securely transfer documents through a special protocol to their workflow system and quickly understand where applications are in the process. At the same time, management has been able to remove the distraction of PCs, which were being used for unproductive tasks. It's just one example of how the **Kodak** Scan Station turns inefficiency into opportunity.

➤ **IN BANKING**, branch offices are on the front lines of customer satisfaction. And keeping clients satisfied requires fast, accurate information management. The **Kodak** Scan Station helped one bank enhance customer relations by allowing tellers to quickly capture documents and access core application functions on the touchscreen — without leaving the customer. Of course, the Scan Station also helped the bank meet firm requirements for user interface and document transfer security. And the integration capabilities allowed the bank to create and distribute a simple application to use on the Scan Station. Simplify your processes quickly and securely with the **Kodak** Scan Station.

Kodak Scan Station 730EX Specifications

Connectivity	10/100/1000 Base T and no host PC required; built-in 56K fax modem
Output Methods	Scan to network share, scan to print, scan to e-mail, scan to hardware fax, scan to portable USB drive, scan to Kofax Front Office Server, FTP, sFTP, FTPS (anonymous, authenticated, with proxy support), and scan to Microsoft SharePoint
Network Protocols	TCP/IP, SMB, authenticated SMTP (login, plain text, CRAM, NTLM), DHCP (or static IP), Network domain authentication
Security Features	PDF private key encryption, optional password access, option to enable/disable the ability to scan to portable USB drives, secure login via LDAP, activity logging by Login ID, IP port blocking
Remote Administration (for system administrators only)	Secure login with a customizable password, ability to create and manage lists of Scan Station 730EX devices, group and easily classify managed devices, update the configuration and/or embedded software of one, some or all managed devices, view the status of managed devices, remotely access and manage the logs of a single managed device, restart or power off a single managed device
File Format Outputs	Single and multipage TIFF, JPEG, PDF, text searchable PDF, PDF/A, Microsoft Word , Microsoft Excel , RTF, encrypted PDF, optional JPEG compressed TIFF, WAV audio files
Control Panel	9.7 in. (24.6 cm) 1024 x 768 Touchscreen LCD
Audio	Built-in microphone and speaker to record and play back Voice Attachment messages
Scanning Technology	Duplex scanning with dual color quadlinear CCD, 600 dpi optical resolution, capture bit depth is 30 bits (10 x 3), color output bit depth is 24 bits (8 x 3), grayscale output bit depth is 256 levels (8-bit)
Output Resolution	100, 150, 200, 240, 300, 400, 600 dpi
Imaging Features	Perfect Page Scanning, deskew, autocrop, content-based blank page removal, automatic orientation, hole fill, edge fill, streak filter, color dropout
Throughput Speeds (portrait, letter size, black-and-white/grayscale/color)	Up to 70 ppm/140 ipm at 200 dpi
Multi Feed Detection	With ultrasonic technology
Feeder	Up to 75 sheets of 20 lb. (80 g/m ²) paper
Maximum Document Size	215 mm x 863 mm (8.5 in. x 34 in.) – may be restricted at certain resolutions
Minimum Document Size	50 mm x 63.5 mm (2 in. x 2.5 in.); Multiple-sheet feeding: 75 mm x 125 mm (3 in. x 5 in.)
Paper Thickness and Weight	413 g/m ² (110 lb.) paper and ID cards up to 1.25 mm (0.05 in.) thick
Recommended Daily Volume	Up to 6,000 pages per day
Approvals and Product Certifications	AS/NZS CISPR 22:2009 +A1:2010 (Class B RCM mark), CAN/CSA-C22.2 No 60950-1-07 +A1:2011 (TUV C mark), Canada CSA-CISPR 22-10 / ICES-003 Issue 5 (Class B), China GB4943.1:2011; GB9254:2008 Class B (CCC S&E mark), EN55022:2010 ITE Emissions (Class B), EN55024:2010 ITE Immunity (CE mark), EN60950-1:2006 +A1,+A11,+A12 (TUV GS mark), IEC60950-1:2005 +A1, Taiwan CNS 13438:2006 (Class B), CNS 14336-1 (BSMI mark), UL 60950-1:2007 R12.11 (TUV US mark), CFR 47 Part 15 (FCC Class B), Argentina S-mark
Dimensions	Weight: 10.5 kg (23 lbs.); Depth 38.2 cm (15 in.); Width: 35.6 cm (14.0 in.); Height: 20.6 cm (8.1 in.)
What's in the box	Kodak Scan Station 730EX, power cords, User's Guide, Setup & Documentation CD-ROMs, Installation Guide, scanner administration software
Recommended PC Configuration for scanner administration software	Intel Core2 duo 6600 @ 2.4 GHz Duo Processor or equivalent, 4 GB RAM, USB 2.0, running Windows XP (SP3), Windows Vista (SP2), Windows 7 (SP1), Windows 8 (32-bit and 64-bit), Windows 8.1 (32-bit and 64-bit)
Accessories Available	Portable USB drives, Kodak Scan Station Keyboard and Stand Accessory, Kodak Legal Size Flatbed Accessory, Kodak A3 Size Flatbed Accessory
Consumables Available	Feed modules, roller cleaning pads, Staticide Wipes
Warranty (US and Canada)	90-day warranty
Environmental Factors	Operating temperature: 10-35° C (50-95° F); Operating humidity: 10% to 85% RH, Altitude <2000M or 6562 feet
Illumination	Dual indirect LED
Power Consumption	Off mode: <0.5 Watts; Energy Star /Sleep mode: ≤4 Watts; Operating mode: <50 Watts

Kodak Alaris' Document Imaging solutions enable customers to capture and consolidate data from digital and paper sources, understand and extract valuable insight from the contents, and deliver the right information to the right people at the right time. Our offerings include award-winning scanners, capture and information management software, an expanding range of professional services and industry-leading service and support. With customers ranging from small offices to global operations, Kodak Alaris delivers superior systems and solutions to automate business processes, enhance customer interactions and enable better business decisions.

To learn more:

www.kodakalaris.com/go/ScanStation730EX

Kodak Alaris Inc., 2400 Mt. Read Blvd., Rochester, NY 14615 1-800-944-6171

Kodak Alaris Operations Canada Inc., Mississauga, Ontario, Canada L5R 1B9 1-800-944-6171

© 2015 Kodak Alaris Inc. Kodak Alaris is the Company's trade name for its global business. The Kodak trademark and trade dress are used under license from Eastman Kodak Company. Specifications are subject to change without notice.

1/15



Kodak
Service & Support
for Document Imaging Solutions

Kodak alaris