



PT1545P Touch Monitor

15" Touch Screen Monitor

For image-conscious retail, hospitality or healthcare applications, the Planar® PT1545P 15" touch screen monitor is optimized with multi-touch interactivity for space-constrained settings. With its ultra-thin profile enclosure and its sleek edge-to-edge glass surface, the Planar PT1545P provides the ultimate interactive experience.



SPECIFICATION	DETAIL
Product Name	PT1545P
Planar Part Number	997-7413-00
Viewable Size	15" diagonal (11.97" horizontal x 8.98" vertical)
Touchscreen Type	Projected Capacitive
Number of Touch Points	10
Touchscreen Interface	USB
Transmissivity	N/A
Contrast Ratio (typ)	500:1
Viewing Angle (typ)	140° Horizontal and 125° Vertical
Response Time (typ)	8 ms
Brightness (w/touchscreen)	225 cd/m ²
Brightness (w/o touchscreen)	250 cd/m ²
Brightness (Typical)	N/A
Display Type	Edge-Lit LED LCD
Display Resolution	1024 x 768

Aspect Ratio	4:3
Tilt Range	-5° to +90°
Palette	16.7 million colors
Pixel Pitch	0.297 mm
Refresh Rate	56 to 75 Hz
Panel Depth	N/A
Dimensions (W x H x D)	13.8" x 12.1" x 8.0" (350.8 mm x 306.5 mm x 202.0 mm)
Dimensions without Stand	13.8" x 10.9" x 2.5" (350.8 mm x 275.9 mm x 62.5 mm)
Display Weight	9.9 lbs. (4.5 kg)
Display Weight (w/o stand)	6.4 lbs (2.9 kg)
Shipping weight	14.3 lbs. (6.5 kg)
Video Inputs	Analog
Audio Output	2 speakers, 1W/ch
Compatibility	Windows® 8, 7, Vista, XP, 2000, ME, 98, NT 4.0, CE, XP Embedded, Apple® Mac OS, Linux, HID Compliant - no drivers needed for basic touchscreen operation
External Connections	D-sub 15-pin, Type B socket USB, audio-in, AC power-in
Power Supply	Internal
Power Requirements	100-240 VAC, 50/60Hz
Power Consumption (max)	25W (<3W sleep, <1W off)
Operating Temperature	0° to +40° C
VESA Compatible/Location	Built-in 100mm VESA, monitor back
Service and Support	3-Year Customer First™ Warranty featuring FREE 2-Day Advance Replacement (US only)
Options / Features	Multi-language On screen display (OSD), Kensington® Security Slot
Product Approvals	UL/c-UL, FCC-Class B, CE, RoHS II
CI-Black-PN	997-7413-00
CI-White-PN	N/A
In the Box	PT1545P 15" Touchscreen LCD Monitor, Power Cord, VGA Cable, USB Cable (A to B), Audio-in Cable, User's Guide, Quick Start Guide
UPC	8 10689 00022 8

For more information, please visit www.planar.com

Specifications are subject to change without notice.

Specification Report Date: 1/2/2014

© Copyright 2014 Planar Systems, Inc. All rights reserved