



PLATINUM DIGITAL HD **3MP**



Professional HD Security System

8 Channel Network Video Recorder & 8 Cameras

8CH

8 CHANNEL VIEWING

3MP

SUPER HD



AUDIO MONITORING

PoE

POWER OVER ETHERNET

2TB

LARGE HDD



DAY/NIGHT VISION



WEATHER PROOF

Be protected & see every detail in HD

- Swann's network video recording security system with beyond 1080p high definition live viewing & playback in real-time (30 fps per channel)
- State-of-the-art digital imaging technology for 9 x the picture sharpness of traditional security systems including analog D1
- Includes 8 x security cameras capable of generating super high definition 3 megapixels (50% more than 1080p) video with IR cut filters for powerful night vision to 100ft / 30m & a weather-resistant rating of IP66 for indoor & outdoor use
- You can also hear what's happening as each camera has a built-in microphone
- Set & forget by recording continuously from 8 channels for 24 days+ onto a 2TB hard drive (expandable to 6TB[^]) or even longer with motion detection
- Save time & have peace of mind by easily locating incident video, then transfer to external storage via USB or network
- Security in the palm of your hand with live viewing on your Smartphone or tablet including iOS (iPhone, iPad) & Android devices using the free 'SwannView Link' app
- View live in HD on your HDTV via HDMI or VGA connection to your LCD screen
- Professional surveillance system gives you peace of mind by being able to see the detail you need from longer distances including license plates, faces, clothing colors & more, all in super HD

SWNVK-873008

For more information on this product visit www.swann.com

Professional HD Security System

NVR8-7300™ 8 Channel 3MP Network Video Recorder & 8 x NHD-815™ 3MP Cameras

What's in the box

All installation accessories included

- NVR8-7300™ 8 Channel NVR
- 2TB Hard Drive (installed)
- NHD-815™ 3MP Cameras x 8
- Cat5e Ethernet Cable x 9 (60ft / 18m x 8, 3ft / 1m x 1)
- HDMI Cable
- Mouse
- Power Adapter
- Mounting Screws & Plugs
- Operating Instructions
- Theft Deterrent Stickers



Specifications

NVR8-7300™ DIGITAL VIDEO RECORDER

Video

Inputs 8 Channels
Outputs VGA, HDMI
Display Resolution Up to 1080p

Audio

Input 8, via Ethernet Integrated with Cameras
Output 1 x RCA

Recording

Compression Format H.264
Recording Mode Manual / Motion / Schedule
Recording Resolution 3MP (2048 x 1536 [4:3], 2304 x 1296 [16:9])
Playback Speed Frame Rate up to Real-Time 30fps / 25fps

Hard Drive

HDD Included 2TB
HDD Capacity Up to 6TB - Internal 1 x 3TB; External 1 x 3TB (via eSATA)

Connection

Network Connection SwannLink Peer-to-Peer
Network Interface RJ45 x 1
USB Interface USB 2.0 x 2
eSATA Port x 1

General

Operating Power DC 48V
Dimensions 10" x 9.0" x 2.0" / 255 x 230 x 51mm

Software

Computer Operating System Windows, Mac OS
Internet Viewing SwannView Link
Handheld Device Supported iOS, Android, 3G/4G Smartphones & Tablets

NHD-815™ CAMERA

Video

Video Quality 3MP (2048 x 1536 [4:3], 2304 x 1296 [16:9])
Backlight Compensation Yes
Wide Dynamic Range Yes
Viewing Angle 80°

Audio

Microphone Yes
Audio Range Up to 16ft / 5m

Night Vision

Night Vision Distance Up to 100ft / 30m
IR Cut Filter Yes
General Indoor / Outdoor, IP66 rated
Operating Power DC 12V
Operating Temperature -4°F ~ 122°F / -20°C ~ 50°C
Body Construction Aluminum
Dimensions incl. stand 2.6" x 7.4" x 2.6" / 66 x 188 x 66mm
Weight (incl. stand) 0.961lbs / 436g

Code

Swann Code SWNVK-873008
UPC 840236106141

- + 24 days recording achieved using lower settings, default settings give 5 days recording
- * Monitor, tablet and mobile phones not included. Not all handsets supported
- ^ Depends on camera. Note: Trademarks are properties of their respective owners

Now with
SwannLink™

LINK & SEE YOUR WORLD IN MINUTES!



Free Download
SwannView Link App



COMPATIBLE WITH



Our Promise

Swann stands by its promise of Lifetime Support to make advanced security easy to use, install and maintain. Everything is in the pack but if you need it Swann's help desk is available **24 hours a day, 7 days a week** for the life of the product.

Installation is easy

Do-it-Yourself

Installing this Swann product is simple. For instructions, tips and videos see the operating instructions in this pack or visit www.swann.com

Professional Installation

Need extra help?

We have an installer in your region! For more visit www.swann.com

For more information on this product visit
www.swann.com