



A⁺

Siemens
KG34NVL24G
Free-standing fridge-freezer

Predecessor:

Successor:

EAN code:
4242003717271
sales programme:

iQ300
Fridge freezer
KG34NVL24G
NoFrost

Performance and Consumption

- Energy efficiency class: A⁺
- Annual energy consumption 293 kWh (per year).
- Total net capacity: 277 litres
- Net fridge capacity: 184 litres
- Net freezer capacity: 93 litres
- Noise level dB(A) re 1 pW: 42

Design features

- Stainless steel look doors and chrome inox metallic side panels
- high door design, softline curved door design
- Plastic lacquered vertical door handle
- Right hinged door, reversible
- Electronic control (LED chain)
- Removable magnetic door seals - easy to clean
- Twin evaporators allows independent temperature control and ensures there is no transference of humidity between the fridge and freezer cavity.

Food freshness system

- multiAirflow cooling - improves circulation of air around the fridge
- 1 vegetable crisper box with integrated humidity control with rippled base for improved air circulation

Key features - Fridge section

- Interior design with metal applications
- Bottle rack
- Bright interior LED fridge light
- 1 vegetable crisper box with integrated humidity control
- 3 removable safety glass shelves of which 1 are easy pull out
- 1 large door shelf, 2 small door shelf
- Automatic defrost in fridge section

Key features - Freezer section

- NoFrost, never have to defrost ever again
- 4 star rating
- 3 transparent freezer drawers, 1 big box
- VarioFreezing - adaptable storage for more flexibility
- Freezing capacity in 24 hours: 10 kg
- Maximum freezer storage time in power failure: 14 hours

Functions

- superFreeze function with automatic deactivation
- LED temperature display
- Removable magnetic door seals - easy to clean

Dimension and installation

- Climate class SN-T (suitable for ambient temperatures between 10 to 43°C)

Included accessories

- 1 x egg tray, 1 x ice cube tray

Technical Data

Characteristics

Built-in / Free-standing : Free-standing
Number of compressors : 1
Number of independent cooling systems : 2
Width of the product (mm) : 600
Height (mm) : 1850
Depth of the product : 650
Net weight (kg) : 69.0
Door panel options : Not possible
Door hinge : Right reversible
Number of Adjustable Shelves in fridge compartment (Stck) : 1
Shelves for Bottles : Yes
Frost free system : Full
Interior ventilator : No
Reversible Door Hinge : Yes
Length electrical supply cord (m) : 240.00
Noise level (dB(A) re 1 pW) : 42
Multi-Flow Air Tower : Yes
Fast cooling switch : No
Fast freezing switch : Yes
Number of Door Bins - Refrigerator : 2
Gallon Storage : Yes
Number of Gallon storage : 1
Motorized Shelf : No
Material of the shelves : Glass
Door opened indicator freezer : No
Automatic motor-driven ice-maker : No

Consumption and connection features

Connection Rating (W) : 120
Current (A) : 10
Voltage (V) : 220-230
Frequency (Hz) : 50
Storage Period in Event of Power Failure (h) : 14
Approval certificates : CE, VDE
Main colour of product : Inox-look
Door panel options : Not possible
Noise level (dB(A) re 1 pW) : 42
Energy Star Qualified : No
Approval certificates : CE, VDE
Plug type : GB plug
Dimensions of the packed product (in) : 75.39 x 25.98 x 29.13
Net weight (lbs) : 153
Gross weight (lbs) : 166

Alternative colors available