



ClearView

A Clear Choice

600TVL IR 0 Lux 2.8~12mm Outdoor Vandalproof / 100ft IR Range TD-88

OVERVIEW

- 1/3" SONY Super HAD CCD
- 600 TV Lines
- 2.8mm-12mm Vari-Focal Lens
- 0 Lux (IR on)
- Vandal Proof
- Flat front glass design
- Up to 100 Feet IR Coverage



600
TVL

2.8 - 12
mm Lens

0 Lux
IR On

100FT
IR Range

12VDC

Outdoor
Housing

Camera Features

Image Sensor: 1/3" Super Sensitive CCD

Resolution: 600 TV Lines

Effective Pixel: NTSC: 768(H)x494(V)

Minimum Illumination: 0 Lux (IR on)

S/N Ratio: > 50dB

Signal Format: NTSC / PAL

Lens: 4~9mm Vari-Focal

Gain Control: AUTO

Auto Shutter (AES): NTSC/EIA: 1/50~ 1/12,000 sec.

Gamma Correction: 0.45

White Balance: Auto

IR Range: 100ft (30M)

Video Output: Composite Output 1.0V p-p at 75
ohm

Power Supply: 12V DC

Power Consumption: 350mA

Working Temperature: 12°F ~ 122°F

Working Humidity: 10% - 90%

Barometric Pressure: 86kpa - 106kpa

Dimensions: 4.72"(W) 3.14"(H) 4.72"(D)

TD-88

IR Dome Camera



ClearView

A Clear Choice

TD-88 CAMERA SPECIFICATIONS

Image Sensor	1/3" SONY Super HAD CCD
Resolution	600 TV Lines
Effective Pixel	NTSC: 768(H)x494(V)
Minimum Illumination	0 Lux (IR on)
S/N Ratio	> 50dB
Signal Format	NTSC / PAL
Lens	2.8 ~ 12mm Vari-Focal
Gain Control	AUTO
Auto Shutter (AES)	NTSC/EIA: 1/50~ 1/12,000 sec.
Gamma Correction	0.45
White Balance	Auto
IR Range	100ft (30M)
Video Output	Composite Output 1.0V p-p at 75 ohm
Power Supply	12V DC
Power Consumption	350mA
Working Temperature	12°F ~ 122°F (-10°C ~ +50°C)
Working Humidity	10% - 90%
Barometric Pressure	86kpa - 106kpa
Dimensions	4.72"(W) 3.14"(H) 4.72"(D)
Weight	2.2lb or 1kg or 35.27oz

TD-88 Dimensions

