

MR16 GU5.3 12V LED ENERGY STAR, 3000K. 500 lumens, 50W Halogen Replacement. Dimmable

- ENERGY STAR qualified lamp
- Reduces energy consumption by over 80% when compared to traditional halogen MR16 lamps
- 30,000 hour* lifetime reduces maintenance costs
- 30-degree beam angle provides uniform illumination
- Warm color temperature of 3000K satisfy most commercial, hospitality and residential retrofit applications
- Cool beam protects illuminated objects from radiated heat.
- Environmentally-friendly product has no mercury or other hazardous materials and is RoHS compliant and UL listed.
- 3-year limited warranty

*lifetime statement on packaging may state 25,000hrs (directional lamp) or 15,000hrs (decorative lamp) based on Energy Star life testing requirements.



Specifications

Lamp Type	MR16 (GU5.3) 3000K ENERGY STAR 500 lm
Model	M16ES-L500-C30-B30
Wattage	7W
Lumen Output	500 lm
Efficacy	71 lm/W
Color Temperature	3000K
CRI	80
Beam Angle	30°
Dimmable	Yes
Voltage	12V
Operating Temperature	-20°C to 40°C
Socket	GU5.3
Weight	1.9 oz
Design life	30,000* Hrs.
CBCP	1200
Part Number	97943

