

# Surgeon Console

**Nightingale**



# Surgeon Console

## Specialty Task Chair

The Surgeon Console chair was engineered and designed to provide individual comfort and support for prolonged periods of time through its unique features.

The patented unique self-adjusting back and armrest support offers a level of ergonomic support and comfort that the user of this specialized chair will appreciate.

*Available in two models: Task and drafting stool.*

*Options include sit to lock casters, stand to lock casters and California Fire Code #133.*



1864 Model

# Surgeon Console Features

## Specialty Task Chair

Integrated back and arm feature a unique and patented torsion spring system that adjusts to each individual user for ergonomic lumbar support and comfort.

High density and high resiliency molded foam for comfort and durability. ENERSORB™ seat foam to reduce sitting fatigue by reducing pressure points and increasing blood circulation.

Back is standard with built-in ratchet system for back height adjustment. Swivel mechanism with free float or variable back angle adjustment, pneumatic height adjustment, seat slide adjustment.


2" Black, dual wheel, non-marking, hooded polyurethane soft wheel casters for hard floor surfaces.

5 prong, polished aluminum base with clear lacquer finish to maintain bright appearance.

California Fire Code #117 and ANSI/BIFMA approved.



1864DS Model



SEAT SLIDER



ENERSORB™ FOAM

# Surgeon Console Dimensions



Model:	1864	1864DS
OVERALL		
width	25"	25"
depth	25"-27"	25"-27"
height	36"-43"	40.5"-48"
Seat Height:	17"-22.5"	22.5"-30"
Weight:	44lbs	49lbs
Volume:	14 cu ft	14 cu ft
Seat Depth:	16.5"-18.5"	16.5"-18.5"
Seat Width:	17.5"	17.5"
Back Height:	16.5"-19.5"	16.5"-19.5"
Back Width:	24.5"	24.5"
Base Diameter:	25"	25"



1864 Model