

HSM® SECURIO

P36 L6 Professional shredder

Large volume, High Performance



EPL Listed*



- Uses Energy Management Control System (EMCS) to deal with energy in a sensible manner by reducing energy consumption up to 90%
- Automatically switches to energy-saving mode in 2 minutes after last use; switches off entirely if not used for 4 hours; temporary mode for small shredding jobs; and permanent mode for large shredding jobs
- Multifunctional control key with reversing function and shred bin level indicator
- Removable waste container
- Integrated auto oiler
- Cutting rollers are V-TEK by HSM with specially hardened steel rollers. This optimum design of all cutting unit components saves valuable energy.
- Continuous motor operation
- Equipped with Anti-Jam technology to easily and quickly reverse out paper in the event the machine is overloaded
- Includes a removable bag frame
- Uses a 58 gallon capacity shred bag; Part #HSM2117



HSM part#	HSM1854
Cutting type	Cross cut
Cutting size	1/32" x 3/16"
Security level DIN 32757-1	6
Security level DIN 66399	P-7 / F-3
Cutting capacity per run in sheets	12 - 14^
Cutting speed	18 ft / min
Throat opening	13"
Motor at max. no. of sheets	1600W
Motor power (horsepower)	2.15
Voltage	115 V / 60Hz
Dimensions (H x W x D)	36.9" x 22.8" x 21.7"
Weight	150 lbs
Shred-bin volume	38.3 gallons
Cutting capabilities	

All technical specifications are approximate values. Technical and design modifications reserved.

*Meets DOD and NSA/CSS 02-01 mandatory security requirements.

[^]Sheet capacity will vary depending on paper size, weight, quality, and proper power supply.

HSM of America, LLC
419 Boot Road
Downington, PA 19335
www.hsmofamerica.com
Customer Service / 800.613.2110

Great Products, Great People.

HSM®