

## CHERRY MX-Board 3.0 "BROWN SWITCH"



*Models may vary from image shown*

### Extremely robust professional keyboard for fast and precise input

The CHERRY MX-Board 3.0 captivates with its world-exclusive use of Gold Crosspoint contacts in the MX modules, ensuring perfect and extremely fast keystrokes. This professional, maximum-precision keyboard is even sturdier and more robust than its predecessor, making it the perfect partner for every type of exacting input imaginable.

### Key Features

- Original CHERRY MX module: Quality "Made in Germany" proven effective billions of times
- MX module with Gold Crosspoint contacts for reliable contact capability and exemplary responsiveness
- N-key rollover: Simultaneous operations of up to 14 keys without any key ghosting effects
- Available in four different key confirmation types
- Professional quality with a perfect key stroke: 50 million operations for each key
- The integrated metal plate and extensive anti-slip protection ensure it remains robust
- Detachable cable
- Win-Key lock: Windows buttons can be disabled to prevent inadvertent operation

### Technical Data:

#### Housing color:

- Black

#### Weight (product):

Approx 830 g  
1.83 lbs

#### Total weight (with packaging):

- 1215g
- 2.67 lbs

#### Cable Length:

Approx. 1.80 m  
Approx. 5.91 ft.

#### Storage Temperature:

- -20°C to 60°C
- -4°F to 140°F

#### Operating Temperature:

- -0°C to 50°C
- 32°F to 122°F

#### Interface:

- USB

#### Connection sockets:

- 1 USB port (type mini B 5-pin)

#### Product Approvals:

cURus



c-tick



VCCI



CE



FCC



BSMI



KC



#### System Requirements:

- USB connection

#### Delivery Volume:

- CHERRY MX-Board 3.0
- Operating instructions in hard copy
- Detachable cable (USB A plug / USB mini B plug)
- 2 non-slip surfaces
- 2 rubber caps for adjustable feet

#### Dimensions (product):

Approx. 446 x 158 x 28 mm  
Approx. 17.56" x 6.22" x 1.10" inches

#### Dimensions (packaging):

Approx. 468 x 202 x 35 mm  
Approx. 18.43" x 7.95" x 1.38"

#### Reliability:

- MTBF (90) > 80,000 hours

#### Keyboard:

- Key technology: MX
- Service Life, standard key: > 50 million key operations
- Operation characteristics: Product dependent, see table "Models"
- Inscription Technology: Laser
- Inscription layout: Standard
- Number of Keys: 104
- Number of additional keys: 4

#### Packing Unit:

- Number of products in the master package: 8
- Number of master packages per pallet: 20

#### Warranty





- 2 years

Errors, technical changes and delivery possibilities excepted. Technical information refers only to the specifications of the products. Features may differ from the information provided.

Product name	Order Number	EAN Code	Operation characteristics
CHERRY MX-Board 3.0	G80-3850LXBEU-2	4025112080500	BROWN SWITCH Pressure point
CHERRY MX-Board 3.0	G80-3850LSBEU-2	4025112080494	BLUE SWITCH Click Pressure point
CHERRY MX-Board 3.0	G80-3850LUBEU-2	4025112080487	BLACK SWITCH Linear (60 cN)
CHERRY MX-Board 3.0	G80-3850LYBEU-2	4025112080135	RED SWITCH Linear (45 cN)

**<sup>1</sup>Operation characteristics:**

- BLACK SWITCH Linear (60 cN)


**• BLUE SWITCH Click pressure point**

**• BROWN SWITCH Pressure point**

**• RED SWITCH Linear (45 cN)**


ZF Electronics Corporation

11200 88th Avenue

Pleasant Prairie, WI 53158

USA

Phone: 262.942.6500

 Internet: [www.cherrycorp.com](http://www.cherrycorp.com)

Sales: 262.942.6562

 E-Mail: [CEP\\_sales@zf.com](mailto:CEP_sales@zf.com)

Fax: 262.942.6566

The manufacturer accepts no liability for errors or non-availability, and reserves the right to change specifications without prior notice. Technical data relates to product specifications only. Features may differ from those described. Only drawings combined with product specifications shall be deemed binding.