



Mobile



Education


 Speech
Recognition

 Video
Conferencing

Features:

- Noise cancelling microphone**
With internal windscreens to minimize breath popping
- Heavy duty rigid-flex microphone boom**
Allows for perfect placement of microphone
- 40mm speakers with deep base sound**
For crystal clear audio
- Extra thick leatherette ear cushions**
Reduce background noises and are easy to wipe clean
- Adjustable head band**
Allows for a comfortable fit even on smaller heads
- Single 3.5mm Plug for Mobile Devices**
For use with Tablets, Mobile Phones and Laptops with single Microphone/Speaker Jack
- Certified for safe use by children in accordance with the United States Consumer Product Safety Commission**



Parameter	Value
Connections Microphone/Speaker Plug 3.5mm	Black
Microphone Noise Cancellation	5.0 dB/octave
Frequency Range	100-10,000 Hz
Electrical Signal-to-Noise Ratio	>60 dB
Sensitivity at 1 kHz (0 dB = 1 V/Pa)	-44 dB
Current Consumption	<0.5 mA
Speakers Frequency Range	50-20,000 Hz
Coil Resistance	32 ohm
Sound Output from 1 kHz 1mW Input (0 dB = 20 µPa)	114 dB
Maximum Input Power	40 mW



Proprietary Mic Design



Single Mobile Plug