



ReadyNAS: Storage Made Easy

Application data, virtual images, client files, email... the types of data central to running a successful business can seem endless. With ReadyNAS® you finally have an advanced and easy-to use solution for centralizing, securing and controlling access to your digital assets. Way more than just simple unified (NAS and SAN) storage for your company, ReadyNAS allows you to do more than you ever thought you could afford by pairing the latest in performance with innovative efficiency technologies such as unlimited snapshots, thin provisioning and cloud-managed replication.

Every networked attached storage (NAS) device from NETGEAR runs on the revolutionary ReadyNAS operating system. This custom-built OS protects stored data not only with XRAID2™ automatic expansion, but is the first desktop NAS for the SMB to feature the continuous data protection of unlimited snapshots along with real-time anti-virus and native encryption. Designed specifically for the unique needs of small business users, ReadyNAS devices utilize proprietary ReadyCLOUD™ technology for cloud-based discovery, provisioning and even ongoing management. In addition, these new devices are virtualization-ready with iSCSI support, thin provisioning capability and certification with VMware and Microsoft.

These days, your data is your world. With ReadyNAS, protecting and accessing that world has never been easier. ReadyNAS — Storage Made EASY.

Key Business Features



- **Unlimited Snapshots:** Unlimited data snapshot capability for on-box protection and flexible data recovery



- **XRAID2™ & Instant Provisioning:** Easily expand capacity and feel confident knowing that data is always protected



- **Cloud-managed Replication:** Maintain data sets in multiple locations or ensure protection of data from remote or branch office locations



- **iSCSI and Thin Provisioning:** Powerful tools for a businesses taking advantage of virtual infrastructures



- **Anti-virus & Encryption:** Keep data protected from outside threats and safe from prying eyes



- **Modern GUI and Cloud/Remote Access from Anywhere:** Sleek modern interface and patented technology for secure remote access without configuration effort

Key Business Solutions



- **File Server:** Unified storage platform for sharing files between Windows, Mac and Linux-based computers



- **Backup:** RAID redundancy with automatic expansion and unlimited data snapshots for point-in-time restore



- **Disaster Recovery:** Cloud-managed replication for maintaining multiple sets of data and performing easy restores in case of disaster





- **Virtualization:** Thin provisioning, iSCSI support and certified with VMware and Microsoft

ReadyNAS Solutions


File Sharing

These days, running a successful business often depends on successful file sharing—application data, virtual images, client files, email, all the digital files that make your business go. With ReadyNAS, you finally have an advanced and easy-to-use solution for centralizing, securing, and sharing those critical assets. Faster processors mean more simultaneous users can access unified storage—across PC, Mac and Linux environments. ReadyDROP and full Dropbox integration make it easier than ever to sync your important files, photos or videos across all of your web-connected devices.




Backup

Unlimited snapshots give you complete control over the past, present, and future of your data. This enterprise-class feature copies any point of time in the file system, can be manually or automatically scheduled, and can restore any version with a simple click. Other data protection innovations for disk-based storage like Real Time Anti-Virus and Encryption bring new confidence to the integrity of your data and back-ups.



Disaster Recovery

The custom-built ReadyNAS OS protects stored data with automatic RAID configuration, the continuous security of Unlimited Snapshots, and easy-to-manage Cloud Replication. By maintaining multiple copies of vital data through cloud replication, it makes it easy for you to move data offsite to protect against natural disasters and theft.



Virtualization

With Unlimited Snapshots, thin provisioning, and improved iSCSI support, ReadyNAS delivers a virtualization platform with next-generation features at an affordable price.

Technical Specifications

Data Protection (Backup & Replication)

- Unlimited block-based snapshots for continuous data protection
- Restore Snapshots to any point in time
- Restore Snapshot data from local admin GUI, ReadyCLOUD, or native Windows File Explorer
- Scheduled and manual snapshots
- File Synchronization (rsync)
- Encrypted Remote Replication
- Cloud managed Remote Replication (ReadyNAS to ReadyNAS). No licenses required for ReadyNAS OS 6 devices.
- AES 256-bit volume based encryption
- X-RAID2 (automatic single volume online expansion)
- Single Disk, JBOD
- RAID Levels: 0, 1, 5, 6, 10 (RAID level support depends on number of drives/bays)
- RAID Global Hot Spare
- eSATA Expansion
- Backup to external storage (USB/eSATA)
- Apple Time Machine support
- Remote Apple Time Machine backup and restore (over ReadyNAS Remote)
- ReadyNAS Vault™ Cloud backup (optional service)
- ReadyDROP file synchronization (sync folder on Mac/Windows to a folder on ReadyNAS)
- Dropbox™ file synchronization (requires Dropbox account)
- Real-time Anti-Virus scanning using signature and heuristic algorithms. (No end-user licenses required) Protection for viruses, malware, worms, and Trojans.

Storage Area Networks (SAN), Virtualization

- Unlimited iSCSI LUN Snapshot
- Thin or thick provision LUNs
- Multi-LUN per target
- LUN mapping
- LUN masking
- SPC-3 Persistent Reservation (iSCSI)
- MPIO (iSCSI)
- MC/S (iSCSI)
- Max # iSCSI Target: 256
- Max # iSCSI LUN: 256
- VMware vSphere 5
- Citrix XenServer 6

Windows Server

- Windows Server 2008 Hyper-V
- Windows Server 2008 Failover Clustering
- Windows Server 2012

ReadyCLOUD (cloud access to ReadyNAS)

- ReadyCLOUD portal based data access and management
- VPN quality remote data transfer and management
- Share data with friends & co-workers directly from portal

Remote Access Clients

- ReadyNAS Remote™ clients for Apple Mac OS X, Microsoft Windows, Android, Apple iOS (Remote file access and management client).
- VPN quality remote data transfer and management
- Simple remote access through ReadyNAS Remote (no firewall or router configuration needed)
- ReadyDROP file synchronization (sync folder on Mac/Windows to a folder on ReadyNAS)

File System & Transfer Protocols

- ReadyNAS OS 6
- Linux 3.x
- Internal File System: BTRFS
- External File System: EXT3, EXT4, NTFS, FAT32, HFS+
- Copy-on-write file system
- Microsoft Network (CIFS/SMB)
- Apple OS X (AFP 3.3)
- Linux/Unix (NFS v3)
- Internet (HTTP)
- Secure Internet (HTTPS)
- File Transfer Protocol (FTP)
- FTP over SSL / TLS (explicit)
- FTP Passive mode with port range setup
- FTP Bandwidth control
- FTP Anonymous
- FTP Transfer Log
- Secure Shell (SSH)
- SSH File Transfer Protocol (SFTP)
- Web Authoring (WebDAV)
- Storage Array Network (iSCSI)
- File Synchronization (rsync)
- Local web file manager

Users/Groups

- Max # Users: 8192
- Max # User Groups: 8192
- Max # Share Folder: 1024
- Max # Concurrent Connections: 1024
- Share Folder Level ACL Support
- Advanced Folder Permissions with Subfolder ACL support for CIFS/SMB, AFP, FTP
- Microsoft Active Directory (AD) Domain Controller Authentication
- Local access list
- ReadyCLOUD based ACL
- Domain user login via CIFS/SMB, AFP, FTP

Management

- ReadyCLOUD cloud based discovery and management
- RAIDar local discovery agent (Windows/Mac)
- Save and restore system configuration (clone devices)
- Local event log
- Connection reporting (SMB)
- Local Graphical User Interface (GUI) Languages: English, German, French, Japanese, Chinese, Russian, Swedish, Portuguese, Italian, Spanish, Polish, Czech, Dutch, Korean
- Genie+ marketplace integration to add productivity, media, backup, surveillance and other applications
- Unicode support
- Volume Management
- Thin provision Shares and LUNs
- Instant Provisioning/Expansion with data protection
- Restore to factory default
- Supported Operating Systems (Microsoft Windows Vista (32/64-bit), 7 (32/64-bit), 8 (32/64-bit), Microsoft Windows Server 2008 R2/2012, Apple OS X, Linux/Unix, Solaris, Apple iOS, Google Android)
- Supported Web Browsers (Microsoft Internet Explorer 9+, Mozilla Firefox 14+, Google Chrome 20+, Apple Safari 5+)

Technical Specifications

System Monitoring

- Device capacity, performance, resource and health monitoring
- Bad block scan
- Hard Drive S.M.A.R.T.
- File System Check
- Disk Scrubbing
- Disk Defragment
- Alerts (SMTP email, LCD, SNMP, syslog, local log)
- Auto-shutdown (hard drive, fan, UPS)
- Auto-restart on power recovery

Networking Protocols

- TCP/IP
- IPv4
- Next-generation Internet Protocol (IPv6)
- Static IP Address
- Dynamic IP Address
- Multiple IP Settings
- DHCP Client
- UPnP Discovery
- Bonjour Discovery
- Link Aggregation IEEE 802.3ad
- Port Trunking (balanced round robin, active backup, balance xor, broadcast, 802.3ad link aggregation LACP, transmit load balancing, adaptive load balancing)
- Hash Types IEEE 802.3ad LACP or XOR (Layer 2, Layer3, Layer 4)
- Jumbo Frames
- Virtual LAN (VLAN)
- SSH
- SNMP v2, v3
- Network Time Protocol (NTP)

Media

- ReadyDLNA (UPnP DLNA Media Server)
- ReadyDLNA Streams to any compliant device including PS3/Xbox 360
- ReadyDLNA mobile clients for remote media streaming (iOS, Android)
- ReadyDLNA supported music formats (wav, wma, pcm, ogg, mp3, m4a, flac, aac)

- ReadyDLNA supported photo formats (jpg, jpeg)

- ReadyDLNA supported video formats (3gp, mp4, wmv, xvid, vob, ts, tivo, mts, mpeg, mpg, mp4, mov, mkv, m4v, m4p, m2t, m2ts, flv, f4v, fla, divx, avi, asf)
- ReadyDLNA supported playlist formats (pls, m3u)

- ReadyNAS Surveillance (1-camera license included) supports over 85 brands and 2000 models of IP cameras

- ReadyNAS Surveillance supports up to 8 cameras (optional licenses required)

- iTunes Server

- iTunes supported audio formats (mp3, m4a, m4p, wav, aif)

- iTunes supported video formats (m4v, mov, mp4)

- iTunes supported playlist formats (m3u, wpl)

- TiVo Archiving

- Plex Media Server streams to DLNA and Plex clients (mobile, desktop, Google TV, Roku, Samsung & LG TVs)

Hardware

- Marvell® Armada™ XP (78230) 1.2GHz Dual Core
- Memory: 2GB DDR3
- Floating Point CPU
- Flash: 128MB for OS
- Drive Bays: 4
- Drive Types Supported: SATA/SSD 2.5" or 3.5"
- Hot Swappable Drives
- Two eSATA ports
- One USB 2.0 & Two USB 3.0 ports
- Total solution capacity: 16TB
- Dual Gigabit Ethernet ports with link aggregation and failover
- LEDs: Power, Activity, Disk, Backup, LAN
- Integrated rackmount ears
- Three 40mm fans
- Dimensions (DxWxH): 308mm x 430mm x 44mm
- Weight: 7.48 kg
- Power cord localized to country of sale

Compliance

- ENGR 10049 EST Environmental Stress Test Guideline
- ENGR 10045 EVT Engineering Validation Test Guideline
- ENGR 10048 CTV Compliance Validation Test Guideline
- ENGR 10046 System Validation Test Guideline
- ENGR 10023 HALT Accelerated Life Test Guideline
- ENGR 10036 CDG Component Derating Guideline

Environment

- Noise levels: <28dBA
- Operating Temperature: 0-40C
- Operating Humidity: 5-95% relative humidity, non-condensing
- Power Consumption (Operation): 38W
- Power Consumption (Wake on LAN): 1.4W
- Power Consumption (Power Off): 0.30W
- Smart Fan
- Scheduled Power on/off
- UPS Support
- Network UPS with SNMP Management
- Wake on LAN
- Schedule power on/off
- Auto-power on (after shutdown)
- AC Input Power Voltage 100V to 240V
- Power Frequency: 50Hz to 60Hz, Single Phase
- Certification: FCC Class B, CE Class B, RoHS, VCCI Class B
- Warranty: 5 years*

ProSUPPORT Service Packs Available

- OnCall 24x7 (1-year: PMB0313, 3-year: PMB0333, 5-year: PMB0353)
- XpressHW Replacement (3-year: PRR0333, 5-year PRR0353)

Accessories

- RTRAY04: Replacement/additional 3.5" or 2.5" hard drive tray
- RRAIL04: Sliding rack mount rail

*The 5-Year Hardware Warranty only covers hardware, fans, and internal power supplies, and does not include external power supplies or software. Hardware modifications or customization void the warranty. The warranty is only valid for the original purchaser and cannot be transferred. Warranty for included drives is 3-year for Desktop class drives and 5-year for Enterprise class drives.

NETGEAR, the NETGEAR Logo, ProSUPPORT, ReadyNAS, ReadyNAS Cloud, ReadyNAS Vault, and X-RAID are trademarks of NETGEAR, Inc. in the United States and/or other countries. Other brand names mentioned herein are for identification purposes only and may be trademarks of their respective holder(s). Information is subject to change without notice. © 2014 NETGEAR, Inc. All rights reserved.