



30" Industrial Fan

High Velocity Fan



Product Features

- 2 Speeds
- High Velocity
- Pull Chain Switch
- Adjustable Height 39" to 60"
- Individually Balanced Aluminum Blades
- Grounded Cordset Meets OSHA Requirements
- Approved for Sale in the US and Canada

#CZHVP30 (123790) pack 1

Product Specifications

Airflow Rate	1553 CFM
Box Dimensions	L-34.0" x W- 6.75" x H- 41.5"
EA Weight	61.3 lbs.
EA Cube	5.51'
Pallet Qty.	8
40' H/C Container Qty.	447
UPC-A Barcode	075877023797



Tel: 800-523-1268 • 609-860-9990 • Fax: 609-860-9991
324A Half Acre Rd., Cranbury, NJ 08512
www.comfortzoneforyou.com