



IZ2/UD2 Series



PROFILE

A small, affordable, energy-efficient hardware platform that can be VESA mounted on the back of a monitor (optional). The DVI-I port supports dual monitors with an optional Y-Cable and it can connect to common peripherals with its four USB ports.

FEATURES AND BENEFITS

- ▶ **Slim Design**
The perfect companion for any workplace due to the small form factor and the latest design.
- ▶ **Excellent price performance**
Very affordable price as Zero Client as well as Universal Desktop Thin Client.
- ▶ **Dualview support**
The DVI-I port offers the possibility to connect one digital and one analog monitor via the optional Y-Cable.
- ▶ **VESA mountable** (optional)
Mountable on the back of a monitor with the optional available VESA bracket, ideal for space constrained environments.
- ▶ **No moving parts, e.g. cooling fans**
The absence of moving parts means the devices are almost noiseless and fail-safe with minimal heat generation.
- ▶ **Free evaluation:**
www.igel.com/evaluation



DEVICES

Zero Clients
IZ2 HDX
IZ2 RFX
IZ2 Horizon

Universal Desktop
UD2 LX

Free evaluation:
www.igel.com/evaluation

COLOR

 black

PERIPHERAL INTERFACES



- 4 x USB 2.0
- RJ45 Ethernet
- PS/2-Keyboard
- DVI-I-Monitor
- Power
- Front:
Line-out, Mic-in



Microsoft Partner

Gold OEM
Gold Application Development



IGEL IZ2/UD2 SPECIFICATIONS

SYSTEM

Available Operating Systems	IGEL Linux v5 (LX)
Management	IGEL Universal Management Suite included
Form Factor	Standard Desktop
Processor	VIA Eden ULV 1 GHz
Chipset	VIA VX855

MEMORY

RAM	1 GB
Flash Memory	2 GB

GRAPHICS

Chipset	VIA Chrome9
Video Memory	64–256 MB shared memory
Ports	1 x DVI-I (DVI-to-VGA adapter available at no charge, please indicate interest when placing order)
Supported Resolutions	1920 x 1200, Dualview

NETWORK

Ethernet	10/100 Base-T
----------	---------------

AUDIO

Chipset	AC97 compatible
Ports	Front: 1 x line-out, 1 x mic-in
Speakers	1 x internal

PERIPHERAL INTERFACES

PS/2	1 x keyboard
Serial	Optional, via USB-to-Serial adapter
Parallel	Optional, via USB-to-Parallel adapter
USB 2.0	4 x back
Kensington Lock	1 x back

DIMENSIONS

Device (D x W x H), upright	203 x 55 x 208 mm
Packaging (D x W x H), horizontal	268 x 112 x 264 mm
Weight (without foot)	0.9 kg

ENVIRONMENT

Cooling	Fanless convection
Operating Temperature	0° to 40° C (vertical) 0° to 35° C (horizontal, with rubber feet)
Operating Humidity	10%–80%, non-condensing

POWER

Input	Auto sensing 100~240 VAC / 50~60 Hz
Power Supply	External
Power Consumption: Idle / Sleep Mode	9W / 2W

OPTIONS

VESA Mount	For mounting on the back of a monitor
Rubber Feet	For horizontal placement of the device
Dualview Y-Cable	For DVI-I to DVI-D + VGA. Connect two monitors
USB-to-Serial Adapter	For connecting peripherals that require a serial port
USB-to-Parallel Adapter	For connecting printers that require a parallel port
Shared WorkPlace (only UD2 LX)	It allows user-dependent configuration based on setting profiles

After purchase, just register with us online, and all your IGEL thin clients UD2, UD3, and UD5 will be upgraded from a standard 2-year to a 5-year hardware warranty, according to our end customer hardware warranty declaration, at no additional cost. The UD9, UD10, IZ1, IZ2 and IZ3 series will be upgraded to a 3-year hardware warranty. The warranty upgrade does not cover any additional hardware options. IGEL is a registered trademark of IGEL Technology GmbH. All hardware and software names are registered trademarks of the respective manufacturers. Errors and omissions excepted.
©06/2014 IGEL Technology | 85-EN-1-7 | WEEE-Reg.-Nr. DE 79295479

IGEL Technology Ltd | info@igel.com | www.igel.co.uk | www.igel.com/en

GERMANY Augsburg Bremen Mainz	AUSTRALIA Sydney	AUSTRIA Vienna	BELGIUM Leuven	CHINA Hong Kong Beijing Shanghai Guangzhou	FRANCE Paris	THE NETHERLANDS Utrecht	SINGAPORE Singapore	SWEDEN Sundsvall	SWITZERLAND Zurich	UNITED KINGDOM Reading	UNITED STATES Cincinnati
--	---------------------	-------------------	-------------------	--	-----------------	----------------------------	------------------------	---------------------	-----------------------	---------------------------	-----------------------------

info@igel.com
www.igel.com



thin clients | development | services | solutions

Many functions. One device.