

## 1 x 4 VGA over Cat5/6 Extender Kit, Transmitter/Receiver for Video, 2 Local/2 Remote Displays, Up to 500 ft. (152 m)

MODEL NUMBER: **B130-202**



### Features

- Connect up to 4 VGA monitors - 2 local and 2 remote
- Extends a 1440 x 900 @ 60Hz signal up to 165 ft. (50 m) from the source
- Extends a 1024 x 768 @ 60Hz signal up to 500 ft. (150 m) from the source
- EDID copy feature ensures optimal display compatibility
- Built-in equalization control allows for adjustment of the video image
- All operating systems supported
- Plug-and-play; no software or drivers are required
- HDCP compliant

## Specifications

OVERVIEW	
UPC Code	037332182630
Product Type	Extender Kit
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A, 4.5 ft.
Technology	VGA/SVGA; Cat5/5e; Cat6
VIDEO	
Max Supported Video Resolution	1440x900 @ 60Hz
Max 720P Range (ft)	165

### Highlights

- Extends a VGA signal up to 500 ft.
- Connect up to four VGA monitors: 2 Local and 2 Remote
- EDID copy feature ensures optimal display compatibility

### System Requirements

- PC with VGA video output
- Monitors with VGA input

### Package Includes

- Transmitter Unit
- Receiver Unit
- (2) External Power Supplies with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A, 4.5 ft.)
- Screwdriver for equalization adjustment
- Owner's manual

Max 1280 x 720 (720p) Range (ft)	165
Transmitter Video Input	VGA
Transmitter - Number of Video Outputs	2
Transmitter - Local Display Output	VGA
Receiver/Transceiver Video Output	VGA
Receiver - Number of Video Outputs	2
Signal Range (ft)	500ft @ 1024 x 768 (60Hz) 165ft @ 1440 x 900 (60Hz)
Signal Range (m)	152.4m @ 1024 x 768 (60Hz) 50m @ 1440 x 900 (60Hz)
Range Extension using other Tripp Lite product	1000ft @ 1024 x 768 (60Hz) 500ft @ 1920 x 1440 (60Hz)
Recommended Cabling	Solid Wire Cat6 Cables (Tripp Lite's N202-Series)
Other Tripp Lite product used to extend range	B132-110A
<b>POWER</b>	
Power Source	Transmitter and Receiver (Included)
Power Source Type	AC Adapter
AC Plug Type	NEMA 1-15P
External Power Supply Input Specs (V / Hz / A)	100-240V / 50-60Hz / 0.5A
External Power Supply Output Specs (V / A)	5V/2A
External Power Supply Cord Length (ft.)	4.5
External Power Supply Cord Length (m.)	1.38
External Power Supply DC Barrel Connector Specs	OD: 5.5 x 2.1 x 7.5mm, Positive Pin, Negative Sleeve
External Power Supply Certifications	FCC; PSE; TUV; UL; cUL
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	TX & RX: Red (Power); EDID (Orange); RJ45: Green (Connection), Orange (Data Transmission)
<b>PHYSICAL</b>	
Color	Black
Included Mounting Accessories	Wallmount
Number of Displays	4
Optional Mounting Accessory Notes	Can DIN Mount using Tripp Lite Bracket &nbsp;<a class="productLink" href="//www.tripplite.com/din-rail-mounting-bracket-for-digital-signage-version-1-B110-DIN-01">B110-DIN-01</a>&nbsp;
Form Factor/Mounting Options	Box; Wall-mount

Receiver Unit Dimensions (hwd / in.)	4.53 x 1.06 x 2.46
Receiver Unit Weight (lbs.)	0.5
Shipping Dimensions (hwd / cm)	5.59 x 16.00 x 21.34
Shipping Dimensions (hwd / in.)	2.20 x 6.30 x 8.40
Shipping Weight (kg)	0.82
Shipping Weight (lbs.)	1.80
Transmitter Unit Dimensions (hwd / in.)	4.53 x 1.06 x 2.46
Transmitter Unit Weight (lbs.)	0.5
Unit Dimensions (hwd / cm)	Transmitter: 2.69 x 11.43 x 6.2 Receiver: 2.69 x 11.43 x 6.2
Unit Packaging Type	Box
Housing	Metal
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32 to 122 F (0 to 50 C)
Storage Temperature Range	-4 to 158 (-20 to 70 C)
Relative Humidity	10% to 90% RH, Non-Condensing
<b>COMMUNICATIONS</b>	
Max 1024 x 768 Range (ft)	500
Max 480P Range (ft)	500
Max 1440 x 900 Range (ft)	165
Max 480i Range (ft)	500
Max 640 x 480 Range (ft)	500
Max 800 x 600 Range (ft)	500
EDID Compatible	Yes
USB Extension Support	No
<b>CONNECTIONS</b>	
Ports	2
Side A - Connector 1	(3) HD15 (FEMALE)
Side A - Connector 2	RJ45 (FEMALE)
Side B - Connector 1	(2) HD15 (FEMALE)
Side B - Connector 2	RJ45 (FEMALE)
<b>FEATURES &amp; SPECIFICATIONS</b>	
Driver Required	No



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Built-In Equalizer	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>