

OnSite Shred at the Source!



AC Geared Motor: Powerful, durable and built to outlast the competition



LED Control Panel: Easy to use with load indicator and energy-saving ECO Mode



AC Geared Motor: Heavy duty steel gears for high performance and minimal noise



Heavy Duty Waste Bin: Rugged molded plastic with a lifetime guarantee

FD 8602CC / SC OFFICE SHREDDER

Commercial-grade components in a sleek, compact design

Formax FD 8602CC & FD 8602SC Office Shredders combine document security with convenience, safety and reliability. Cross-cut and Strip-cut models feature an easy-to-use LED control panel and an extra-wide 16" feed opening which accommodates green-bar computer forms.

Commercial-grade components include heat-treated steel blades, a steel cabinet, lifetime guaranteed waste bin, and a powerful AC geared-motor to ensure years of reliable performance and information security in your office environment. In addition, the ECO Mode saves energy by automatically switching into standby mode after 5 minutes of inactivity.

The optional EvenFlow™ Automatic Oiling System helps to keep the FD 8602CC and FD 8602SC in peak operating condition.

FORMAX®

Standard Features

- Auto Start/Auto Stop:** Optical sensor detects paper and starts operation automatically
- LED Control Panel with Load Indicator:** Provides machine status and helps operators avoid jams
- ECO Mode:** Automatically enters energy-saving standby mode after 5 minutes of inactivity
- Door Safety Sensor:** Motor stops automatically if cabinet door is opened
- Auto Reverse:** In case of paper jam, built-in controls switch motor into reverse to clear jam
- Heat-treated Steel Cutting Blades:** Specially ground for longevity and require minimal oil
- High Quality Geared Motor:** Powerful, efficient AC geared-motor with heavy duty steel gears for high performance, minimal noise and continuous operation
- Extra-wide 16" feed opening**
- All-Metal Cabinet with casters**
- Auto Sensor:** Motor stops automatically when waste bin is full
- Lifetime Guaranteed Heavy-Duty Waste Bin**
- Auto Cleaning:** Press reverse button for 5 seconds and motor will run in reverse for 1 minute
- Oil Indicator:** Control panel LED flashes to suggest oiling cutting blades for optimal performance
- Self-Diagnosis System:** Records a variety of information for use by service technicians
- Thermal Overload Protection**
- Safety Circuit Breaker:** Ensures safe operation

Abilities

- Accepts staples, paper clips and credit cards
- Manual Function:** For shredding small paper or films which can't be detected by the sensor

Options

- EvenFlow™ Automatic Oiling System:** Lubricates cutting blades for optimal performance

Supplies

- Cutting Head Lubricating Oil:** #8000-10, six 8-ounce bottles per case
- Shredder Bags:** Uses #8000-50, case of 100

Warranty

- Lifetime Limited Warranty:** Cutting head
- 1-Year Warranty:** All other parts

Specifications:

FD 8602CC

FD 8602SC

Cutting Style:	Cross Cut	Strip Cut
Shred Size:	5/32" x 1-1/5"	1/4"
Sheet Capacity:	35 to 37	29 to 31
Speed:	22 fpm	30 fpm
Feed Opening:	16"	16"
Dimensions:	24" W x 20" D x 35" H	24" W x 20" D x 35" H
Bin Capacity:	33 gal.	33 gal.
Weight:	242 lbs.	242 lbs.
Security Level:	Level 3 (HIPAA Compliant)	Level 2
Power Supply:	110V, 50/60 Hz	110V, 50/60 Hz

* Sheet capacity varies depending on paper and power supply



Easy-to-use control panel with Load Indicator and ECO Mode



Lifetime Guaranteed Heavy-Duty Waste Bin



Optional EvenFlow™ Automatic Oiling System

Formax – New Hampshire, USA
www.formax.com

Local Dealer: