

# Product data sheet

Specifications



APC Smart-UPS On-Line, 10kVA/10kW, Rackmount 10U, 208V, 24x 5-20R+4x L6-30R NEMA, Network Card+SmartSlot, W/ rail kit, W/ 2 transformer 208V to 120V

SRT10KRMXLT-5KTF2

## Overview

Lead time Usually in Stock

## Main

Main Input Voltage	208 V
Product or Component Type	Uninterruptible power supply (UPS)
Main Output Voltage	120 V
Kw Rating	10000 W
Rated power in VA	10000 VA
output connection type	24 NEMA 5-20R 4 NEMA L6-30R
Output connector type	Hard Wire 3-wire (2PH + G) 1
number of rack unit	10U
Provided equipment	CD with software Documentation CD Installation guide Rack mounting hardware Rack Mounting brackets Rack Mounting support rails Temperature Probe USB cable Warranty card Web/SNMP Management Card
Range of Product	Smart-UPS On-Line

## Batteries & Runtime

Run Time	<a href="#">View Runtime Graph</a>
Efficiency	<a href="#">View Efficiency Graph</a>
Battery Type	Lead-Acid battery
Included Battery Modules	0
Typical recharge time	1.5 h
RBC Quantity	2
Battery Voltage	+/-192 V (split battery referenced to neutral)
Battery Charge Power (Watts)	1191 W rated
Battery life	3...5 year(s)
Replacement battery	<a href="#">APCRBC140</a>

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

---

Extendable Run Time	1
---------------------	---

## General

---

Topology	Double Conversion Online
----------	--------------------------

---

product web sub-family	High density
------------------------	--------------

---

Number of power module free slots	0
-----------------------------------	---

---

Number of power module filled slots	0
-------------------------------------	---

---

Redundant	No
-----------	----

## Physical

---

color	Black
-------	-------

---

Height	17.4 in (44.1 cm)
--------	-------------------

---

Width	17.008 in (43.2 cm)
-------	---------------------

---

Depth	28.1 in (71.5 cm)
-------	-------------------

---

Net Weight	436.009 lb(US) (197.77 kg)
------------	----------------------------

---

Mounting Location	Front
-------------------	-------

---

Mounting preference	Lower
---------------------	-------

---

Mounting Mode	Rack-mounted
---------------	--------------

---

Two post mountable	0
--------------------	---

---

USB compatible	Yes
----------------	-----

---

Mounting position	Horizontal
-------------------	------------

## Input

---

Input Frequency	40 - 70 Hz auto-sensing
-----------------	-------------------------

---

Number of input connectors	1 Hard Wire 3-wire (2PH + G)
----------------------------	------------------------------

---

Efficiency at full load	100...275 V adjustable (half load)
-------------------------	------------------------------------

## Output

---

Maximum configurable power in VA	10000 VA
----------------------------------	----------

---

Max Configurable Power (Watts)	10000 W
--------------------------------	---------

---

Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains
----------------------------------	---------------------------------

---

Waveform Type	Sine wave
---------------	-----------

---

Harmonic distortion	Less than 2%
---------------------	--------------

---

Crest factor	3 : 1
--------------	-------

---

Bypass type	Internal Bypass (Automatic and Manual)
-------------	----------------------------------------

## Conformance

---

Product Certifications	ENERGY STAR V2.0 (USA) FCC part 15 class A UL 1778
------------------------	----------------------------------------------------------

## Environmental

---

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
---------------------------------------	-------------------------

Relative Humidity	0...95 % non-condensing
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 % non-condensing
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)
Acoustic level	55 dBA
Online Thermal Dissipation	2490 Btu/h
IP degree of protection	IP20

## Communications & Management

Free slots	1
Pre-Installed SmartSlot™ Cards	Network management card 3 with environmental monitoring
Alarm	Audible and visible alarms : prioritized by severity
Emergency Power Off (EPO)	Yes

## Surge Protection and Filtering

Surge energy rating	480 J
---------------------	-------

## Ordering and shipping details

GTIN	731304732907
Country of origin	PH

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	41.7 in (106 cm)
Package 1 Width	39.4 in (100 cm)
Package 1 Length	24.5 in (62.2 cm)
Package 1 Weight	511.80 lb(US) (232.15 kg)

## Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
----------	-----------------------------------------------------------------------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)




Energy Efficient Take-back Transparency RoHS/REACH


## Resource performance

 Energy Efficient Product

 Take-Back Program Available

## Well-being performance

 Mercury Free

 Rohs Exemption Information Yes

## Environmental Certifications

 Energy Star® ENERGY STAR UPS V2.0 (USA)

## Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)

**California Proposition 65** WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)