



## Designed for mobile public safety applications

**KBA BLH-5RU**      USB

### Key Features:

- Very rugged integrated pointing device
- Special "emergency" key which, when pressed, sends a signal of Shift + F1 and is illuminated brighter than other keys for 15 seconds
- Meets NEMA 4 requirements
- Fully customizable
- Low cost, low profile with full size keys
- Tactile feedback
- LED backlighting good for life of keyboard
- Black keypads with bold legends
- FCC, UL, and CE compliant

### Electrical:

- Voltage: +5Vdc from data cord
- Current:
  - Non-backlit: 100mA max
  - Backlit: 500mA
- Interface: USB
- Radiated immunity: 20 volts/meter
- Dimming has eight levels of intensity controlled by a single button

### Environmental:

- Storage temperature: -55C to +85C
- Operating temperature: -40 to +75C
- Humidity: 100%

### Backlighting:

- Bold backlighting
- LED backlighting good for life of product
- Red standard with other colors available
- Dimming: 8 levels of brightness including "off"
- 200,000 hr LEDs = 22 years continuous "on"

### Mechanical:

- 82 key compact disk
- Overall dimensions: 12" x 6" x 1.5
- Weight: 2lbs
- 5 million cycle keyswitches with gold contacts
- Plastic injection molded top for ease of customizing mounting techniques

### Industrial Ratings:

- NEMA 4
- UL 60950
- CE
- FCC Class B