



UD6 Series



PROFILE

Maximum performance for maximum requirements! Our most powerful hardware series sets a new standard in thin client computing. Because of its fast quad-core processor and flexible expansion capability, the UD6 is the device of choice for the most demanding use scenarios. Video playback in Full HD, computer-aided design (CAD) or 3D applications – none pose the slightest problem for the new high-end model. Outfitted with multiple interfaces, including USB 3.0 and PCIe slot, the UD6 series offers you everything on your wish list.

FEATURES AND BENEFITS

- ▶ **Maximum Performance**
The highest processor and graphics performance for the most demanding tasks, e.g., Flash multimedia, CAD applications, video playback in Full HD.
- ▶ **Free PCIe slot**
Customize the UD6 for individual needs via PCIe expansion cards, e.g., fiber optic network cards.
- ▶ **Dualview support**
Parallel use of two digital monitors with a DVI and a DisplayPort.
- ▶ **Integrated smartcard reader (optional)**
Excellent for highly secure two factor authentication and fast login.
- ▶ **Connectivity bar (optional)**
Expand your device with a parallel port and WLAN or an anti-theft USB port.
- ▶ **No moving parts, e.g. cooling fans**
Because it contains no moving parts, the UD6 makes almost no noise, is nearly failsafe and produces minimal heat – even with high-performance usage



DEVICES

UD6 LX
UD6 W7
UD6 W7+

COLOR



black

OPTIONS

Connectivity bar:
Optional connectivity for parallel I/O and wireless networking or an anti-theft USB port.



PERIPHERAL INTERFACES



2 x USB 3.0
2 x USB 2.0
RJ45 Ethernet
Stereo-out / Mic-in
PS/2 Keyboard
PCIe Slot
DVI-I
2 x Serial Port
Display Port
Power

Front: 2 x USB 2.0

Free evaluation:
www.igel.com/evaluation

IGEL UD6 SPECIFICATIONS

**CITRIX®
READY**

Microsoft Partner

Gold OEM
Gold Application Development

**vmware®
READY**
END-USER
COMPUTING

SYSTEM

Available Operating Systems	IGEL Linux v5 (LX) Microsoft Windows Embedded Standard 7 (W7 / W7+)
Management	IGEL Universal Management Suite included
Form Factor	Standard
Processor	Intel Celeron J1900 1,99 - 2,42 GHz Quad-Core
Chipset	Intel Bay Trail SoC
PCI-slot	1 x (low profile)

MEMORY

RAM (DDR3L)	2 GB (LX / W7 / W7+)
Flash Memory (SATA SSD)	2 GB (LX), 4 GB (W7), 8 GB (W7+), larger SSD modules on request

GRAPHICS

Chipset	Intel HD Graphics
Video Memory	64 – 512 MB Shared Memory
Ports (Supported Resolutions)	1x DisplayPort 1.1a (max. 2560 x 1600) 1x DVI-I (max. 1920 x 1200)

NETWORK

Ethernet	10/100/1000 Base-T
WLAN	Optional, via connectivity bar

AUDIO

Chipset	Realtek High Definition Audio (ALC662)
Ports	1 x line-out, 1 x mic-in
Speakers	1 x internal

PERIPHERAL INTERFACES

PS/2	1 x keyboard
Serial	2x
Parallel	1 x optional, via connectivity bar or USB-to-Parallel adapter
USB 2.0	2x front, 2x back; optional: anti-theft USB (via connectivity bar)
USB 3.0	2x back
Kensington Lock	1 x back

DIMENSIONS

Device (D x W x H), upright	232 x 99 x 242 mm with foot, 232 x 74 x 225 mm without foot
Packaging (D x W x H), horizontal	297 x 366 x 125 mm
Weight (without foot)	1.47 kg

ENVIRONMENT

Cooling	Fanless convection
Operating Temperature	0° to 40°C (vertical) 0° to 40°C (horizontal, with rubber feet)
Operating Humidity	20% – 80%, non-condensing

POWER

Input	Auto sensing 100~240VAC / 50~60 Hz
Power Supply	External
Power Consumption: Idle / Sleep Mode	8W / < 1W

OPTIONS

VESA Mount	For mounting on the back of a monitor
Rubber Feet	For horizontal placement of the device
Connectivity Bar	Option 1: parallel port and anti-theft USB port Option 2: 1x parallel and 1x 802.11 a/b/g/n 2,4 GHz, 5 GHz WLAN
Built-in Smartcard Reader	For secure smartcard-based authentication
USB-to-Serial Adapter	For connecting peripherals that require a serial port
USB-to-Parallel Adapter	For connecting printers that require a parallel port
DisplayPort to DVI Adapter	For connecting a monitor that requires a DVI port
Shared WorkPlace	It allows user-dependent configuration based on setting profiles
Multimedia Codec Pack (UD Linux)	Required for multimedia re-direction and full multimedia functionality

After purchase, just register with us online, and all your IGEL thin clients UD2, UD3, UD5 and UD6 will be upgraded from a standard 2-year to a 5-year hardware warranty, according to our end customer hardware warranty declaration, at no additional cost. The UD9, UD10, IZ2 and IZ3 series will be upgraded to a 3-year hardware warranty. The warranty upgrade does not cover any additional hardware options. IGEL is a registered trademark of IGEL Technology GmbH. All hardware and software names are registered trademarks of the respective manufacturers. Errors and omissions excepted.

©01/2015 IGEL Technology | 85-EN-21-1 | WEEE-Reg.-Nr. DE 79295479

IGEL Technology Ltd | info@igel.com | www.igel.co.uk | www.igel.com/en

GERMANY
Augsburg
Bremen
Mainz

AUSTRALIA
Sydney

AUSTRIA
Vienna

BELGIUM
Leuven

CHINA
Hong Kong
Beijing
Shanghai
Guangzhou

FRANCE
Paris

THE NETHERLANDS
Utrecht

SINGAPORE
Singapore

SWEDEN
Sundsvall

SWITZERLAND
Zurich

UNITED KINGDOM
Reading

UNITED STATES
Cincinnati
New York

info@igel.com
www.igel.com



thin clients | development | services | solutions

Many functions. One device.