

# 24" (23.6" viewable) Full HD Multimedia LED Monitor with HDMI

Stunning Color Performance with SuperClear® MVA Technology

**VA2465Smh**



Available for this model:

**Privacy Filter Screen Protector**

VSPF2360  
(Sold Separately)

The ViewSonic® VA2465Smh 24" (23.6" viewable) LED backlit, HD widescreen monitor delivers stunning images driven by our latest SuperClear® MVA panel technology and a 3000:1 contrast ratio. With HDMI 1.4 and VGA support and built-in speakers, this monitor supports a variety of devices from your PC to your latest gaming device. Our exclusive ViewMode™ setting optimizes the monitor for a variety of applications from gaming to editing your next novel. Integrated Flicker-free and Blue Light Filter technology helps eliminate eye-strain during extended viewing periods. The VA2465Smh includes a VESA-mountable design to provide additional mounting options. Backed by our 3-year limited warranty and one of the industry's best pixel performance policies, the VA2465Smh packs an amazing amount of performance in a sleek streamlined design.

#### **Key Features:**

SuperClear® MVA technology for stunning color performance and wide-angle viewing

Flexible connectivity options include HDMI and VGA

Full HD1080p resolution provides superior pixel performance

Exclusive ViewMode technology delivers superior color rendering and intuitive settings

Flicker-free and Blue Light Filter technology for more comfortable viewing

#### **Designed for:**

Home

Business

# 24" (23.6" viewable) Full HD Multimedia LED Monitor with HDMI

VA2465Smh



**1080p**  
Full HD



## Specifications

LCD PANEL	
Type	Color a-Si Active Matrix TFT LCD
Display Area	20.5" horizontal x 11.5" vertical; 23.6" diagonal
Optimum Resolution	1920x1080
Brightness	250 cd/m <sup>2</sup> (typ.)
Contrast Ratio	3,000:1 (typ.)
Viewing Angles	178° horizontal, 178° vertical
Colors	16.7M (6bit + Hi-FRC)
Response Time	6.5ms (GTG)
Backlight	White-light LED
Backlight Life	40,000 hours (min.)
Panel Surface	Anti-glare, hard-coating (3H)
VIDEO INPUT	
Digital Frequency	VGA, HDMI
Sync	Fh: 24~82kHz, Fv: 50~75Hz
	Separate Sync, Composite Sync, Sync on Green
AUDIO OUTPUT	
Speakers	2-watt (x2)
COMPATIBILITY	
PC	Up to 1920x1080 non-interlaced
Mac®	Up to 1920x1080
CONNECTOR	
Video In	VGA, HDMI
Audio In	3.5mm mini jack
Headphone	3.5mm mini jack
Power	External power adapter
CONTROLS	
Front Panel Buttons	Power, 1, Up, Down, 2
OSD	Auto Image Adjust, Contrast/Brightness, Input Select, Audio Adjust, Color Adjust, Information, Manual Image Adjust, Setup Menu, Memory Recall (See user guide for complete OSD functionality)

## Optional Accessories

ViewSonic HDMI male to DVI male cable 1.8 meter ..... CB-00008948

ERGONOMICS	Tilt	Forward 5° / Back 20°
POWER	Voltage Consumption Optimize Conserve	AC 100~240V (universal), 50 / 60Hz 22W (typ.) / 30W (max.) 17W (typ.) 13W (typ.)
OPERATING CONDITIONS	Temperature Humidity	32~104° F (0~40° C) 20~90% (non-condensing)
DIMENSIONS (W x H x D)	Physical with Stand Physical without Stand Packaging	22.2 x 16.1 x 7.6 in. / 563.9 x 407.2 x 193.1 mm 22.2 x 13.7 x 1.8 in. / 563.9 x 347.1 x 46.0 mm 24.6 x 16.4 x 5.2 in. / 624 x 417 x 132 mm
WEIGHT	Net with Stand Net without Stand Gross	9.0 lb. / 4.1 kg 7.8 lb. / 3.6 kg 11.6 lb. / 5.3 kg
WALL MOUNT	VESA	100 x 100mm
REGULATIONS		CE CB, WEEE, RoHS, TCO 6.0, Erp, WHQL, cUL, ENERGY STAR, FCC-B, EPEAT Silver
RECYCLE/DISPOSAL		Please dispose of in accordance with local, state, or federal laws
WARRANTY		Three-year limited warranty on parts, labor and backlight

## What's in the box?

VA2465Smh monitor, Power cable, VGA cable, Quick Start Guide

