

Monitor | B226HQL

Flexible viewing, professional style

- Ergonomic stand: adjustable tilt, swivel, pivot and height
- Earth-friendly: recycled plastic, LED backlight, Acer EcoDisplay
- 21.5" Full HD Acer ComfyView display with Acer eColor technology
- Extensive connectivity: DisplayPort™, VGA, DVI and USB3.0


The Acer B6 series is a powerful professional monitor line which defines the essences of top ergonomics and versatile productivity. The Acer B226HQL is designed for professionals who require exceptional visuals and comfortable viewing. This professional display has 21.5" non-glare screen with White LED Technology that ensures exceptional reliability and great energy savings.

The smart professional B226HQL display provides multiple interface options, including DisplayPort and traditional DVI/VGA, as well as 4 USB 3.0 ports.

LED used technology, together with high quality VA Wide Viewing Angle panel, offers superior performance and durability while minimizing environmental impact.



| | | |
|-------------------------------------|------------------------------|------------------|
| Model number | B226HQL A | |
| Display | 21.5" (16:9) | |
| Active display area | 47.6 x 26.8 cm | |
| Panel type | VA | |
| Maximum resolution and refresh rate | 1920 x 1080 @ 60 Hz | |
| Glare | No | |
| Response time | 8 ms (G to G) | |
| Contrast ratio (ACM) | 100 million:1 max | |
| Brightness | 250 cd/m ² | |
| Viewing angle (CR=10) | 178° (H), 178° (V) | |
| Colors | 16.7 million | |
| Bits | 6-bit + Hi-FRC | |
| Input signal | 1) VGA + DVI (DVI with HDCP) | |
| VESA wall mount | 100 x 100 mm | |
| Speaker | 2 x 1 W | |
| Power supply (100 – 240 V) | Internal | |
| Power consumption (ENERGY STAR®) | Off | 0.25 W (typical) |
| | Sleep | 0.35 W (typical) |
| | On | 19.5 W (typical) |



Unit: cm



Full HD LED monitor



The 1920 x 1080 resolution of this LED monitor delivers excellent detail, making it perfect for advanced HD productivity and multimedia applications. LED monitors also consume less power and last longer than those with CCFL lamps. In addition, this monitor is mercury-free, making it safer for you and the environment.



Acer Eco Display

Acer monitors using white LED backlight technology minimize environmental impact while providing superior performance. White LED monitors do not contain *mercury*, making them safer for the environment. They also consume less power and are more durable than CCFL lamps, for good savings. Plus, as part of our commitment to sustainable operations and CSR, Acer uses methods to carry out product design and material management distinctly meant to reduce environmental impact.

ErgoStand

The ergonomic design of this monitor optimizes the viewing position for maximum comfort even during prolonged use.



- Height: 150 mm up or down
- Tilt: 35° up or 5° down
- Swivel: 60° to the left and right
- Pivot (rotation): Up to 90°



ComfyView

Acer ComfyView monitors reflect less ambient light to deliver vivid colors, reduced glare and more comfortable viewing, even over prolonged periods.

About Acer

Established in 1976, Acer is an information and communication technology company dedicated to the research, design, marketing, sale and support of innovative products that enhance people's lives. Acer's green supply chain delivers environmentally friendly PCs, displays, projectors, servers, tablets and smartphones — tools our customers need to explore beyond limits and experience more. Ranked No. 2 for notebooks globally (Gartner 2011), Acer employs 8,000 people, and 2011 revenues reached US\$15.7 billion. Please visit www.acer.com for more information.

acer
explore beyond limits™