



HP Z240 Tower Workstation

The world's number one choice for entry level workstations features a choice of Tower or SFF configurations.⁴ It just got better with the HP Z240 which packs the performance, features, and reliability of a workstation into the price point of a desktop PC.



- Windows 10 Pro¹
- Intel® Xeon® processor²

Powered to manage your challenges

Powerful processors, graphics, memory, and two optional ultra-fast HP Z Turbo Drives⁴ make the HP Z240 a true workstation-class solution. Handle your growing and complex workloads with performance for any stage in your work process.

Small price, big possibilities

The essential features of the HP Z240 Tower easily support your workload with slots and ports to spare. When you're ready for workstation class features, like professional ISV certifications, the HP Z240 Tower is the right first step.

Priced for your budget

HP's most affordable workstation allows you to customize your experience while still balancing your IT budget. HP reliability, thorough testing, and ISV certification means your HP Z240 is designed as a long-term budget friendly solution.

Featuring

- Support your unique user needs with a choice of Windows 10 Pro¹ or Linux® operating systems.
- Get more performance, expandability and flexibility in the chassis the world loves.
- Achieve the performance you need with your choice of next generation Intel® Xeon® processors or Intel® Core™ processors.²
- Handle large files, reduce work time and increase performance with the optional HP Z Turbo Drive.³
- Up to 64 GB DDR4 ECC memory helps provide no compromise capacity, performance, and reliability.
- Ignite productivity with NVIDIA® professional graphics cards in 2D or 3D.³
- Access AMD professional graphics including high-end 3D on Tower configurations.⁵
- Help internal components stay clean and cool with a removable and cleanable dust filter.
- Charge your device using the fast charging front USB port.

HP Z240 Tower Workstation Specifications Table



Form Factor	Tower
Operating System	Windows 10 Pro 64 ¹ Windows 10 Home 64 ¹ Windows 7 Professional 64 ¹ Windows 7 Professional 64 (available through downgrade rights from Windows 10 Pro 64) ² HP Linux-ready
Processor Family	Intel® Xeon® E3 processor; Intel® Core™ i7 processor; Intel® Core™ i5 processor ³
Processors^{3,11}	Intel® Xeon® E3-1280 v5 (3.7 GHz, up to 4 GHz with Intel Turbo Boost Technology, 8 MB cache, 4 cores); Intel® Xeon® E3-1270 v5 (3.6 GHz, up to 4 GHz with Intel Turbo Boost Technology, 8 MB cache, 4 cores); Intel® Xeon® E3-1245 v5 with Intel HD Graphics P530 (3.5 GHz, up to 3.9 GHz with Intel Turbo Boost Technology, 8 MB cache, 4 cores); Intel® Xeon® E3-1240 v5 (3.5 GHz, up to 3.9 GHz with Intel Turbo Boost Technology, 8 MB cache, 4 cores); Intel® Xeon® E3-1230 v5 (3.4 GHz, up to 3.8 GHz with Intel Turbo Boost Technology, 8 MB cache, 4 cores); Intel® Xeon® E3-1225 v5 with Intel HD Graphics P530 (3.3 GHz, up to 3.7 GHz with Intel Turbo Boost Technology, 8 MB cache, 4 cores); Intel® Core™ i7-6700 with Intel HD Graphics 530 (3.4 GHz, up to 4 GHz with Intel Turbo Boost, 8 MB cache, 4 cores); Intel® Core™ i5-6600 with Intel HD Graphics 530 (3.3 GHz, up to 3.9 GHz with Intel Turbo Boost, 6 MB cache, 4 cores); Intel® Core™ i5-6500 with Intel HD Graphics 530 (3.2 GHz, up to 3.6 GHz with Intel Turbo Boost, 6 MB cache, 4 cores)
Chipset	Intel® C236
Maximum Memory	64 GB DDR4-2133 Unbuffered SDRAM (Transfer rates up to 2133 MT/s)
Memory Slots	4 UDIMM
Drive Controllers	Integrated SATA (4 ports 6 Gb/s) with RAID 0 (striped array) and RAID 1 (mirrored array) supported on Windows operating system only. Requires identical hard drives (speeds, capacity, interface). Integrated RAID 0, 1 (data configuration) for PCIe SSDs.
Internal Storage	500 GB up to 4 TB SATA (7200 rpm) ⁴ 500 GB SATA SED ⁴ 256 GB up to 1 TB SATA SSD ⁴ 256 GB SATA SED SSD ⁴ 1 TB SATA SSHD ⁴ 128 GB up to 512 GB HP Z Turbo Drive G2 (NVMe PCIe SSD) ⁴
Optical Storage	HP Slim DVD-ROM Drive; HP Slim SuperMulti DVD-RW Drive; HP Slim Blu-ray Writer ⁵
Additional Storage	SD media card reader (optional)
Available Graphics	Integrated: Intel® HD Graphics 530; Intel® HD Graphics P530 ⁶ Professional 2D: NVIDIA® NVS™ 310 (1 GB); NVIDIA® NVS™ 315 (1 GB); NVIDIA® NVS™ 510 (2 GB) Entry 3D: AMD FirePro™ W2100 (2 GB); NVIDIA® Quadro® K420 (2 GB); NVIDIA® Quadro® K620 (2 GB) Mid-range 3D: NVIDIA® Quadro® K2200 (4 GB); AMD FirePro™ W5100 (4 GB) High-end 3D: AMD FirePro™ W7100 (8 GB); NVIDIA® Quadro® M4000 (8 GB)
Audio	Integrated Realtek HD ALC221-VB audio
Networking	LAN: Integrated Intel® I219LM PCIe GbE; Intel® Ethernet I210-T1 PCIe NIC (optional) WLAN: Intel® 8260 802.11a/b/g/n/ac PCIe wireless NIC (optional)
Expansion Slots	1 PCIe Gen3 x16; 1 PCIe Gen3 x4 (x4 connector); 1 PCIe Gen3 x4 (x16 connector); 1 PCIe Gen3 x1; 1 PCI (optional)
Ports and Connectors	Front: 2 USB 3.0; 2 USB 2.0 (1 charging); 1 headphone; 1 microphone Back: 4 USB 3.0; 2 USB 2.0; 2 DisplayPort 1.2; 1 DVI-I single link; 1 serial (optional); 1 parallel (optional); 2 PS/2; 1 RJ-45; 1 audio line-in; 1 audio line-out; 2 IEEE 1394b (optional) Internal: 1 USB 3.0; 2 USB 2.0 (1 USB 3.0 and 2 USB 2.0 ports available as 2 separate 2x10(3.0 x1, 2.0 x1) and 2x5(2.0 x2) header. Supports one HP Internal USB 2.0 Port Kit and one USB 3.0 media card reader.)

Drive Bays (Internal)	One 2.5"; Two 3.5"
Drive Bays (External)	Two 5.25"; One slim ODD
Input Device	HP Wireless Business Slim Keyboard; HP USB CCID SmartCard Keyboard; HP USB Business Slim Keyboard; HP PS/2 Business Slim Keyboard ⁸ HP SpaceMouse Pro USB 3D; HP USB 1000 dpi Laser Mouse; HP USB Optical 3-Button Mouse; HP USB Optical Mouse; HP PS/2 Mouse; 3Dconnexion CADMouse ⁸
Software	HP Performance Advisor; HP Remote Graphics Software (RGS) 7.1; PDF Complete - Corporate Edition; Cyberlink Power DVD and Power2Go; HP PC Hardware Diagnostics UEFI; HP Client Security Software; Buy Office
Security	HP Solenoid Lock and Hood Sensor (optional); HP Business PC Security Lock kit (optional); HP UltraSlim Cable Lock Kit (optional)
Power	400 W 92% efficient, wide-ranging, active PFC; 280 W 90% efficient, wide-ranging, active PFC
Dimensions	6.7 x 17.4 x 15.7 in 170 x 442 x 399 mm (Standard tower orientation)
Weight	Starting at 18.95 lb Starting at 8.6 kg (Exact weight depends upon configuration)
Energy Efficiency Compliance	ENERGY STAR [®] certified and EPEAT [®] registered configurations available ⁹
Environmental Certification	Low halogen ¹⁰
Compatible Displays	HP Z27s 27-inch UHD Display; HP Z27q 27-inch IPS 5K Display; HP Z24s 24-inch UHD IPS Display; HP Z Display Z30i 30-inch IPS LED Backlit Monitor; HP Z Display Z27i 27-inch IPS LED Backlit Monitor; HP Z Display Z24i 24-inch IPS LED Backlit Monitor; HP Z Display Z23i 23-inch IPS LED Backlit Monitor; HP Z Display Z22i 21.5-inch IPS LED Backlit Monitor; HP DreamColor Z24x Professional Display; HP DreamColor Z27x Professional Display

HP Z240 Tower Workstation

Accessories and services (not included)

AMD FirePro™ W7100 8GB Graphics Card



Drive your advanced visualization, complex models, large data sets, and video editing and production applications across up to four displays with the AMD FirePro™ 7100 graphics board loaded with 8 GB GDDR5 memory.

Product number: J3G93AA

HP Z420 Handle in Top Optical Bay



The HP Z420 comes with a space in the optical drive bay for SFF internal hard disc drives. This handle covers that area in the top optical bay.

Product number: A9A48AA

HP Z24nq 23.8-inch Narrow Bezel IPS Display



Enjoy quad HD visuals on the HP Z24nq Narrow Bezel IPS Display, which has an edge-to-edge 23.8-inch diagonal screen for easy tiling of multiple displays¹, plus out-of-the-box color calibration and flexible connectivity for all of your devices.

Product number: L1K59A4

HP Z Turbo Drive G2 256GB PCIe Solid State Drive



Super charge your productivity and creativity and deliver optimized HP Workstation workflows with the HP Z Turbo Drive G2 PCIe SSD, which delivers four times the read performance of traditional SSDs at a cost that's remarkably similar.

Product number: M1F73AA

HP Z Turbo Drive G2 512GB PCIe Solid State Drive



Super charge your productivity and creativity and deliver optimized HP Workstation workflows with the HP Z Turbo Drive G2 PCIe SSD, which delivers four times the read performance of traditional SSDs at a cost that's remarkably similar.

Product number: M1F74AA

Messaging Footnotes

¹ Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers and/or software to take full advantage of Windows functionality. Windows 10 is automatically updated, which is always enabled. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.microsoft.com>.

² Multi-Core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering is not a measurement of higher performance.

³ Sold separately or as alternate features.

⁴ Source: IDC WW WS Historical Tracker 2015Q1 – 05.06.15

⁵ 3D graphics only available as AMO and are not available on small form factor configurations.

Technical Specifications Footnotes

¹ Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows 10 is automatically updated, which is always enabled. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.microsoft.com>.

² This system is preinstalled with Windows 7 Professional software and also comes with a license and media for Windows 10 Pro software. You may only use one version of the Windows software at a time. Switching between versions will require you to uninstall one version and install the other version. You must back up all data (files, photos, etc.) before uninstalling and installing operating systems to avoid loss of your data.

³ Multi-Core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering is not a measurement of higher performance.

⁴ For storage drives, GB = 1 billion bytes. TB = 1 trillion bytes. Actual formatted capacity is less. Up to 16 GB (for Windows 7) and up to 36 GB (for Windows 8.1 and 10) of system disk is reserved for system recovery software.

⁵ Duplication of copyrighted material is strictly prohibited. Actual speeds may vary. Double Layer media compatibility will widely vary with some home DVD players and DVD-ROM drives. Note that DVD-RAM cannot read or write to 2.6GB Single Sided/5.2 Double Sided-Version 1.0 Media.

⁶ HD content required to view HD images.

⁷ Wireless cards are optional or add-on features and requires separately purchased wireless access point and internet service. Availability of public wireless access points limited.

⁸ Optional or add-on feature.

⁹ EPEAT® registered where applicable. EPEAT registration varies by country. See www.epeat.net for registration status by country.

¹⁰ External power supplies, power cords, cables and peripherals are not low halogen. Service parts obtained after purchase may not be low halogen.

¹¹ Intel Turbo Boost performance varies depending on hardware, software and overall system configuration. See <http://www.intel.com/technology/turboboost> for more information.

Sign up for updates
hp.com/go/getupdated

Learn more at
hp.com

The product could differ from the images shown. © 2015 Hewlett-Packard Development Company, L.P. The information contained herein is subject to change without notice. Specific features may vary from model to model. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

ENERGY STAR and the ENERGY STAR mark are registered trademarks owned by the U.S. Environmental Protection Agency. Microsoft and Windows are U.S. trademarks of the Microsoft group of companies. Intel and Core are trademarks of Intel Corporation in the U.S. and other countries. Linux® is the registered trademark of Linus Torvalds in the U.S. and other countries. All other trademarks are the property of their respective owners.

