



The VisionTek Lightning to USB 3.0/2.0 Charge & Sync 0.25 meter cable lets you connect your iDevice to a USB 3.0 or 2.0 port.

Durable, everyday charging and data cable with Lightning connector. Upgrade your everyday charging cable to the high-speed USB-A cable with Lightning connector. With a sturdy cable and durable connectors, this cable stands up to everyday wear and tear. Whether you're charging your iPhone or iPad, the cable works seamlessly with all of your Apple devices.

**Lightning Connector Compatible** - Charge and sync any iOS devices with a Lightning connector such as your iPhone or AirPods.


**High-Speed USB 3.0 Cable** - Quickly and efficiently charge and backup your Apple devices.

**Quality Assured** - Vigorous testing and quality controls ensure each cable works properly.

**Plug and Play Use** - Fully compatible with Apple iDevices.

**Error-Free Operation** - Unlike generic cables, you're assured full compatibility so you can charge and sync free of any error message hassle.


PN 900779 | UPC 7 84090 03340 6



Compatible with most Apple Devices with a Lightning port, including iPhone 12, iPhone 12 Pro, iPhone 12 Mini, iPhone 12 Pro Max, iPhone 11, iPhone 11 Pro, iPhone 11 Pro Max, iPhone SE, iPhone XS, iPhone XS Max, iPhone XR, iPhone X, iPhone 8, iPad Pro, iPad Air, iPad, iPad mini, iPod touch, and AirPods. All previous Apple Devices with Lightning ports are also supported.

### Key Features

- Plug and Play.
- Error-Free Operation.
- Connects to Mac or PC USB 3.0/2.0 ports.
- Charge & Sync.
- 0.25 Meter (9.8") cable length.
- Two Year Warranty.



**Lightning ⇄ USB-A**  
 

All specifications are subject to change without notice. Products may not be available in all markets. The VisionTek name and design are registered trademarks of VisionTek Products, LLC. All other registered and unregistered trademarks are the property of their respective owners.

FOR MORE INFORMATION CONTACT: 1-866-883-5411 | [sales@visiontek.com](mailto:sales@visiontek.com)