

Xerox® WorkCentre™

4265

Letter / A4

Black and White

Multifunction Printer



Xerox® WorkCentre™ 4265

Simplify how you share information.

xerox 

Xerox® WorkCentre™ 4265 Multifunction Printer

Transform the way you work. The WorkCentre 4265 streamlines everyday office communications, providing the solutions you need to collaborate more effectively through simplified digital and paper-driven work flows – securely and cost effectively.

A Complete Solution

- **Customised for your business.** Whether you choose a desktop or floor-standing model, you get copy, print, scan, email and fax* functionality, plus a range of finishing and media handling options that let you tailor the WorkCentre 4265 to your office environment.
- **No more waiting.** Designed for businesses with intensive workloads, the WorkCentre 4265 scans up to 70 ipm, copies and prints as fast as 55 ppm letter / 53 ppm A4, and delivers the first page in as few as 8 seconds.
- **Define and control.** Xerox® Workflow Solutions, built on our Xerox Extensible Interface Platform®, hosted within the cloud or locally on a server, allows a highly personalised user experience and access to a range of useful applications directly from the colour touch screen.
- **Complete security.** The WorkCentre 4265 offers state of the art security features to ensure your data is protected. Common Access Card (CAC) support enables users to encrypt and digitally sign electronic documents; 256-bit AES encryption is iron-clad, and secure print, fax, and email means your communication is both safe and secure.
- **Keep it confidential.** Password-protected Secure Print and Encrypted Hard Disk ensure that your data and documents remain solely yours.

Unprecedented Ease of Use

- **Xerox® Global Print Driver®.** This print driver is truly universal. One single driver enables IT administrators to install, upgrade, and manage Xerox® and non-Xerox® devices. The core features and functionality are the same across all devices, simplifying use for end-users. Faster proficiency and fewer mistakes reduce support calls while also simplifying print services management.
- **Network management made easy.** Get remote device monitoring and troubleshooting using Xerox® CentreWare® IS Embedded Web Server and CentreWare Web, as well as third party management systems. In addition, automatic email alerts notify administrators or users of events that require attention, such as low toner levels.
- **Streamline the process.** Print directly from a USB memory drive or scan and store for convenient printing later – no computer needed. The intuitive icon-based colour touch screen not only supports capacitive swipe, but gives users easy instructions and help screens that make the entire process effortless.
- **Universal Address Book.** This time saver allows import/export of address books from other Xerox® products, saving significant time during initial setup as well as ongoing maintenance.

The compact design of the WorkCentre 4265 saves space and reduces energy consumption while never sacrificing the power you've come to expect from Xerox.

Minimise Costs

- Save paper with automatic two-sided copying and printing.
- Avoid extra printing with Fax Forward to Email.
- Separate toner cartridge and imaging unit consumables means you will be able to maximise the life of each while also decreasing overall supply costs.
- Reduce your utility bill with Energy Save Mode.

Maximise Time

- The compact size allows the device to be located conveniently within reach unlike a centralised Tabloid- / A3-size multifunction printer.
- Create a dedicated, easy-to-locate scan button directly on the colour touch screen interface and assign the Single Touch Scan button its own scanning work flow for fast document distribution and archiving.
- The Print Around feature automatically holds any job missing resources (such as a different paper size), and all other jobs in the queue will be processed as usual. Your document will print and your email and fax will be sent with no delay.
- Access multiple functions simultaneously; interrupt a print job to make a copy, or scan while printing or receiving an inbound fax.
- Our dual head scanner facilitates single-pass, two-sided scanning, and our class-leading advanced file compression dramatically reduces file sizes.

*Fax is optional on the WorkCentre 4265/S



The intuitive display guides you with easily recognisable icons for print, copy, scan fax or email, as well as 1-touch services and any custom solution installed.



Powerful Scanning Solutions

- **Scan to email** lets you route files to email recipients directly from the touch screen.
- **Network scanning** uses convenient templates to send scans to predefined locations.
- **Copy to hard drive** lets you copy files to the device's hard drive for easy retrieval.
- **Scan to USB** sends scanned images directly onto a portable USB storage device.

- 1 100-sheet Single-pass Duplex Automatic Document Feeder scans two-sided documents in sizes up to 8.5 x 14 in. / 216 x 356 mm.
- 2 USB direct printing/scanning lets you save to or print directly from any USB memory drive.
- 3 Full 8.5 x 14 in. / 216 x 356 mm platen glass allows you to scan documents without removing staples.
- 4 100-sheet adjustable Multipurpose Tray.
- 5 520-sheet Tray 1 / Optional 520-sheet Tray.
- 6 2,100 sheet High Capacity Feeder boosts total paper capacity up to 3,240 sheets.
- 7 320 GB internal hard drive lets you handle more tasks at the device. Use the Save Print feature to keep frequently used documents available for quick printing on the go.
- 8 Advanced faxing capabilities include Embedded Fax and LAN Fax (for paperless faxing right from your desktop), plus Secure Fax Receive and Fax Forward to Email.
- 9 500-sheet stacker/stapler with 50-sheet stapling (single-position).
- 10 The capacitive colour touch UI supports swipe and is intuitive for any user familiar with smart phones or tablets.

Xerox® WorkCentre™ 4265

Device Specifications		WorkCentre 4265/S	WorkCentre 4265/X	WorkCentre 4265/XF
Speed		Up to 55 ppm letter / Up to 53 ppm A4		
Duty Cycle ¹		Up to 250,000 pages / month		
Hard Drive / Processor / Memory		320 GB / 1 GHz / 2 GB		
Connectivity		10/100/1000Base-TX Ethernet, High-Speed USB 2.0, Optional Wireless 802.11b/g/n		
Copy and Print				
Copy and Print Resolution		Copy: Up to 600 x 600 dpi; Print: Up to 1200 x 1200 enhanced image quality		
First-print-out Time (as fast as)		Copy: As fast as 5 seconds; Print: As fast as 8 seconds		
Page Description Languages		Adobe® PostScript® 3 compatibility, PCL® 5c/e / PCL 6 emulations, XML Paper Specification (XPS®)		
Print Features		Booklet Printing, Proof Print, Skip Blank Pages, N-up, Collation, Scaling, Reduce/Enlarge, Fit to Page, Covers, Custom-size Pages, Delay Print, Banner Sheet, Print from USB		
Mobile Printing		Apple® AirPrint™, Web Printing Service, Xerox® Mobile Print (Optional), Xerox® Mobile Print Cloud (Optional), Xerox® PrintBack		
Scan	Standard	Scan to Home, Scan to Computer via SMB, Scan to Mailbox, Scan to Email, Scan to Folder, Scan to SMB, FTP, SFTP, Client, Scan to Network, Scan to HTTP, Scan to HTTPS, XPS, PDF/A, Image-only PDF, JPEG, Single-and Multi-page TIFF, Scan to USB Memory Device, TWAIN Support		
	Optional	Xerox® Scan to PC Desktop® SE and Professional, numerous solutions available		
Fax	Optional		Embedded Fax ² , LAN Fax, Server Fax	
Security	Standard	802.1X, Convenience Authentication, Kerberos Authentication (Unix / Linux / Windows ADS), LDAP Authentication (Secure LDAP), Local PIN Based Guest Login, Simple Authentication (one account with user name and Password), SMB Authentication (ADS), SMTP User Credentials via Kerberos, SMTP User Credentials via SMB (NTLM), Scan to Email with Authentication, Access Controls, User Permissions, Secure Print, Secure Fax Receive, SNMP v3, IPv6, SSL, SMTP over SSL, Smart Card Kit (CAC/PIV), USB port disablement, Audit Log, FIPS 140-2 Encryption, 256-bit Hard Disk Encryption, Image Overwrite, Software Verification Test, IP Filtering, HTTPS, SFTP, Common Criteria Certification (ISO 15408)		
Accounting	Standard	Xerox® Standard Accounting (Copy, Print, Scan, Fax, Email)		
	Optional	Equitrac Express®, Equitrac Office®, YSoft® SafeQ®, Network Accounting Enablement, other network accounting solutions available		
Paper Input	Standard	Duplex Automatic Document Feeder: 100 sheets; Custom sizes: 5.7 x 5.7 in. to 8.5 x 14 in. / 145 x 145 mm to 216 x 356 mm Bypass Tray: 100 sheets; Custom sizes: 3.9 x 5.8 in. to 8.5 x 14 in. / 98 x 148 mm to 216 x 356 mm Tray 1: 520 sheets; Custom sizes: 3.9 x 5.8 in. to 8.5 x 14 in. / 99 x 147 mm to 216 x 356 mm		
	Optional	Optional		Tray 2: 520 sheets; Custom sizes: 3.9 x 5.8 in. to 8.5 x 14 in. / 99 x 147 mm to 216 x 356 mm High Capacity Feeder: 2,100 sheets; Custom sizes: 5.8 x 8.3 in. to 8.5 x 14 in. / 148 x 210 mm to 216 x 356 mm
Total Capacity (Std. / max.)		620 / 3,240 sheets		3,240 / 3,240 sheets
Paper Output	Standard	500 sheets, automatic two-sided		
Finishing		Optional		Finisher: 500-sheet tray, 50-sheet stapling
Warranty		One-year on-site warranty (geography dependent)		

¹ Maximum volume capacity expected in any one month. Not expected to be sustained on a regular basis; ² Requires analogue phone line

Device Management

Xerox® CentreWare® Internet Services, Xerox® CentreWare® Web, Low supplies email alerts
Print Drivers
Windows® XP/2003 Server/2008 Server/2012 Server/Vista/7/8/9, Mac OS® 10.5 and higher, Oracle® Solaris 9, 10, Redhat® Enterprise 4, 5, Linux®, Fedora® Core 15-17, HP-UX® 11iv2, IBM® AIX® 5, openSUSE® 11, 12, Ubuntu®, Xerox® Global Print Driver®, Xerox® Mobile Express Driver®

Media Handling

Duplex Automatic Document Feeder: 12.5 to 28 lb. bond / 50 to 105 gsm; Bypass Tray and Tray 1: 16 lb. bond to 43 lb. bond / 60 to 163 gsm; Tray 2 (Optional): 16 lb. bond to 43 lb. bond / 60 to 163 gsm; High Capacity Feeder: 16 lb. bond to 32 lb. bond / 60 to 120 gsm

Media Types

Plain, Thin Paper, Punched, Letterhead, Card Stock, Recycled, Bond, Labels, Pre-printed, Envelopes, Transparencies

For a complete list, visit www.xerox.com.

Dimensions (W x D x H)

WorkCentre 4265/S: 24.5 x 20.1 x 24.6 in. / 621 x 511 x 624 mm, Weight: 93.3 lb. / 42.32 kg
WorkCentre 4265/X: 24.5 x 20.1 x 24.6 in. / 621 x 511 x 624 mm, Weight: 93.6 lb. / 42.44 kg
WorkCentre 4265/XF: 39 x 25.5 x 45 in. / 990 x 647 x 1,143 mm, Weight: 203.6 lb. / 92.34 kg

Certifications

FCC Part 15, Class A, FCC Part 68, CE Mark applicable to Directives 2006/95/EC, 2004/108/EC 2011/65/EU and 1999/5/EC, UL 60950-1/CSA 60950-1-07, 2nd Edition, EAC, ENERGY STAR® qualified, GS Mark and Blue Angel certification per Ral UZ-171 for Germany, NOM, Ukraine, EPEAT, Canadian EcoLogo, India BIS Registration, Chile Energy and Safety registration

Supplies Recycling Programme

Consumables for the WorkCentre 4265 are part of the Xerox Green World Alliance Supplies Recycling Programme. For more information, please visit the Green World Alliance website at www.xerox.com/gwa.

What Comes in the Box

- WorkCentre 4265 Multifunction Printer
- Starter Toner Cartridge (10,000 print capacity*)
- Drum Cartridge (100,000 yield**)
- Installation Guide, Quick Use Guide, Documentation and Driver CD (Drivers, User Manual, System Admin Guide)
- Power Cable
- Fax Cord (WorkCentre 4265/X and XF)

Supplies

Standard Toner Cartridge (approx. 10,000)*	106R03105
High Capacity Toner Cartridge (approx. 25,000)*	106R02735
Extra High Capacity Toner Cartridge (approx. 50,000)*	106R03103
Drum Cartridge (approx. 100,000 pages)**	113R00776
Staple Cartridge (3 boxes of 5,000 each)	008R12941

Routine Maintenance Items

110V Fuser Maintenance Kit (250,000 pages)**	115R00086
220V Fuser Maintenance Kit (250,000 pages)**	115R00087

Bias Transfer Roll Maintenance Kit

(125,000 pages)** 108R01266

Feed Roll Maintenance Kit (250,000 pages)** 108R01267

Options

Network Accounting Enablement 098S04928

Network Fax Server Enablement 098S04931

Fax Kit (Universal) 097N02154

520-sheet Paper Tray 097N01524

4-Tray Stand (IOT + 3 additional trays) 097S03678

2-Tray Stand (IOT + 1 additional tray) 097S03677

2100-sheet High Capacity Feeder 097N01684

Finisher 097N02155

Foreign Device Interface (FDI) 097N01676

Common Access Card Enablement Kit 497K09950

Wireless Kit 097N02156

* Average standard pages. Declared Yield in accordance with ISO/IEC19752. Yield will vary based on image, area coverage and print mode

** Average standard pages. Yield will vary depending on job run length, media size and orientation.

For more detailed specifications, go to www.xerox.com/office/WC4265Specs.

©2014 Xerox Corporation. All rights reserved. Xerox®, Xerox and Design®, CentreWare®, Global Print Driver®, Mobile Express Driver®, Scan to PC Desktop®, WorkCentre and Xerox Extensible Interface Platform® are trademarks of Xerox Corporation in the United States and/or other countries. As an ENERGY STAR® partner, Xerox Corporation has determined that this product meets the ENERGY STAR guidelines for energy efficiency. ENERGY STAR and the ENERGY STAR mark are registered U.S. marks. Product information and/or specifications are subject to change without notice. 10/14 BR10775

W4XBR-021A

