

HPE ProLiant DL20 Gen9 Server

Compact, versatile, and efficient



Is the HPE DL20 Gen9 Server right for my business?

This compact 1P server with enterprise-class capabilities is a great fit for:

- **Small- to medium-sized businesses and enterprises**—This compact single-socket rack server delivers performance, data protection, and ease-of-use suitable for most small- to medium-sized workloads—all in an install-anywhere compact form factor and a competitive price point. You can also select from a wide range of HPE Qualified Options, allowing you to leverage expandability and reliability features.
- **Tier 2 and 3 service providers**—ProLiant DL20 Gen9 Servers make it possible for you to scale out quickly and affordably to respond to changing business needs. The rack now provides cheaper drive options for environments that call for an affordable solution that can be easily ripped and replaced.

An ideal fit for small- to medium-sized businesses, enterprises, and service providers

The dense and compact HPE ProLiant DL20 Gen9 Server, powered by the latest Intel® Xeon®, Intel Core™ i3, and Pentium® processors, blends enterprise-class capabilities with great value. Outstanding configuration flexibility caters to a wide variety of requirements at an affordable price point—making it an ideal platform for small- to medium-sized businesses, service providers, and enterprises running IT infrastructure workload, Web, or edge-of-network applications in space-constrained environments. The DL20 Gen9 Server offers a range of HPE Qualified Options—from drives to power supplies to storage controllers to HPE FlexibleLOM for next-generation network capability for faster data transfer—helping you find the right configuration and just the right price.

Data protection, ease of use, reliability, and performance

The server's data protection features include optional redundant power supplies, DDR4 memory, enhanced error handling, HPE Smart Array RAID mirroring and striping capabilities, and flash-backed write cache (FBWC) up to 4 GB. FBWC protects data by capturing and holding it indefinitely in the event of a power loss, equipment failure, human error, or virus attacks. Layering on business continuity features, the HPE Insight Online option with HPE Insight Remote Support provides 24x7 remote monitoring and anywhere, anytime access to your IT and support status to get your business up and running quickly if something goes wrong.

The server also features extreme ease of use, starting with a short depth chassis for ease of deployment and mobility. Embedded HPE iLO4 management provides easy-to-use tools for deploying, managing, and troubleshooting servers—ideal for those with limited IT resources. A wide choice of Intel processors with up to 64 GB of DDR4 ECC memory helps you handle a variety of workload demands. And the latest ProLiant DL20 Gen9 Servers, powered by Intel Xeon processors, consume up to 29 percent less power,¹ which, combined with the efficient redundant power supply option,² provides you with an ENERGY STAR®-certified power saving solution.

¹ Compared to the previous generation

² RPS option available only on SFF chassis

Technical specifications

In the following table, bold text denotes new features or functions, as compared to the HPE ProLiant DL320e Gen8 v2 Server.

HPE ProLiant DL20 Gen9 SERVER	
Compute	Choose from one Intel Xeon E3-1200 v5 Series , 4-core; one Intel Pentium, 2-core; or one Intel Core i3, 2-core PCIe 3.0, Up to 2 PCIe 3.0 slots
Memory	4 x DDR4 , up to 2133 MHz (64 GB max)
Storage	HPE Dynamic Smart Array B140i, HPE Smart Array Controller P440 with FBWC, and HPE Smart HBA H240
HPE SmartDrives	2LFF Non hot-Plug & Hot Plug (SAS/SATA); 4SFF Hot Plug (SAS/SATA)
Networking	2 x 1GbE embedded Ethernet Adapter and FlexibleLOM
VGA/serial/USB ports/SD	2 rear USB 3.0, 2 front USB 2.0, and 1 internal USB 3.0
GPU support	One single-width, half-length GPU (optional)
On-premise management	HPE iLO 4 (Advanced/Scale-out/Essentials Optional)
On-cloud management	HPE Insight Online with enhanced mobile application
On-system management	HPE iLO 4, HPE Intelligent Provisioning, HPE System Update Manager (SUM), HPE RESTful Interface Tool
Power and cooling	Standard 290 W power supply; 900 W AC 240VDC redundant power supply (optional for SFF chassis only) [*]
Industry compliance	ASHRAE A3, ENERGY STAR (only on RPS configuration models)
Form factor/chassis depth	Rack (1U) 15.05" (ear to rear)
Warranty (parts/labor/onsite)	1/1/1
System ROM	UEFI and Legacy BIOS

^{*} RPS available in January 2016

Hewlett Packard Enterprise Services

Let Hewlett Packard Enterprise help guide you to the New Style of Business. HPE Technology Services delivers confidence, reduces risk, and helps you realize greater agility and stability.

- Our consulting services provide advice and guidance to safely move your workloads to newer technologies.
- HPE implementation and installation services enable faster, more reliable startup of your new ProLiant Gen9 servers, and our support portfolio allows you to get connected and back to business fast.
- We recommend HPE Proactive Care for ProLiant Gen9 servers to prevent issues and resolve problems quickly and efficiently.
- HPE Foundation Care provides a choice of coverage levels and response times for hardware and software support.
- HPE Datacenter Care enables you to operate and evolve your IT environment at a lower cost and with more agility, including our Flexible Capacity Service to acquire IT without impacting capital budget.
- Our support technology lets you tap into the knowledge of millions of devices and thousands of experts to stay informed and in control, anywhere, any time.

Learn more at hpe.com/servers/dl20gen9



hpe.com/servers/dl20gen9



Sign up for updates

★ Rate this document



© Copyright 2015 Hewlett Packard Enterprise Development LP. The information contained herein is subject to change without notice. The only warranties for Hewlett Packard Enterprise products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. Hewlett Packard Enterprise shall not be liable for technical or editorial errors or omissions contained herein.

ENERGY STAR is a registered mark owned by the U.S. government. Intel Xeon, Pentium, and Intel Core are trademarks of Intel Corporation in the U.S. and other countries. SD is a trademark or registered trademark of SD-3C in the United States and other countries or both.

4AA6-2663ENN, December 2015