

# HP HD Pro 42-in Scanner

Produce exceptional, high-quality results with HP's high-production HD color scanner



## GROW—Expand your capabilities and opportunities

- Reproduce everything from technical documents to graphics—even damaged originals—with CCD scanning technology
- Create large-format color and monochrome scans/copies up to 42-inches (1067-mm) wide, even on thick media<sup>1</sup>
- Produce incredibly accurate and high-quality scans with 1200 dpi optical resolution
- Easily share and collaborate—scan to HP SmartStream software,<sup>2</sup> email, USB, network folders, and HDDs

## ACCELERATE—Speed up production and drive results

- Accomplish more with incredible speeds—scan 6 inches/sec in color, 13 inches/sec in monochrome<sup>3</sup>
- Experience an uninterrupted workflow with advanced touchscreen controller that enables ultra-fast processing
- Save time operating and managing your scanner with an intuitive user interface that requires less clicks to final scan
- Be more productive with improved compression options, unlimited presets, multi-page PDFs, and collating

## OPTIMIZE—Integrate and secure your workflow

- Enjoy seamless integration with HP PageWide XL and HP DesignJet printers; rely on a single support solution
- Avoid reprints—large touchscreen to preview, enhance images; post-scan editing with HP SmartStream software<sup>2</sup>
- Protect your data with advanced security—set up a password to scan to USB and access advanced settings
- Build a multifunction system<sup>4</sup>—save space with the adjustable stand and easily control output destinations<sup>5</sup>

## Learn more at

[hp.com/go/pagewidexl/sdproscanner](http://hp.com/go/pagewidexl/sdproscanner)  
[hp.com/go/designjethdproscanner](http://hp.com/go/designjethdproscanner)



## Technical specifications

<b>Scan and copy</b>	Scan speed <sup>3</sup>	Color: 15 cm/sec (6 in/sec) Grayscale: 33 cm/sec (13 in/sec)
Enhanced resolution	9600 dpi	
Optical resolution	1200 dpi	
Imaging technology	CCD scanning technology	
Accuracy	+/- 0.1% +/- 1 pixel	
Data capture (color/mono)	48-bit/16-bit	
Maximum scan width	1067 mm (42 in)	
Supported file formats	PDF, TIFF, JPEG, JPEG2000, DWF, CALS (B&W), multi-page PDF generation	
Scan to	File, email, USB, HDD, network folder, FTP, print	
Settings	Type of original/preset, color mode, resolution (dpi), batch, single/multi-page, file format, customizable file naming, customizable default settings, de-skew, image crop and align preview, enlarge/reduce, blueprint, lightness, saturation and RGB controls, white point and black point adjust, sharpen/blur, background removal, invert, mirror, accounting	
Copier specific settings	Print mode, output size, paper type, copies, page order, collate, printer output destination (folder, stacker, bin), <sup>5</sup> folding style selection, <sup>7</sup> paneling, tiling, nesting, reprint	
Maximum scan size <sup>8</sup>	0.91 x 26 m (36 x 1204 in); 0.6 x 37.9 m (24 x 1491 in); 0.3 x 75.8 m (12 x 2991 in)	
Maximum copies	Unlimited	
Batch	Available with scan and copy	
Preview	Scan, copy and print after previewing the original in the advanced touchscreen controller	
Size detection	Automatic width detection. Manual size selection also possible	
<b>Applications</b>	Digital fine art, Graphics design, Line drawings, Maps, Orthophotos, Photos, Renderings, Presentations	
<b>Media</b>	Handling	Straight-through scan paper path for sheet and cardboard originals, adjustable paper pressure for very thin media. Face-down, front entry, rear exit, rewind to front, use document return guide for front-return. Automatic high adjustment of scanner bridge for thick originals up to 15mm thickness
Types <sup>9</sup>	Non-abrasive paper, vellum, Mylar, sepia, blueprints, plastic, film, plastic laminate, foam board, cardboard, newspaper, tracing paper. Varying condition documents: old, delicate, folded, creased, crumpled, damaged originals	
Size	Up to 1118 mm (44 in) wide	
Thickness	Up to 15 mm (0.6 in)	
<b>Processor</b>	Intel Core i7	
<b>Memory</b>	4 GB <sup>10</sup> memory, 500 GB <sup>11</sup> hard disk	
<b>Connectivity</b>	Interfaces (standard)	Dual Gigabit Ethernet (1000Base-T), Hi-Speed USB 3.0 certified
	Drivers (included)	Windows drivers for compatible HP PageWide XL and HP DesignJet printers
<b>User Interface</b>	15.6-inch (396-mm) large touchscreen to preview and enhance images	
<b>Languages</b>	Chinese (simplified), Chinese (traditional), Dutch, English, French, German, Italian, Japanese, Korean, Portuguese, Spanish	
<b>Dimensions (w x d x h)</b>	Scanner	1510 x 720 x 1370 mm (59 x 28 x 54 in)
	Shipping	1500 x 680 x 710 mm (59 x 27 x 28 in)
<b>Weight</b>	Scanner	71 kg (157 lb)
	Shipping	90 kg (198 lb)
<b>What's in the box</b>	HP HD Pro 42-in Scanner, stand, touchscreen (panel PC), quick reference guide, media guides, setup poster, copy/scan software, documentation software, Ethernet cables (x2), power cords	
<b>Environmental ranges</b>	Operating temperature	5 to 40°C (41 to 104°F)
	Storage temperature	-25 to 55°C (-13 to 131°F)
	Operating humidity	20 to 80% RH
<b>Acoustic</b>	Sound pressure	47 dB(A) (scanning); <22 dB(A) (ready); <22 dB(A) (sleep)
	Sound power	6.4 B(A) (scanning); <3.9 B(A) (ready); <3.9 B(A) (sleep)
<b>Power</b>	Consumption	109 watts (scanning); 98 watts (ready); <3 watts (sleep)
	Requirements	Input voltage (auto ranging): 100 to 240 VAC (+/-10%), 50/60 Hz, 5 A max

<sup>1</sup> Up to 0.6-inches (15-mm) thickness.<sup>2</sup> HP SmartStream is a professional software solution that supports HP PageWide XL printer series and HP DesignJet Production printers.<sup>3</sup> Monochrome scanning: A1/D image with black text graphics at 200 dpi; color scanning: A1/D fully-inked color image at 200 dpi, 24-bit RGB.<sup>4</sup> Scanner can be placed above the following HP DesignJet printers: HP DesignJet 500/510/T520/T610/T620/T790/T1100/T1200/T1500/T7100/Z6100 Printer series; HP DesignJet T795/T1300 Printers; HP DesignJet Z2100/Z3100/Z3200 Photo Printer series; HP DesignJet Z5200 Photo Printer; HP DesignJet Z5400 PostScript Printer; HP DesignJet Z6200/Z6800 Photo Production Printers; HP DesignJet T7200/Z6600 Production Printers.<sup>5</sup> Output destinations when copying --such as folders and stackers --are available for the HP PageWide XL 8000 Printer, HP PageWide XL 5000 Printer series, HP DesignJet T200 Production Printer, HP DesignJet T7100 Printer series, HP DesignJet T3500 Production MFP, HP DesignJet T2500 Multifunction Printer series, HP DesignJet T1500 Printer series,

<b>Certification</b>	Safety	USA and Canada (UL certified), EU (LVD and EN 60950-1 compliant), Russia (EAC), Singapore (PSB), China (CCC), Argentina (IRAM), Mexico (NYPE), Korea (KC)
Electro-magnetic	Compliance for Class A ITE products: EU (EMC Directive), USA (FCC Rules), Canada (ICES), Australia (ACMA), New Zealand (RSM), China (CCC), Japan (VCCI), Korea (MSIP), Taiwan (BSMI), Russia (EAC)	
Environmental	ENERGY STAR, WEEE, RoHS (EU, China, Korea, India), REACH, EPEAT Bronze	

**Warranty** One-year limited hardware warranty

## Ordering information

<b>Product</b>	G6H51B	HP HD Pro 42-in Scanner
----------------	--------	-------------------------

## Service and support

<b>Product</b>	U4PS5E	HP 3 year Next Business Day Onsite Support with DMR
	U4PS6E	HP 5 year Next Business Day Onsite Support with DMR
	U4PS7PE	HP 1 year Post Warranty Onsite Support with DMR
	U4PS8PE	HP 2 year Post Warranty Onsite Support with DMR
	U1XV4E	HP Preventive Maintenance Service

## Supported printers

HP PageWide XL 8000 Printer	HP DesignJet T1500 Printer series
HP PageWide XL 8000 Blueprint <sup>12</sup>	HP DesignJet T1300 Printer
HP PageWide XL 5000 Printer series	HP DesignJet T1200 Printer series
HP PageWide XL 5000 Blueprint <sup>12</sup>	HP DesignJet T1120 Printer series
HP PageWide XL 4000/4500 Printer series	HP DesignJet T1100 Printer series
HP DesignJet Z6800 Photo Production Printer	HP DesignJet T930 Printer series
HP DesignJet Z6600 Production Printer	HP DesignJet T920 Printer series
HP DesignJet Z6200 Photo Production Printer	HP DesignJet T830 Multifunction Printer
HP DesignJet Z6100 Printer series	HP DesignJet T795 Printer
HP DesignJet Z5400 PostScript® Printer	HP DesignJet T790 Printer series
HP DesignJet Z5200 Photo Printer	HP DesignJet T770 Printer series
HP DesignJet Z3200 Photo Printer series	HP DesignJet T730 Printer
HP DesignJet Z3100 Photo Printer series	HP DesignJet T610/T620 Printer series
HP DesignJet Z2100 Photo Printer series	HP DesignJet T520 Printer series
HP DesignJet T2200 Production Printer	HP DesignJet S5500 Printer series
HP DesignJet T7100 Printer series	HP DesignJet 5100 Printer
HP DesignJet T3500 Production MFP	HP DesignJet 4500/4520 Printer series
HP DesignJet T2530 Multifunction Printer series	HP DesignJet 4000/4020 Printer series
HP DesignJet T2500 Multifunction Printer series	HP DesignJet 1050C/1055CM Printer series
HP DesignJet T2300 Multifunction Printer series	HP DesignJet 510 Printer series
HP DesignJet T1530 Printer series	HP DesignJet 500 Printer series

## Eco Highlights

• ENERGY STAR® qualified and EPEAT Bronze registered<sup>6</sup>

**Please recycle large-format printing hardware and printing supplies.**

**Find out how at our website**

[hp.com/ecosolutions](http://hp.com/ecosolutions)

© Copyright 2014, 2016 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

ENERGY STAR and the ENERGY STAR mark are registered U.S. marks. Windows is a U.S. registered trademark of Microsoft Corporation. Mac and the Mac logo are trademarks of Apple Computer, Inc., registered in the U.S. and other countries.

4AA5-1487ENW, January 2016, Rev. 2



and HP DesignJet T920 Printer series.

<sup>6</sup> EPEAT registered where applicable and/or supported. See [epeat.com](http://epeat.com) for registration status by country.

<sup>7</sup> Only available when folder accessory is available and supported by the HP large-format printer.

<sup>8</sup> The HP HD Pro 42-in Scanner maximum scan length is 21.6 m (852 in) for a 42-in width image. The maximum scan size is measured using a color original at 200 dpi and TIFF file format. For grayscale or black-and-white originals, the maximum scan length is longer in all cases.

<sup>9</sup> The HP HD Pro 42-in Scanner does not support the following types of media: plywood, stone plates, metal plates or abrasive, dirty, rough, sharp edged, metal clamped, or burned surfaces or transparencies.

<sup>10</sup> Scanning process.

<sup>11</sup> For scan job storage, Win7 OS and recovery system.

<sup>12</sup> Only available in Asia Pacific countries with the exception of Korea, Singapore, Australia, and New Zealand.