

X402

Bright projection

- Bright projection – 4200 ANSI lumens
- XGA resolution, 20,000:1 contrast ratio, HDMI input
- Crestron RoomView® – RJ45 control and monitoring
- Lightweight and portable, carry bag included



X402

Project bright, vibrant widescreen presentations any time of day. Designed for meeting rooms and classrooms, the X402 boasts a long lamp life and energy-saving features which provide a low overall cost of ownership.

This projector has a built-in speaker, networking capabilities, Full 3D technology and can be easily connected via a HDMI cable, giving a clear projected image with sound. The lightweight projector can be installed or taken on the move in the handy carry bag for off-site meetings.

High Contrast

Add more depth to your image with a high contrast projector; with brighter whites and ultra-rich blacks, images come alive and text appears crisp and clear - ideal for business and education applications.



2000:1 Contrast Ratio



20,000:1 Contrast Ratio

Full 3D

Optoma projectors can display true 3D content from almost any 3D source, including 3D Blu-ray players, 3D broadcasting and the latest generation games consoles. Support for 144Hz rapid refresh rate provides ultra-smooth flicker free images.



Integrated Speaker

The built-in speaker offers excellent audio support. Easy to set up without the need for costly external speakers

Eco+



Eco+ technology brings together high contrast, improved lamp life and energy saving features that are easy to use while reducing power consumption.

Energy Saving

Using the specially designed lamp modes, you can reduce the power consumption by up to 70%. Each mode also has a positive effect on the lamp life, while lowering the total cost of ownership and reducing maintenance.

Auto Power Off

There may be instances when the projector is left running when not in use. To help save energy, the "Auto Power Off" feature automatically turns off the projector after a set period of time if it is not being used

Eco AV Mute

Stay in control of your presentation with Eco AV mute. Direct your audience's attention away from the screen by blanking the image when no longer needed. This also reduces the power consumption by up to 70%, further prolonging the life of your lamp.



Eco AV mute off
100% power consumption



Eco AV mute on
25% power consumption

Long Lamp Life

Reduce the number of lamp changes with lamp life of up to 7000 hours.

Remote Mouse & Laser

Keep your audience's attention focused on the right things using the simple, yet powerful remote with USB mouse control and built in laser pointer.

Networking and Control

Featuring a wide range of options you can control and monitor the projector remotely.

- RS232 - Optoma projector's come with an extensive set of RS232 commands making it simple and easy to manage using any control system.
- AMX Compatibility - Dynamic discovery protocol is incorporated into the projector allowing for easy installation with AMX control systems.
- LAN Control
 - Using the compatible RoomView® software you can power on/off, monitor, manage and control up to 250 projectors at the same time from any computer.
 - Schedule the projectors to power on/off.
 - Control and alter the projector settings using the simple web browser.
 - Emergency text broadcast capabilities for urgent or important announcements.



Amazing Colors

For vibrant, natural looking images, Optoma projectors incorporate BrilliantColor™ multi-colour processing technology.




Quick Resume

This feature allows the projector to be instantly powered on again, if it is accidentally switched off.

Quick Resume

On



Wireless Presenting (optional extra)

Making presentations couldn't be easier using the optional wireless features of the WPS Wireless Adapter (sold separately) - you can connect and display presentations wirelessly from a laptop, PC or mobile device.

X402 Specification

Display Technology	Single 0.55" XGA DC3 DMD chip DLP® Technology by Texas Instruments
Native Resolution	XGA 1024 x 768
Brightness	4200 ANSI Lumens
Contrast Ratio	20,000:1
Noise Level (Eco mode)	31dB
Weight	2.49
I/O Connectors	HDMI (1.4a 3D support), 2 x VGA (YPbPr/RGB), S-Video, Composite, 2 x Audio In 3.5mm, Audio Out 3.5mm, VGA Out, RS232, USB mouse/service, RJ45
Maximum Resolution	UXGA (1600 x 1200)
Computer Compatibility	WUXGA, UXGA, SXGA+, WXGA+, WXGA, SXGA, XGA, SVGA, VGAresized
Video Compatibility	NTSC, PAL, SECAM, SDTV (480i), EDTV (480p), HDTV (720p, 1080i/p)
Displayable Colors	1.07 Billion
Projection Lens	F/2.4~2.66; f=18.2~21.8mm, 1.2x Manual Zoom and focus
Throw Ratio	1.6–1.92 (distance/width)
Projection Screen Size	30" to 307" (0.76– 7.8m)
Projection Distance	3.9'–32.8' (1.2–10 m)
Zoom Type	1.2x Manual
Aspect Ratio	4:3 Native, 16:9 Compatible
Offset	115%
Horizontal Scan Rate	15.375–91.4KHz
Vertical Scan Rate	24–85Hz, 120Hz
Lamp Type	260W
Lamp Life ² Bright	3000 (hrs)
Keystone Correction	± 40° Vertical
Audio	10-Watt speaker
Dimensions (W x H x D)	12.4" x 3.0" x 8.8" (314 x 101 x 224 mm)
Remote Control	IR remote mouse control with laser
Power Supply	AC Input 100–240V, 50–60Hz, auto-switching
Power Consumption	Max 306W (Normal), Min 257W (Eco+), <0.5W (standby-ECO)
Operating Conditions	41–104°F (5–40°C), 85% max humidity
Uniformity	>80%
Security	Security bar, Kensington lock, password protection
Standard Accessories	AC power cord, VGA to VGA cable, remote control, batteries for remote, multilingual CD-ROM user's manual, quick start card, carrying case and warranty card
Optional Accessories	DLP® Link™ 3D glasses, wireless, ceiling mount, Optoma screens, RF 3D emitter, RF 3D glasses
RoHS	Compliant
3D Support	Full 3D - The 3D features of Optoma projectors can only be used with compatible 3D content. Typical applications include use with 3D educational or 3D design and modelling systems. 3D TV broadcast systems, (SKY in the UK), Blu-ray 3D™ and 3D games from the Sony® PS3 or Microsoft® Xbox 360 are now supported as part of the HDMI v1.4a specification.
3D Compatibility	Supports all HDMI 1.4a mandatory 3D formats (Frame pack, side-by-side, top-bottom) and up converts frame rate from 60Hz to 120Hz or 24Hz to 144Hz (i.e 60 or 72 frames per eye). 3D glasses are needed and are sold separately. Refer to user manual for details
On Screen Display	Complete on-screen menu, adjustments
Optional Wireless	Yes
Warranty	3-Year Optoma Express Service, 1-Year Lamp
Projection method	Front, rear, ceiling mount, table top



Optoma USA

3178 Laurelview Ct., Fremont, CA 94538

www.optomausa.com

¹Brightness and lamp lifetime will vary depending on the selected projector mode, environmental conditions and usage. As is common with all lamp based projectors, brightness will decrease over the lamp lifetime. ²Typical lamp life achieved through testing and will vary according to operational use and environmental conditions. 8,000 hours lamp life is based on a daily cycle that reflects projector usage

in a typical education environment. Details of this cycle are available on request. ³Optoma guarantees that in normal use, Optoma DLP® colour quality will be indistinguishable from when new. Exclusions: (a) Guarantee is voided if the projector is subject to damage through misuse. (b) Guarantee may be void in industrial or commercial entertainment environments where dust or smoke is excessive (c) Guarantee will not apply if lamp brightness is below 50% due to wear or if the projector is not working due to other faults. (d) Over time worn lamps within all projector types will show a slight colour variance. Copyright © 2013, Optoma Europe Ltd. All other product names and company names used herein are for identification purposes only and may be trademarks or registered trademarks of their respective owners. Errors and omissions excepted, all specifications are subject to change without notice. DLP®, BrilliantColor™ and the DLP logo are registered trademarks of Texas Instruments. All images of products are for representation purposes only. Whilst every care is taken to provide accurate images of our products, actual products may differ slightly. Some product images may have been digitally altered by us to add an Optoma logo to the front panel. Optoma reserves the right to amend or alter actual product, product specifications or product images without notice. Some images may be simulated.

18/04/2015 06:25