


## Serie | 6 Ovens

### Oven

#### HBA53B150B



### The built-in oven that assists with its cleaning: you have to clean less thanks to reduced soiling during the cooking process.

- EcoClean liners absorb and break down dirt and grime so less cleaning is required from you.
- Our unique 3D Hotair system evenly heats all 3 cooking levels for even cooking results, you don't even have to turn the food.
- **Energy efficiency class A:** Best baking results with low energy consumption.

#### Technical Data

|   |   |  |
|---|---|--|
| Color / Material Front :  | Stainless steel   |  |
| Construction type :   | Built-in  |  |
| Integrated Cleaning system :                                      | Catalytic all sides   |  |
| Required niche size for installation (HxWxD) :                    | 575-597 x 560-568 x 550   |  |
| Dimensions of the product (mm) :                                  | 595 x 595 x 548   |  |
| Dimensions of the packed product (HxWxD) (mm) :                   | 670 x 670 x 680   |  |
| Control Panel Material :  | Stainless steel   |  |
| Door Material :   | Glass   |  |
| Net weight (kg) :   | 37.0  |  |
| Usable volume of cavity (l) :                                     | 66  |  |
| Cooking method :  | Bottom heat, Conventional heat, Defrost, Full width variable grill, Half width variable grill, Hot Air, Hot air grilling, Pizza setting |  |
| First cavity material :   | Enamelled   |  |
| Temperature control :   | mechanical  |  |
| Number of interior lights :                                       | 1   |  |
| Approval certificates :   | CE, VDE   |  |
| Length of electrical supply cord (cm) :                           | 150   |  |
| EAN code :  | 4242002898339   |  |
| Number of cavities (2010/30/EC) :                                 | 1   |  |
| Energy efficiency class - NEW (2010/30/EC) :                      | A   |  |
| Energy consumption per cycle conventional (2010/30/EC) :          | 0.95  |  |
| Energy consumption per cycle forced air convection (2010/30/EC) : | 0.82  |  |
| Energy efficiency index (2010/30/EC) :                            | 98.8  |  |
| Electrical connection rating (W) :                                | 2990  |  |
| Current (A) :   | 13  |  |
| Voltage (V) :   | 220-240   |  |
| Frequency (Hz) :  | 50; 60  |  |
| Plug type :   | no plug   |  |

#### Included accessories

- 1 x insert grid
- 2 x combination grid
- 1 x universal pan



4 242002 898339

#### Optional accessories

HEZ338357 : 3 level telescopic shelf rails,full ext.

## Serie | 6 Ovens

### Oven

#### HBA53B150B

**The built-in oven that assists with its cleaning: you have to clean less thanks to reduced soiling during the cooking process.**

#### Key Information

- Mechanical control
- Drop down door

#### Design

- Rotary dial, 2 retractable control dials
- Straight bar handle

#### Features

- Electronic clock timer
- 1 interior light
- Control panel lock
- Cavity inner surface: Enamel
- Smooth enamelled oven interior
- 5 shelf positions
- Full glass inner door

#### Programmes/functions


- Oven with 8 heating methods: 3D hot air, conventional top and bottom heat, Hotair grilling, pizza function, bottom heat, defrost
- Fast heat

#### Performance/technical information

- Cavity volume: 66 litre
- Integral cooling fan
- Stainless-steel fan
- Length of mains cable: 150 cm
- Total connected load electric: 2.99 KW
- Appliance dimension (hxwxd): 595 mm x 595 mm x 548 mm
- Niche dimension (hxwxd): 575 mm - 597 mm x 560 mm - 568 mm x 550 mm
- Please reference the built-in dimensions provided in the installation drawing
- Maximum window temperature 40° C
- Energy efficiency rating (acc. EU Nr. 65/2014):  
Energy consumption per cycle in conventional mode: 98.8  
Energy consumption per cycle in fan-forced convection mode: 0.82 kWh  
Number of cavities: 1  
Heat source: electrical  
Cavity volume: 66 litre


#### Standard accessories

- 1 x insert grid, 2 x combination grid, 1 x universal pan

**Serie | 6 Ovens**
**Oven**
**HBA53B150B**



\*20 mm for metal fascias

Measurements in mm



\*20 mm for metal fascias

Measurements in mm



Dimensions in mm