


ZAN2211CI

Product	Model No PNC Name Bar code (EAN 13)	ZAN2211CI 801 409 498 AirSpeed Lite 'SuctionSeal' Pet & Car 7332543895304	Energy Label	B
Categorisation	Group Product Class Technology Supply Unit	Floorcare Upright Bagless HUP	Carpet	B
USP's	Main USP or Key Feature 2nd USP or Key Feature 3rd USP or Key Feature	Lightweight Powerful suction Pet mini turbo nozzle	Hardfloor	D
			Dust Re-emission	G
			Noise db	89db
			Annual Energy Con kwh	29.8kWh
Energy Labeling	Energy Rating Carpet Pickup Hardfloor Pickup Dust Re-emission	B B D G		
Design/Controls	Colour Carpet Height Adjustment Speed Settings	Ice White/Blue Yes 1		
Technical Specifications	Voltage V Frequency Hz Power Output W/V Guarantee Period Yrs Thermal Cut Out Power Cord Length Mtrs Hose Length Action Radius Cyclone technology Dims Product Only (WxDxH)mm Weight Product Only Kgs Dust Capacity Ltrs	230v 50Hz 1000w 1 Yr Yes 8m 2.4m Stretch Multi Cyclonic 3.8Kgs 1.5L		
Vacuum Performance	Energy cons, Wh Suction Power AirWatts Motor Filter Type Exhaust Filter Type	180AW Sponge Filter - Washable Hygine Filter - Washable		
Nozzles	Nozzle Floor Integr. access. Mini Turbo Nozzle Hose	Dusting brush Crevice nozzle Yes - Risor Visor Stretch 2.4m		
Spares - Original	Motor Filter Ref No Exhasust Filter Ref No Dustbag ref. n° Drive Belt Ref No Dustbag Ref No	4055244851 EF35 ZED90		
Packaging & Logistics Single Package	Net weight, kg Gross Weight, kgs Packaging Dims (WxDxH)mm Package volume, Ltrs Stacking level Package type Palette, units per Palette, layers per Palette Dims (WxDxH)mm Palette, max height mm 20ft Container Units 40ft Container Units 40ft HQ Container Units Intrastat code Country Of Origin	4.4Kgs 5.7Kgs 341 x 209 x 668 48L 1 Cardboard Corrugated 1200 x 800 x 160 2000 528 1122 1422 85081100 China		
Logistics			<p>ZAN2211CI Ice White/Blue</p>	

SuctionSeal Technology

All-Surface Suction Plates concentrates airflow for deep cleaning suction power. As you move across carpet, hardwood or tile floors the plates raise and lower, creating a seal to maximize airflow for powerful cleaning performance. Whether it's surface dirt or debris hiding in crevices, it's sucked up and away without any scattering.



AirSpeed Technology

Unlike other vacuums, AirSpeed® Technology has two smooth tubes, featuring limited bends and turns. This allows more air to pass through the vacuum. The direct air path from floor to cup, decreases the distance for dirt to travel, which increases the amount of airflow for powerful suction.

Never Loses Suction

Zanussi has engineered SuctionSeal™ to provide maximum suction power longer than other types of vacuums.* Tested to strict industry standards, Zanussi's multi-cyclonic dust cup system never loses suction and maintains power as you vacuum your home.