

DS-2CD4A65F-IZ(H)(S)


6MP Smart IP Outdoor Bullet Camera



Key Features

- Up to 3072 x 2048 high resolution
- WDR, 3D DNR
- Multi-video streams
- On-board storage, up to 64GB
- Up to 50m IR range
- Motorized VF lens with Smart Focus
- IP67
- Audio/Alarm IO (-S)
- Smart Heater (-H)

Dimensions



Available models

DS-2CD4A65F-IZ
DS-2CD4A65F-IZH
DS-2CD4A65F-IZS
DS-2CD4A65F-IZHS

DS-2CD4A65F-IZ(H)(S)	
Camera	
Image sensor	1/1.8" Progressive Scan CMOS
Min. illumination	0.01 Lux @ (F1.2, AGC ON), 0 Lux with IR 0.014 Lux @ (F1.4, AGC ON), 0 Lux with IR
Shutter time	1 s to 1/100,000 s
Slow Shutter	Support
Lens	2.8-12mm @ F1.4, 94.5°-30.5°
Auto-iris	DC drive
Day & night	Electronic (-I: IR cut filter with auto switch)
Digital noise reduction	3D DNR
Wide dynamic range	Support
Compression standard	
Video compression	H.264 / MJPEG
H.264 Type	Baseline Profile / Main Profile / High Profile
Video Bit Rate	32 Kbps – 16 Mbps
Audio Compression	G.711/G.722.1/G.726/MP2L2
Audio Bit Rate	64Kbps(G.711) / 16Kbps(G.722.1) / 16Kbps(G.726) / 32-128Kbps(MP2L2)
Image	
Max. Resolution	3072 x 2048
	50Hz: 25fps (3072x2048, 3072x1728, 2560x2048, 2560x1920, 2048x1536, 1920x1080, 1280x720)
Frame rate	60Hz: 25fps (3072x2048), 30fps (3072x1728, 2560x2048, 2560x1920, 2048x1536, 1920x1080, 1280x720)
Third Stream	Independent with Main Stream and Sub Stream, up to 50Hz: 25fps @ 1280 x 720 ; 60Hz: 30fps @ 1280 x 720
BLC	Support
Smart Defog	Support
Image Setting	Saturation, Brightness, Contrast adjustable by client software or web browser
Day/Night Switch	Auto/Schedule/Triggered by Alarm In
ROI	Support
Network	
Network storage	NAS (Support NFS, SMB/CIFS)
Alarm Trigger	Intrusion detection, Defocus detection, Motion detection, Face detection, Dynamic analysis, Tampering alarm, Network disconnect, IP address conflict, Storage exception
Protocols	TCP/IP, ICMP, HTTP, HTTPS, FTP, DHCP, DNS, DDNS, RTP, RTSP, RTCP, PPPoE, NTP, UPnP, SMTP, SNMP, IGMP, 802.1X, QoS, IPv6, Bonjour
Security	User Authentication, Watermark, IP address filtering, Anonymous access
Standard	ONVIF, PSIA, CGI, ISAPI
Interface	
Communication Interface	1 RJ45 10M/100M Ethernet port
Video Output	1Vp-p composite output (75 Ω/BNC)
On-board storage	Built-in Micro SD/SDHC/SDXC slot, up to 64 GB
Reset Button	Yes
Smart Feature-set	
Behavior Analysis	Line crossing detection, Intrusion detection, Region entrance, Region exiting, Unattended baggage, Object removal
Line Crossing Detection	Cross a pre-defined virtual line
Intrusion Detection	Enter and loiter in a pre-defined virtual region
Region Entrance	Enter a pre-defined virtual region from the outside place
Region Exiting	Exit from a pre-defined virtual region
Unattended Baggage	Objects left over in the pre-defined region such as the baggage, purse, dangerous materials
Object Removal	Objects removed from the pre-defined region, such as the exhibits on display.
Exception Detections	Scene change detection, Sudden audio increase/decrease detection, Audio loss detection, Defocus detection
Recognition	Face detection recognition
Statistics	Object Counting (Entrance and Exit object number is accounted and showed on screen in real time)
General	
Operating conditions	-30 °C – 60 °C (-22 °F – 140 °F), -H: -40 °C – 60 °C (-40 °F – 140 °F), Humidity 95% or less (non-condensing)
Power supply	12V DC ± 10%, PoE (802.3at)
Protection Level	IP67
IR Distance	20 to 50m
Power Consumption	12W MAX
Dimensions	100x103.9x311.8 mm
Weight	2000g

* "S" series support 1-ch audio in/out interface, 1-ch alarm in/out interface and 1-ch RS-485 interface

PTZ DOME

NETWORK

ANALOG

DVR

NVR

ATM DVR

VIDEO ENCODER

CARD

NETWORK STORAGE