

## Strong enough for every day.

Lenovo N22 laptops are rugged, durable, and adaptable to any setting. Plus, their thin and light design makes them the perfect solution for on-the-go work, school, and play.



### Rugged and Durable

- **Drop resistant** – built to withstand bumps and accidental drops from up to 70cm (2.3 feet)
  - **Stronger, thicker** rear cover and a frame around the screen, sides and corners absorb the force of bumps and reduce damage when dropped.
- **Reinforcement** around ports and hinges adds durability that stands up to student wear and tear
- **Anti-peel keys** resist removal by students
- **Water resistant keyboard** channels spills (up to 330ml) away from the electronics to prevent damage.
- **Sealed touchpad** protects the electronics from moisture and spills
- **Non-slip texture** hides wear and scratches and helps the students to better grip the device
- **Fanless design** eliminates the need for bottom vents which helps keep debris away from the electronics

### Designed for Education

- **Rotatable camera** gives students flexibility in how they capture images and video.
  - A student can rotate the camera away to record a science experiment or capture video of other students doing a skit or presenting a report.
  - A student can rotate the camera up to closely examine an object.
  - The integrated microphone also rotates with the camera to better capture sound.
- The **anti-glare screen** produces less reflection under fluorescent lights and near classroom windows, reducing student eyestrain.
- With **up to 10 hours of battery life**, teachers and students can work where they need to without a power cord. The battery is serviceable and can be replaced by school IT.

## Performance

### Processor

Intel® Braswell N3050, N3060

### Operating System

Windows OS

### Memory

2GB, 4GB or 8GB option

### Camera

Rotatable 1.0MP 720p HD camera can be angled to capture images, video and support scientific inquiry activities

### Storage

Up to 128GB SSD

### Audio

Stereo sound

Integrated microphone rotates with camera

### Battery

Up to 10 hours of battery life (40whr)

Serviceable battery – can be replaced by school IT

## Design

### Display

11.6" 1366x768 resolution HD LED anti-glare screen

### Dimensions

300mm x 215mm x 22.1 mm  
11.8 inches x 8.5 inches x 0.88 inches

### Weight

1.29kg (2.8lbs)

## Connectivity

### Ports

2-in-1 card reader (SD/MMC)

Full HDMI

2x USB 2.0

1x USB 3.0

Kensington security lock slot

### Communication

Intel Dual Band AC 7260 adapter (WIFI 802.11 ac/a/b/g/n 2x2 with Bluetooth 4.0)

## Warranty

1 Year Limited Mail-In Warranty

## Optional Service Upgrades

- Priority Technical Support
- Warranty Upgrades
- Accidental Damage Protection

## Recommended Accessories & Services



Sleeve

4X40E48909



Essential Backpack

4X40E77329



Security Cable Lock

57Y4303

Upgrade to 3-year depot warranty with Accidental Damage Protection

P/N 5PS0H71476