



# Planar PXL2470MW-WH

## 24" LCD Monitor

The Planar® PXL2470MW-WH 24" widescreen LED backlit LCD monitor features a wide viewing angle, DisplayPort and HDMI inputs, and external power supply. The Planar PXL2470MW fits seamlessly into home, office, healthcare, and digital signage environments.



SPECIFICATION	DETAIL
<b>Product Name</b>	PXL2470MW-WH
<b>Planar Part Number</b>	997-8265-00
<b>Viewable Size</b>	23.6" diagonal (20.52" horizontal x 11.54" vertical)
<b>Aspect Ratio</b>	16:9
<b>Contrast Ratio (typ)</b>	1000:1
<b>Viewing Angle (typ)</b>	178° Horizontal and 178° Vertical (Specified at CR>10:1)
<b>Response Time (typ)</b>	5 ms (GTG)
<b>Brightness (Typical)</b>	250 cd/m <sup>2</sup>
<b>Display Type</b>	Edge-Lit LED LCD Active Matrix Flat Panel Display (TFT)
<b>Display Resolution</b>	1920 x 1080, full HD
<b>Tilt Range</b>	-5° to +20°
<b>Palette</b>	16.7 million colors
<b>Pixel Pitch</b>	0.2715 mm
<b>Refresh Rate</b>	55~76 Hz (60 Hz recommended)
<b>Dimensions (W x H x D)</b>	22.10" x 15.73" x 7.85" (561.3 mm x 399.6 mm x 199.3 mm)
<b>Dimensions without Stand</b>	22.10" x 13.12" x 1.58" (561.3 mm x 333.2 mm x 40.2 mm)
<b>Panel Depth</b>	1.58" (40.2 mm)
<b>Display Weight</b>	7.8 lb (3.53 kg); Weight without stand: 7.1 lb (3.2 kg)
<b>Shipping weight</b>	11.3 lb (5.1 kg)
<b>Video Inputs</b>	HDMI, DisplayPort, VGA
<b>Audio Output</b>	1W x 2, headphone out

<b>External Connections</b>	HDMI 19-pin, DisplayPort 20-pin, VGA 15-pin, 3.5 mm audio in, 3.5mm headphone out
<b>Compatibility</b>	PC and Mac® (adapter may be required for Mac)
<b>Power Supply</b>	External (DC power)
<b>Power Consumption (max)</b>	26 Watt Typical (<0.5 Watt standby)
<b>Power Requirements</b>	AC 100/240 VAC
<b>VESA Compatible/Location</b>	Built-in 100 mm VESA, back
<b>Product Approvals</b>	FCC-B, CE, UL/cUL, RoHS
<b>Service and Support</b>	3-Year Customer First™ Warranty featuring FREE 2-Day Advance Replacement (US only)
<b>Options / Features</b>	White, Wide color consistent viewing angle, Uniform bezel, Discreet branding, Anti-glare coating, Multi-language display, On screen display (OSD), Kensington® Security Slot
<b>In the Box</b>	PXL2470MW-WH 23.6" white LED LCD Monitor, 12V DC AC Adaptor, Power Cord, VGA Cable, DisplayPort Cable, Audio Cable, User's Guide
<b>UPC</b>	8 10689 00309 0

For more information, please visit [www.planar.com](http://www.planar.com)

*Specifications are subject to change without notice.*

*Specification Report Date: 3/1/2016*

*© Copyright 2016 Planar Systems, Inc. All rights reserved*