

# Multimedia Presentation Projector EH415e



## IDEAL PROJECTOR FOR CLASSROOMS, BOARDROOMS AND THE HOUSE OF WORSHIP



Full 1080p HD resolution with HDMI 1.4a connectivity and LAN Control



Bright 4200 lumens image with 15,000:1 contrast ratio makes it ideal for large screen applications



Lens shift for installation flexibility



Full 3D compatibility for audience captivating immersive presentations




1.5x zoom ratio for greater installation placement flexibility



Full 3D  
1080p

WIDESCREEN  
16:9  
ENHANCED



The Optoma EH415e is the perfect projector solution for medium to large size conference rooms, small auditoriums, higher education lecture halls and houses of worship.

With a powerful 4200 lumens, 1920x1200 WUXGA resolution and a stunning 15,000:1 contrast ratio the EH415e delivers bright large-screen presentations with fantastic image clarity, outstanding color accuracy and incredibly sharp image detail.

Engineered for today's digital world, the EH415e provides 2 HDMI v1.4a ports, vertical lens shift for installation flexibility and RJ45 for LAN command and control.

## CONNECTIVITY (May require optional accessories)



Computers



Smart  
Phones



Tablets



3D Blu-ray/DVD Players  
Set Top Boxes



Camcorders



Game  
Consoles



Digital  
Cameras



Roku®



Apple TV®



Chromecast™

## MULTIMEDIA PROJECTOR – EH415e

### OPTICAL/TECHNICAL SPECIFICATIONS

Display Technology	Single 0.65" DC3 DMD DLP® Technology by Texas Instruments™
Native Resolution	Full HD (1920x1080)
Maximum Resolution	WUXGA (1920x1200)
Brightness (Typical)	4200 lumens
Contrast Ratio	15,000:1 (full on/full off)
Displayable Colors	1.07 Billion
Lamp Life* and Type	7000/4000/3000 (Bright+Dynamic/ECO/Bright)
Projection Method	Front, rear, ceiling mount, table top
Keystone Correction	±40° Vertical
Uniformity	>80%
Aspect Ratio	16:9, 4:3, LBX, Native, Auto
Throw Ratio	1.46-2.02 (distance/width)
Projection Distance	3.9'-32.8' (1.2-10 m)
Image Size (Diagonal)	25.32" -317.99" (0.64-8.08 m)
Projection Lens	F=2.42-2.97, 1.5x manual zoom and focus
Lens Shift Offset	Vertical: 110% ~ 124%
Digital Zoom	0.8 ~ 2.0
Typical Offset	111.5%
Audio	10-Watt speaker
Noise Level	37dB min
Remote Control	IR remote mouse with laser
Operating Conditions	41-104°F (5-40°C), 85% max humidity
Power Supply	AC Input 100-240V, 50-60Hz, auto-switching
Power Consumption	Max 290W (Normal), Min 230W (Eco+), <0.5 (standby-ECO)
High Altitude	Operating Temp @ Sea Level to 10000 feet = 23C (max); must manually switch to high altitude mode @ 5000 feet & above (using OSD)

### COMPATIBILITY SPECIFICATIONS


Computer Compatibility	UXGA, SXGA+, WXGA+, WXGA, SXGA, XGA, SVGA, VGA, WUXGA, HDTV 720p, HDTV 1080p
Video Compatibility	NTSC, PAL, SECAM, SDTV (480i), EDTV (480p), HDTV (720p, 1080i, 1080p)
3D Compatibility <sup>†</sup>	Supports all HDMI 1.4a mandatory 3D formats (Frame pack, side-by-side, top-bottom) and up converts frame rate from 60Hz to 120Hz or 24Hz to 144Hz (i.e 60 or 72 frames per eye). 3D glasses are needed and are sold separately. Refer to user manual for details.
Vertical Scan Rate	24-85Hz, 120Hz
Horizontal Scan Rate	15.375-91.146KHz
User Controls	Complete on-screen menu adjustments in 27 languages
I/O Connection Ports	2x HDMI v1.4a, VGA-in, VGA-out, composite video, Dual Analog RCA 3.5mm audio-in, 3.5mm audio-out, 12V trigger, RS-232C, RJ45 & USB-B, 2x HDMI v1.4a, USB-A (Power Only), USB-B mini (service only)

### PHYSICAL SPECIFICATIONS

Security	Kensington® lock port, security bar and keypad lock
Weight	5.95 lb (2.7 kg)
Dimensions (W x H x D)	11.26" x 4.88" x 10.43" (286 x 124 x 265 mm)

\*Lamp-life is dependent on many factors, including lamp mode, display mode, usage, environmental conditions and more. Lamp brightness can decrease over time.

†3D content can be viewed with DLP Link active shutter glasses when projector is used with a compatible 3D source (Blu-Ray Player, Cable/Satellite Box, Game Console and more). Please visit [www.OptomaUSA.com](http://www.OptomaUSA.com) for more information.



### Warranty

3-Year Optoma Express Service, 1-Year on Lamp

### What's In the Box

EH415e projector, AC power cord, VGA to VGA cable, remote control, batteries for remote, carrying case, lens cap, CD-ROM user's manual, quick start card and warranty card

### Optional Accessories

Wireless VGA dongle, universal ceiling mount, Optoma screens, DLP®Link™ 3D glasses, wireless HDMI system and Cat6 HDBaseT

### Accessory Part Numbers

Lamp: 5811118924-SOT	Wireless VGA dongle: BI-EXTBG03
Remote: 5041846800	DLP® Link™ 3D glasses: BG-ZD301
Wireless HDMI system: WHD200	Single-Cat6 HDBaseT kit: EVBMN-M110
Universal ceiling mount: BM-5001U	Universal ceiling mount: OCM818W-RU
	Universal ceiling mount (with extensional pole): OCM815W

UPC 796435 41 950 9

[www.OptomaUSA.com](http://www.OptomaUSA.com)

Copyright © 2015 Optoma Technology, Inc. DLP® and the DLP logo are registered trademarks of Texas Instruments™. All other trademarks are the property of their respective owners. All specifications subject to change at any time. 06302015