



CC8130(HS)

Height Strip Network Camera




1MP · Height Strip Housing · Eye-level Panoramic View · Flexible Viewing Direction · PoE

The VIVOTEK CC8130(HS) is a height-strip network camera equipped with a 180 degree wide-angle lens, delivering clear images for reliable facial recognition. An ideal installation height of 170cm (5.5 ft) allows the CC8130(HS) to capture clear facial images at eye view, even when the subject is wearing a hat or hood. In addition, the plug and play design makes the CC8130(HS) installation simple and rapid. Combining low-profile and high-level features, the CC8130(HS) is ideal for discreet indoor applications, such as retail, banks, restaurants, small businesses and particularly in cashier areas.

To dramatically reduce file sizes and conserve valuable network bandwidth, the CC8130(HS) supports the industry-standard H.264 compression technology. Combined with the ST7501 multi-lingual 32-channel recording software, users can quickly and easily set up an IP surveillance system that's simple to operate but hard to beat.

Key Features

- 1-Megapixel CMOS Sensor
- 30 fps @ 1280x800
- 180° Horizontal Panoramic View
- Height Strip Design for Eye-level Video Surveillance
- Real-time H.264 and MJPEG Compression (Dual Codec)
- Built-in IEEE 802.3af Compliant PoE
- Easy Installation



The CC8130(HS) provides clearer facial images than ceiling-mounted devices, even when subjects wear hats or hoods.

CC8130(HS)


Ceiling-mounted Camera



Banks



Retail




Entrance



180°

180° Panoramic View

Technical Specifications

Model	CC8130(HS): 1MP in black/silver housing with U.S. or Metric dimensions	Intelligent Video	
System Information			
CPU	Multimedia SoC (System-on-Chip)	Video Motion Detection	Triple-window video motion detection
Flash	128 MB	Alarm Triggers	Video motion detection, manual trigger, periodical trigger, system boot, recording notify
RAM			
RAM	128 MB	Alarm Events	Event notification using HTTP, SMTP, FTP and NAS server File upload via HTTP, SMTP, FTP and NAS server
Camera Features			
Image Sensor	1/4" Progressive CMOS	General	
Maximum Resolution	1280x800	Connectors	RJ-45 for Network/PoE connection
Lens Type	Fixed-focal	LED Indicator	System power and status indicator
Focal Length	f = 1.3 mm	Power Input	IEEE 802.3af PoE Class 1
Aperture	F1.8	Power Consumption	Max. 3.8W
Field of View	180° (Horizontal) 100° (Vertical) 180° (Diagonal)	Dimensions	27.66 (D) x 49.3 (W) x 866.4 (H) mm
Shutter Time	1/5 sec. to 1/32,000 sec.	Weight	Net: 94 g
Minimum Illumination	0.4 Lux @ F1.8 (Color)	Safety Certifications	CE, LVD, FCC Class B, VCCI, C-Tick
Pan/tilt/zoom Functionalities	ePTZ: 4x digital zoom IE plug-in	Operating Temperature	0°C ~ 40°C (32°F ~ 104°F)
Video			
Compression	H.264 & MJPEG	Warranty	24 months
Maximum Frame Rate	30 fps @ 1280x800 In both compression modes	System Requirements	
Maximum Streams	2 simultaneous streams	Operating System	Microsoft Windows 7/Vista/XP/2000
S/N Ratio	Above 56 dB	Web Browser	Mozilla Firefox 7~10 (streaming only) Internet Explorer 7/8/9/10
Video Streaming	Adjustable resolution, quality and bitrate	Other Players	VLC: 1.1.11 or above QuickTime: 7 or above
Image Settings	Adjustable image size, quality and bit rate Time stamp, text overlay, flip & mirror Configurable brightness, contrast, saturation, sharpness, white balance, exposure control, gain, backlight compensation, privacy masks Scheduled profile settings	Included Accessories	
Network			
Users	Live viewing for up to 10 clients	CD	User's manual, quick installation guide, Installation Wizard 2, ST7501 32-channel recording software
Protocols	IPv4, IPv6, TCP/IP, HTTP, HTTPS, UPnP, RTSP/RTP/RTCP, IGMP, SMTP, FTP, DHCP, NTP, DNS, DDNS, PPPoE, CoS, QoS, SNMP, 802.1X	Others	Quick installation guide, warranty card, camera stand, screw pack
Interface	10 Base-T/100 BaseTX Ethernet (RJ-45) *It is highly recommended to use standard CAT5e & CAT6 cables which are compliant with the 3P/ETL standard.	Dimensions	
ONVIF	Supported, specification available at www.onvif.org		

All specifications are subject to change without notice. Copyright © VIVOTEK INC. All rights reserved.

Ver. 7



VIVOTEK INC.

6F, No.192, Lien-Cheng Rd., Chung-Ho,
New Taipei City, 235, Taiwan, R.O.C.
T: +886-2-82455282 F: +886-2-82455532
E: sales@vivotek.com

VIVOTEK USA

2050 Ringwood Avenue,
San Jose, CA 95131
T: 408-773-8686 F: 408-773-8298
E: salesusa@vivotek.com

VIVOTEK Europe

Randstad 22-133, 1316BW Almere,
The Netherlands
T: +31(0)36-5298-434
E: saleseurope@vivotek.com

VIVOTEK India

602, Best sky Tower, Plot No. F-5,
Netaji Subhash Place, Pitam Pura, Delhi-110 034
T: +91-11-45137465
E: salesindia@vivotek.com