

QTH7211B

Camera Type	Bullet
Camera Technology	BNC HD
Image Sensor Size	1/4
Image Sensor Type	CMOS
Image Resolution	720P High Definition
Megapixels (digital)	1
Effective Pixels	1280x720
Lens Size	2.8mm
Angle of View	65 to 70
IR Cut Filter	Yes



**Use with
QTH Series
BNC HD DVRs**

NIGHT VISION

IR LEDs	36
Infrared Wavelength	850nm
Min Lux Illumination	.001Lux (Color) / 0Lux with IR on (B&W)
Night Vision Range	Up to 100 ft

ADDITIONAL IMAGE FEATURES

Auto Iris	No
On Screen Display	No
Backlight Compensation	No
Electronic Shutter	1/60-1/100,000s
Gain Control	Auto
Wide Dynamic Range	No
Noise Reduction	No

REMOTE MONITORING

Use as Standalone	No
Compatible Mobile Devices	None, depends on DVR connected to
Compatible Systems	QTH Series BNC HD DVRs

PHYSICAL ATTRIBUTES

Weatherproof	Yes
IP Rating	IP66
Body Construction	Metal
Mounting Hardware	Screws
Weight	17.5 oz
Dimensions without bracket	2.55" w x 3.25" d x 2.85" h
Dimensions with bracket	2.5" w x 6.4" d x 2.85" h
Operating Temperature	14° to 120° F

PTZ

Horizontal Rotation	Not applicable
Vertical Tilt	Not applicable
Preset and Cruise Patterns	Not applicable

AUDIO

Audio Range	Not applicable
Audio Microphone	Not applicable

CONNECTIVITY

Connector Types	BNC
Other Connections	2.1mm power
Wireless	No

POWER

Power Supply	12V 500mA
Power Consumption	<5W (LEDs ON)