

WT46W490GB

iSensoric Heatpump dryer



A++

iSensoric heat-pump dryer with selfCleaning condenser for high energy efficiency throughout the life of the dryer.

- ✓ Cleaning the condenser becomes obsolete and energy consumption remains constantly low thanks to the self-cleaning system.
- ✓ A++: dries very efficient.
- ✓ 40 minute quick dry programme: Rapid 40.
- ✓ Special drying programme for functional textiles such as sportswear and outdoor clothing.
- ✓ Sensor-controlled autoDry technology prevents laundry from shrinking when being dried.

Features

Technical Data

Built-in / Free-standing : Free-standing
 Removable top : No
 Door hinge : Right
 Color / Material body : White
 Length electrical supply cord (cm) : 145.0
 Height with worktop (mm) : 842
 Dimensions of the product (mm) : 842 x 598 x 652
 Net weight (kg) : 51.0
 Drum volume (l) : 112
 Fluorinated greenhouse gases : Yes
 Type of refrigerant : R134A
 Hermetically sealed equipment : Yes
 Connection Rating (W) : 1000
 Current (A) : 10
 Voltage (V) : 220-240
 Frequency (Hz) : 50
 Approval certificates : CE, VDE
 Drying process : automatic
 Capacity cotton (kg) - NEW (2010/30/EC) : 9.0
 Standard cotton programme : Cotton cupboard dry
 Energy efficiency class (2010/30/EC) : A++
 Energy consumption electric dryer, full load - NEW (2010/30/EC) (kWh) : 2.01
 Standard cotton programme time at full load (min) : 226
 Energy consumption electric dryer, partial load - NEW (2010/30/EC) (kWh) : 1.14
 Standard cotton programme time at partial load (min) : 131
 Weighted annual energy consumption, electric dryer - NEW (2010/30/EC) (kWh) : 258.0
 Power consumption in off-mode (W) - NEW (2010/30/EC) : 0.10
 Power consumption in left-on mode (W) - NEW (2010/30/EC) : 0.75
 Duration of the left-on mode - NEW (2012/30/EC) (min) : 0
 Weighted programme time (min) : 172
 Condensation efficiency class - NEW (2010/30/EC) : B
 Average condensation efficiency full load (%) : 86
 Average condensation efficiency partial load (%) : 86
 Weighted condensation efficiency (%) : 86



4 242003 765050

Optional accessories

WTZ20410 Connection set
 WTZ11400 Stacking kit with pull-out shelf
 WMZ20600 Wool in basket - accessory
 WMZ20500 Platform with pull-out

WT46W490GB

iSensoric

Heatpump dryer

Features

engine power and consumption

- Capacity: 9 kg
- Dryer type: Condenser with heat pump technology
- Energy efficiency class: A++
- Energy consumption 258.0 kWh per year, based on 160 drying cycles of the standard cotton programme at full and partial load, and the consumption of the low-power modes. Actual energy consumption per cycle will depend on how the appliance is used
- Energy consumption of the standard cotton programme at full load 2.01 kWh and energy consumption of the standard cotton programme at half load 1.14 kWh
- power consumption in off-mode 0.1 W and in left-on mode 0.75 W
- Duration of left-on mode: 0 min
- The programme Cotton cupboard dry used at full and partial load is the standard drying programme to which the information in the label and the fiche relates, this programme is suitable for drying normal wet cotton laundry and is the most efficient programme in terms of energy consumption for cotton.
- Weighted programme time of the standard cotton programme at full and partial load: 172 min.
- Programme time of the standard cotton programme at full load 226 min and programme time of the standard cotton programme at partial load 131 min.
- Condensation efficiency class B on a scale from G (least efficient) to A (most efficient).<
- Average condensation efficiency of the standard cotton programme at full load 86 % and average condensation efficiency of the standard cotton programme at partial load 86 %.
- Weighted condensation efficiency for the standard cotton programme at full and partial load: 86 %.
- Noise level: 65 dB (A) re 1 pW

programmes

- Special programmes: woollen finish, mix, outdoor, towels, timaprogramm warm, timaprogramm cold, lingerie, shirts/blouses

options

- Anti crease cycle 120 min at the end of the programme
- Touch control buttons: Low Heat, Buzzer, less ironing, end time delay, programme length, start/pause, Fine-tuning of drying aim, 24 h end time delay

comfort and safety

- selfCleaning Condenser
-
- autoDry technology
- soft dial
- Large LED-Display for remaining time and 24 h end time delay, programme status indication, special functions.
- Air flow Drying System: Big Stainless steel drum with textile care structure, soft design paddles
-
- anti-vibration Design: more stability and quietness
- Drum interior light: LED
- Childproof
- Buzzer to indicate the end of cycle
- Glass door with frame silver-white
- comfort lock
- Door hinge: right-hand
- Drain Set

technical information

- Dimensions (H x W x D): 84.2 cm x 59.8 cm x 65.2 cm
- slide-under at height of 85 cm