


CADENCE

Xenith

XS 693



6 x 9 in



TS PARAMETERS

FMS: 73.7 Hz	BL: 5.5 N/A
QMS: 1.64	SPL: 92 dB
QES: 0.99	VAS: 35.4 l
QTS: 0.62	RE: 3.6 Ohm
RES: 8.5 Ohm	RP: 5.1 Ohm
RMS: 5.1 kg/s	LP: 9.2 mH
CMS: 0.26 mm/N	CP: 896.6 μ F
MMS: 18.2 gr	LE: 0.3 mH
NREF: 1.38 %	

4 Ohm

400 Watts

Xenith Power

SPECIFICATIONS

Application: 3 - Way Speaker

Basket Type: Open Steel Basket

Cone: Black Plated Acrylic w/ Piano Finish

Tweeter: Extended Frequency Dome Tweeter

Surround Style: Butyl Rubber


Structure Weight: 70 oz.

Impedance: 4 Ohm

RMS / Peak Watts: 60 / 200

Frequency Response: 55Hz - 20KHz

SPL @ 1w/1m: 92dB



Cadence Acoustics

6519 Highway 9 North • Howell, NJ 07731
800.477.2328 • 732.370.5400 • fax: 732.370.5553 • www.cadencesound.com

