

## DS-7604NI-E1/4P and DS-7600NI-E2/8P (16P) series NVR

### Introduction:

DS-7600NI-E1/4P and DS-7600NI-E2/8P (16P) series NVR (Network Video Recorder) is a new generation recorder developed by Hikvision independently. Combined with multiple advanced technologies, such as audio and video decoding technology, embedded system technology, storage technology, network technology and intelligent technology. It can both work alone as a recorder and cooperate with other device to form a comprehensive surveillance system.

The DS-7600NI-E1/4P and DS-7600NI-E2/8P (16P) series NVR are widely applied in the areas of finance, public security, military, communication, transportation, education, etc.

### Available Models:


DS-7604NI-E1/4P;  
DS-7608NI-E2/8P, DS-7616NI-E2/8P, DS-7632NI-E2/8P  
DS-7616NI-E2/16P, DS-7632NI-E2/16P

### Main Features:


- Connectable to the third-party network cameras like like ACTI, Arecont, AXIS, Bosch, Brickcom, Canon, ONVIF, PANASONIC, Pelco, PSIA, SAMSUNG, SANYO, SONY, Vivotek and ZAVIO.
- 4/8/16/32 network cameras can be connected for different models.
- Support live view, storage, and playback of the connected camera with up to the resolution of 6 megapixels.
- Simultaneous HDMI and VGA outputs at up to 1920×1080 resolution.
- New GUI and support starting record with one key.
- Multiple recording types: manual, continuous, alarm, motion, motion | alarm, motion & alarm, and VCA.
- Realize instant playback for assigned channel during multi-channel display mode.
- Customization of tags, searching, and playing back by tags.
- Playback by sub-periods.
- Locking and unlocking record files.
- Support HDD quota mode; different capacity can be assigned to different channel.
- Up to 2 SATA hard disks can be connected with up to 6TB capacity for each.
- 1 self-adaptive 10M/100M/1000M network interface is provided.
- Up to 4/8/16 independent PoE network interfaces for different models.
- Support Hikvision DDNS (Dynamic Domain Name System).
- Support network detection, including network delay, packet loss, etc.
- Support VCA detection alarm and VCA search.



### Physical Interfaces:



DS-7600NI-E1/4P




DS-7600NI-E2/8P



The rear panel of DS-7616NI-E2/16P and DS-7632NI-E2/16P provides 16 independent 100 Mbps PoE network interfaces.

Index	Name
1	Power Supply
2	Audio In
3	HDMI Interface
4	LAN Network Interface
5	Audio Out
6	VGA Interface
7	USB Interface
8	Ground
9	Power Switch
10	Network Interfaces with PoE Function

### Typical Connections:



## Specifications:

Model		DS-7604NI-E1/4P	DS-7608NI-E2/8P
Video/Audio input	IP video input	4-ch	8-ch
	Two-way audio input	1-ch, RCA (2.0 Vp-p, 1kΩ)	
Network	Incoming bandwidth	40Mbps	80Mbps
	Outgoing bandwidth	80Mbps	
	Remote connection	32	128
Video/Audio output	Recording resolution	6MP/5MP/3MP/1080P/UXGA/720P/VGA/4CIF/DCIF/2CIF/CIF/QCIF	
	Frame rate	Main stream: 50 fps (P) / 60 fps (N)	
		Sub-stream: 50 fps (P) / 60 fps (N)	
	HDMI/VGA output	1-ch, resolution: 1920 × 1080 /60Hz, 1600 × 1200 /60Hz, 1280 × 1024 /60Hz, 1280 × 720 /60Hz, 1024 × 768 /60Hz	
	Audio output	1-ch, RCA (Linear, 1kΩ)	
Decoding	Live view / Playback resolution	6MP/5MP/3MP/1080P/UXGA/720P/VGA/4CIF/DCIF/2CIF/CIF/QCIF	
	Capability	4-ch@1080P	8-ch@720P, 6-ch@1080P
Hard disk	SATA	1 SATA interface for 1 HDD	2 SATA interfaces for 2 HDDs
	Capacity	Up to 6TB for each disk	
External interface	Network interface	1 RJ-45 10 /100 Mbps self-adaptive Ethernet interface	1 RJ-45 10 /1000 Mbps self-adaptive Ethernet interface
	USB interface	1 ×USB 2.0 and 1 ×USB 3.0	
	Alarm in/out (Optional)	4 / 1	
PoE	Interface	4 independent 100 Mbps PoE network interfaces	8 independent 100 Mbps PoE network interfaces
	Max. Power	50W	120W
	Supported standard	AF and AT	
General	Power supply	12V DC	
	Consumption (without hard disk and PoE)	≤10W	
	Working temperature	-10 °C ~ +55 °C (+14 °F ~ +131 °F)	
	Working humidity	10 % ~ 90 %	
	Chassis	1U chassis	19-inch rack-mounted 1U chassis
	Dimensions (W × D × H)	315 × 230 × 45mm (12.4" × 9.1" × 1.8")	445 × 290 × 45mm (17.5" × 11.4" × 1.8")
	Weight (without hard disk)	≤ 1 kg (2.2 lb)	

Model		DS-7616NI-E2/ 8P	DS-7632NI-E2/ 8P	DS-7616NI-E2/ 16P	DS-7632NI-E2/ 16P		
Video/Audio input	IP video input	16-ch	32-ch	16-ch	32-ch		
	Two-way audio input	1-ch, RCA (2.0 Vp-p, 1kΩ)					
Network	Incoming bandwidth	160Mbps					
	Outgoing bandwidth	80Mbps					
	Remote connection	128					
Video/Audio output	Recording resolution	6MP/5MP/3MP/1080P/UXGA/720P/VGA/4CIF/DCIF/2CIF/CIF/QCIF					
	Frame rate	Main stream: 50 fps (P) / 60 fps (N)					
		Sub-stream: 50 fps (P) / 60 fps (N)					
	HDMI/VGA output	1-ch, resolution: 1920 × 1080 /60Hz, 1600 × 1200 /60Hz, 1280 × 1024 /60Hz, 1280 × 720 /60Hz, 1024 × 768 /60Hz					
Decoding	Audio output	1-ch, RCA (Linear, 1kΩ)					
	Live view / Playback resolution	6MP/5MP/3MP/1080P/UXGA/720P/VGA/4CIF/DCIF/2CIF/CIF/QCIF					
	Capability	16-ch@4CIF, 12-ch@720P, 6-ch@1080P					
Hard disk	SATA	2 SATA interfaces for 2 HDDs					
	Capacity	Up to 6TB for each disk					
External interface	Network interface	1 RJ-45 10 /100 /1000 Mbps self-adaptive Ethernet interface					
	USB interface	1 ×USB 2.0 and 1 ×USB 3.0					
	Alarm in/out (Optional)	4 / 1					
PoE	Interface	8 independent 100 Mbps PoE network interfaces		16 independent 100 Mbps PoE network interfaces			
	Max. Power	120W		200W			
	Supported standard	AF and AT					
General	Power supply	100~240V AC					
	Consumption (without hard disk and PoE)	$\leq 10W$		$\leq 15W$			
	Working temperature	-10 °C ~ +55 °C (+14 °F~ +131 °F)					
	Working humidity	10 % ~ 90 %					
	Chassis	380 chassis					
	Dimensions (W × D × H)	380 × 290 × 48mm (15.0" × 11.4" × 1.9")					
	Weight (without hard disk)	$\leq 1$ kg (2.2 lb)					

**Note:**

The formula to calculate the incoming bandwidth and the IP camera connected is:  $A = B/(C+D)$ .

A refers to the number of IP camera you connected.

B refers to the value of the incoming bandwidth.

C refers to the bitrate value of the main stream of the connected IP camera.

And D refers to the bitrate value of the sub-stream of the connected IP camera.

**Example:** The incoming bandwidth of DS-7616NI-E2/8P NVR is 100Mbps and the IP camera to connect is with resolution of 1080P (1920\*1080) / 25 (30) fps. The bitrate for the main stream and sub-stream of the IP camera is set as 6Mbps and 1Mbps respectively.

In this example, B=100Mbps, C=6Mbps, D=1Mbps and  $A = B/(C+D) = 100 / (6+1) \approx 14$ . So the number of IP cameras can be connected with is 14.