

Product data sheet

Specifications



APC Smart-UPS On-Line, 8kVA/8kW, Rackmount 8U, 208V, 12x 5-20R+4x L6-20R+1x L6-30R NEMA, Network Card+SmartSlot, W/transformer 208V to 120V,W/rail kit

SRT8KRMXLT-5KTF

Overview

Lead time Usually in Stock


Main

Main Input Voltage	208 V
Product or Component Type	Uninterruptible power supply (UPS)
Main Output Voltage	120 V
Kw Rating	8000 W
Rated power in VA	8000 VA
output connection type	12 NEMA 5-20R 4 NEMA L6-20R 1 NEMA L6-30R
Output connector type	Hard Wire 3-wire (2PH + G) 1
number of rack unit	8U
Provided equipment	CD with software Documentation CD Installation guide Rack mounting hardware Rack Mounting brackets Rack Mounting support rails Temperature Probe USB cable Warranty card Web/SNMP Management Card
Range of Product	Smart-UPS On-Line

Batteries & Runtime

Run Time	View Runtime Graph
Efficiency	View Efficiency Graph
Battery Type	Lead-Acid battery
Included Battery Modules	0
Typical recharge time	1.5 h
RBC Quantity	1
Battery Voltage	+/-192 V (split battery referenced to neutral)
Battery Charge Power (Watts)	1136 W rated
Battery life	3...5 year(s)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Replacement battery	APCRBC140 
Extendable Run Time	1

General

Topology	Double Conversion Online
product web sub-family	High density
Number of power module free slots	0
Number of power module filled slots	0
Redundant	No

Physical

color	Black
Height	13.9 in (35.2 cm)
Width	17.008 in (43.2 cm)
Depth	28.1 in (71.5 cm)
Net Weight	340.99 lb(US) (154.67 kg)
Mounting Location	Front
Mounting preference	Lower
Mounting Mode	Rack-mounted
Two post mountable	0
USB compatible	Yes
Mounting position	Horizontal

Input

Input Frequency	40 - 70 Hz auto-sensing
Number of input connectors	1 Hard Wire 3-wire (2PH + G)
Efficiency at full load	100...275 V adjustable (half load)

Output

Maximum configurable power in VA	8000 VA
Max Configurable Power (Watts)	8000 W
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains
Waveform Type	Sine wave
Harmonic distortion	Less than 2%
Crest factor	3 : 1
Bypass type	Internal Bypass (Automatic and Manual)

Conformance

Product Certifications	ENERGY STAR V2.0 (USA) FCC part 15 class A UL 1778
------------------------	--

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 % non-condensing
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 % non-condensing
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)
Acoustic level	55 dBA
Online Thermal Dissipation	1712 Btu/h
IP degree of protection	IP20

Communications & Management

Free slots	1
Pre-Installed SmartSlot™ Cards	Network management card 3 with environmental monitoring
Alarm	Audible and visible alarms : prioritized by severity
Emergency Power Off (EPO)	Yes

Surge Protection and Filtering

Surge energy rating	480 J
----------------------------	-------

Ordering and shipping details

GTIN	731304732969
Country of origin	PH

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	28.1 in (71.5 cm)
Package 1 Width	39.4 in (100 cm)
Package 1 Length	24.5 in (62.2 cm)
Package 1 Weight	395.99 lb(US) (179.62 kg)

Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
-----------------	---

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)




Energy Efficient Take-back Transparency RoHS/REACH


Resource performance

 Energy Efficient Product

 Take-Back Program Available

Well-being performance

 Mercury Free

 Rohs Exemption Information Yes

Environmental Certifications

 Energy Star® ENERGY STAR UPS V2.0 (USA)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)

California Proposition 65 WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov