


MultiConnect[®] eCell

LTE Cellular to
Ethernet Bridge



The MultiConnect[®] eCell cellular to Ethernet bridge makes adding cellular connectivity to existing wired assets quick and easy. Providing wireless failover to prevent network outages to vending machines, kiosks, digital signs, ATM machines and countless other fixed assets that require reliable, always-on connectivity. With 4G-LTE, there's no need to sacrifice bandwidth when switching between cellular and Ethernet. Plus, it's easy set up wizard, bundled antenna, power supply and Ethernet cable make installation a snap. Best of all, it's cost-optimized to give you exactly what you need with minimal complexity in a rugged, aluminum chassis suitable for even extreme environments. And with FCC, IC, PTCRB and carrier certifications, the MultiConnect eCell reduces time to market as well as cost – so you can deploy your solution fast.

FEATURES

- 4G-LTE with 3G HSPA+ fallback
- 1 Ethernet LAN port
- Reset push button
- Aluminum chassis
- Two-year warranty, upgradable to five years

BENEFITS

- Lowest total cost of ownership
- Long and stable lifecycles
- Certified and carrier approved

Your Devices & Data



Connecting Your Devices




Wireless
Service
Provider



Asset
Management
Platform

Insight + Action + Control



SPECIFICATIONS

Model	MTE-LAT2
Performance	LTE Cat. 3
Frequency Band (MHz)	4G: 700(B17)/850(B5)/AWS1700(B4)/1900(B2) 3G: 850(B5)/1700 (B4)/1900(B2)
Packet Data*	Up to 100 Mbps downlink Up to 50 Mbps uplink
Diversity /MIMO	Rx Diversity and MIMO DL 2x2
Power Requirements	
Voltage	12VDC
Connectors	
Cellular	50 ohm SMA (female connector)
SIM	Mini SIM 2FF
LAN	RJ-45, 10/100 BaseT
Power	2.5mm Plug
Physical Description	
Physical Dimensions (L x W x H)	3.2" x 2.5" x 1.2" (81.2 x 63.5 x 30.5 millimeters)
Physical Weight	1.0 lbs (0.45 Kg)
Chassis Type	Aluminum
Environmental	
Operating Temperature	0° to +40°C
Storage Temperature	-40° to +185°F (-40°C to +85°C)
Relative Humidity	10% to 85% operating 5% to 90% storage
Certifications	
Regulatory Compliance	US: FCC Class B Canada: IC
Network	PTCRB, AT&T

* Actual performance speeds may be affected by a variety of attributes such as cell tower distance, data loads, packet sizes, etc.

HIGHLIGHTS

Applications

MultiConnect eCell cellular to Ethernet bridges are used in a wide variety of applications such as digital signage, smart vending, smart energy or home medical monitoring. It can also be used to provide main internet broadband and dial backup access for business continuity; WAN failover or OBM (Out-of-Band Management) path to IT devices at your remote sites. The MultiConnect eCell will help to ensure infrastructure is accessible from anywhere, even during system or network outage. Because they are certified and carrier approved, customers are able to quickly deploy with cellular connectivity to realize new revenue streams, opex reduction or improved service offering.

Comprehensive Service and Support

The MultiTech commitment to service means we provide a two year product warranty and service that includes free technical support, 24 hour website, and FTP support.

ORDERING INFORMATION

LTE Product

Model	Description	Region
MTE-LAT2-B07-US	LTE Cat 3 Cellular to Ethernet Bridge	North America
B07 = LTE cellular only		
US = Includes power supply, antennas and Ethernet cable		

Use ordering codes for specific build options.
Go to www.multitech.com for detailed product model numbers.

Produced in the U.S. of U.S. and non-U.S. components. Features and specifications are subject to change without notice.

Trademarks and Registered Trademarks: MultiTech and the MultiTech logo, MultiConnect: Multi-Tech Systems, Inc. All other products and technologies are the trademarks or registered trademarks of their respective holders.

2016-03 • 86002181 • © 2016 Multi-Tech Systems, Inc. All rights reserved.

SERVICES & WARRANTY

MultiTech's comprehensive Support Services programs offer a full array of options to suit your specific needs. These services are aimed at protecting your investment, extending the life of your solution or product, and reducing total cost of ownership. Our seasoned technical experts, with an average tenure of more than 10 years, can walk you through smooth installations, troubleshoot issues and help you with configurations.

INSTALLATION SUPPORT

MultiTech's Installation Support Service delivers priority service with the ability to work one-on-one with an experienced MultiTech technical support engineer, to guide you through the installation process for our products.

TECHNICAL SUPPORT SERVICES

At MultiTech, we're committed to providing you personalized attention and quality service while providing you a quick response to your product support needs. We have several options of support for you to choose from.

For additional information on Support Services as well as other service offerings, please contact your MultiTech representative or visit www.multitech.com/support.go

World Headquarters

Multi-Tech Systems, Inc.
2205 Woodale Drive
Mounds View, MN 55112 U.S.A.
Tel: 763-785-3500
Toll-Free: 800-328-9717
Email: sales@multitech.com
www.multitech.com

EMEA Headquarters

Multi-Tech Systems (EMEA)
Strata House
264-270 Bath Road
Harlington UB3 5JJ
United Kingdom
Tel: +(44) 118 959 7774
Email: sales@multitech.co.uk
www.multitech.co.uk

