

PowerLite Pet A5200AZE

AEG
perfekt in form und funktion

Product	Model No	A5200AZE	Nozzles	Nozzle Floor	
	PNC	900 257 963		Integr. access.	
	Name	PowerLite Pet			
	Bar code (EAN 13)	7332543359639		Non Integr. access.	Crevice nozzle, Dusting brush
Categorisation	Group	Floorcare		Nozzle, floor turbo	
	Product Class	Upright		Parketto Hard Floor Nozzle	
	Technology	Bagless		Mini Turbo Nozzle	Yes - Riser Visor
	Supply Unit	HUP		Hose	Stretch 2.4m
USP's				Handle Bent-end	Looped
				Tubes	
	Main USP or Key Feature	Arm & Hammer anti odor HEPA filter	Spares - Original	Motor Filter Ref No	
	2nd USP or Key Feature	Quick release stretch hose		Exhasust Filter Ref No	EF35
Energy Labeling	3rd USP or Key Feature	Multi cyclonic		Dustbag ref. n°	
				Drive Belt Ref No	ZE090
	Energy Rating	D		Dustbag Ref No	
	Carpet	C			
	Hardfloor	E	Spares - Menalux	Motor Filter Ref No	
	Dust Re-emission	E		Exhasust Filter Ref No	
	Noise db	90db		Dustbag ref. n°	
	Annual Energy Con kwh			Drive Belt Ref No	
Design/Controls	Colour	Metallic Silver/Blue		Dustbag Ref No	
	LED Power Display		Packaging & Logistics	Net weight, kg	6Kgs
	Carpet Height Adjustment	Yes	Single Package	Gross Weight, kgs	8.5Kgs
	Brush Roll Clean			Packaging Dims (WxDxH)mm	345 x 280 x 800
	Brush Roll On/Off			Package volume, Ltrs	77L
	Speed Settings	1		Stacking level	1
	Dustbag Full Indicator			Package type	Cardboard Corrugated
	Cord Rewind			Palette, units per	9
Technical Specifications	Remote Control			Palette, layers per	1
	Dust Compactor			Palette Dims (WxDxH)mm	1200 x 800 x 2100
				Palette, max height mm	
				No. of pieces per mastercarton	
	Voltage V	230v	Packaging Material	Corrugated Cardboard grams	
	Frequency Hz	50Hz		Paper/Carton	
	Power Output W/V	1300W NLS		Polyethylene (PE)	
	Guarantee Period Yrs	2 Yrs		Polypropylene (PP)	
	Motorised Brush Roll	Yes		Polystyrene (EPS/EPP)	
	Thermal Cut Out	Yes		Polyamide (PA)	
	Power Cord Length Mtrs	7m		PU Foam	
	Hose Length	2.4m stretch	Logistics	Intrastat code	85081100
	Action Radius			Country Of Origin	China
	Cyclone technology	Multi Cyclonic			
	Dims Product Only (WxDxH)mm	305 x 300 x 1120			
	Weight Product Only Kgs	6.58Kgs			
	Dust Capacity Ltrs	2L			
	Power Regulation				
	Soft Start Function				
	Energy cons, Wh				
Vacuum Performance	Suction Power AirWatts	170AW			
	Max Vacuum kPa				
	Pickup Wilton, meas/ref, %				
	Pickup Crevice, %				
	Max Airflow l/s				
	Noise level db				
	Motor Filter Type	Micro Fibre - Washable			
	Exhaust Filter Type	HEPA Filter - A&H Anti Odour			

