

THE SMART CHOICE FOR YOUR BUSINESS TABLET.

Company-ready. Employee-friendly.

The Lenovo™ TAB3 10 Business is optimized for enterprise mobility and fast, powerful multitasking. It's a truly smart choice for business with up to 12 incredible hours of battery life and powerful Android™ for Work software. After work, watch a movie on the brilliant 10.1" FHD display. Features like Dolby Atmos® audio, 5 MP front / 8 MP rear cameras, and IP52 splash and dust resistance help make this a Tablet where serious business meets serious versatility.

Lenovo™




WHY YOU SHOULD BUY THE LENOVO™ TAB3 10 BUSINESS



Brilliant Full-HD Display

Whether you're viewing spreadsheets or watching movies, get the big picture on the brilliant 10.1" Full-HD (1920 x 1200) IPS display.



Serious Durability

Splash-proof, dust-proof, and scratch-proof featuring Corning® Gorilla® Glass. Use this Tablet virtually anywhere without worrying about damage.



Work-optimized

TAB3 10 Business streamlines your workday with Android™ for Work software along with hardware encryption and policy controls to secure your work.



Long-lasting Battery

TAB3 10 Business's battery is built to go the distance. An astounding 12 hours of juice will let you keep your focus on the task at hand.

Lenovo™ TAB3 10 Business

SPECIFICATIONS

DESIGN



Operating System

Android™ 6.0



PERFORMANCE

Processor

MediaTek™ 1.3 GHz Quad-Core, 64-bit

Audio

Dual Speakers with Dolby Atmos®

Memory

RAM : 2 GB / 3 GB¹

Internal Storage : 32 GB / 64 GB¹ + microSD™

Expandable Memory : Up to 64 GB

Battery

Battery Capacity : 7000 mAh

Usage Time : Up to 12 Hours



¹ Check with MBG contact for MOQ.

² Available for limited countries.

WHAT'S IN THE BOX

- TAB3 10 Business
- Charger
- Safety / Warranty Guide
- Quick-Start Guide
- Cleaning Cloth*

* For selected countries.



WANT MORE?

ideapad™ MIIX 700 Business Edition
ThinkPad® X1 Tablet



WWW.LENOVO.COM



Lenovo reserves the right to alter product offerings and specifications at any time, without notice. Lenovo makes every effort to ensure accuracy of all information but is not liable or responsible for any editorial, photographic or typographic errors. All images are for illustration purposes only. For full Lenovo product, service and warranty specifications visit www.lenovo.com. Lenovo makes no representations or warranties regarding third party products or services. **Trademarks:** The following are trademarks or registered trademarks of Lenovo: Lenovo, the Lenovo logo, Yoga, Google and the Google logo are trademarks of Google Inc. Android is a trademark of Google Inc. Ultrabook, Celeron, Celeron Inside, Core Inside, Intel, Intel Logo, Intel Atom, Intel Atom Inside, Intel Core, Intel Inside, Intel Inside Logo, Intel vPro, i7, i5, i3, Pentium, Pentium Inside, vPro Inside, Xeon, Xeon Phi and Xeon Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product and service names may be trademarks or service marks of others. Battery life (and recharge times) will vary based on many factors including system settings and usage. ©2016 Lenovo. All rights reserved.

Display



Size : 10.1" FHD IPS
Resolution : 1920 x 1200
Scratch-proof : Corning® Gorilla® Glass
Durable : IP52 From P2i Technology
Splash-proof IPX2; Dust-proof IP5X

Colors



Slate Black

Camera



Rear
8 MP Auto-Focus
Front
5 MP Fixed-Focus

Video

Rear
8 MP - 1080p
Front
5 MP - 720p

Sensors

G-Sensor
Hall Sensor
Vibrator

SOFTWARE

Included Applications

- Android™ for Work
- Google Play for Work



CONNECTIVITY

Connectivity / Radios

4G Network : TDD LTE / FDD LTE²
3G Network : WCDMA / EVDO²
2G Network : GSM
WiFi : 802.11 a/b/g/n/ac
Bluetooth® : Yes
GPS Support : Yes
NFC : Yes
3.5 mm Audio Jack : Yes
FM Radio : Yes

RECOMMENDED LENOVO™ SERVICES

Warranty Extensions (1-to-3 Years Total Duration)* The fixed-term, fixed-cost service helps accurately budget for PC expense, protect your valuable investment and potentially lower the cost of ownership.

Accidental Damage Protection* Avoid the hassles of unexpected repair costs. Provides coverage for non-warranted damage incurred under normal operating conditions, such as minor spills, drops or damage to the integrated screen.

* Not available in all countries.